











DE

EN

DE + EN

LuK Standard-Reusable-Packaging

materialno.	photo	short mark	description	application: W = in-plant L = supplier I = Intercompany	remark	weight [kg]	length external [mm]	width external [mm]	height external [mm]	length internal [mm]	width internal [mm]	height internal [mm]
049900021-0000		GP-KL_1	LUK COLLAPSIBLE	W / L / I		87	1220	824	960	1140	744	764
051049031-0000		GP-KL_2	LUK-KLAPPGITTERBOX NIEDRIG	W / L / I		74	1220	824	670	1140	744	432
058188630-0000		K1208	SCHAEFFLER-KLAPPSTAHLBEHÄLTER 1200x800	W / L / I		98	1200	800	650	1150	740	480
002439140-0000		EURO-FLP	EURO-PALETTE	W / L / I	intermediate-term no longer applicable	25	1200	800	145	-	-	-
011023031-0000		K-PAL_1	SCHAEFFLER-KUNSTSTOFFPALETTE SCHWARZ	W / L / I		18	1200	800	160	-	-	-
071482997-0000		KLT 3215	SCHAEFFLER-KLT 3215	W / L / I		0,57	300	200	147	243	162	130
070553300-0000		KLT 4315	SCHAEFFLER-KLT 4315	W / L / I		1,29	400,00	300,00	147,00	346,00	265,00	110,00
050886320-0000		KLT 4328	SCHAEFFLER-KLT 4328	W / L / I		2,60	400,00	300,00	280,00	334,00	247,00	236,00
073713317-0000		KLT 6429	SCHAEFFLER-KLT 6429	W / L / I		2,97	600,00	400,00	280,00	544,00	364,00	242,00
079981771-0000		A 1208	SCHAEFFLER COVERING PLATE 1208	W / L / I		6,10	1200,00	800,00	94,00	-	-	-