



# Embrayages

Octobre 2017



Additif Catalogue



## Nouveautés PL



**SCHAEFFLER**  
AUTOMOTIVE AFTERMARKET

# DAF



## DAF

### CF

290 MX-11 210; (210kW)	05.13-	ZF; Ecosplit 4; Euro 6	643 3438 00		
		ZF; Ecosplit 4; Euro 6	143 0368 10		

### CF 65

65 180, 220, 250, 280 CE 136 C; CE 162 C; CE 184 C; GR 210 S1; (136-210kW)	01.01-05.13	ZF; 6S-850	340 0092 10		
--	-------------	------------	-------------	--	--

### LF 45

45 150, 170, 180, 220 BE 110 C; BE 123 C; CE 136 C; CE 162 C; FR 136 S1; (110-162kW)	01.01-	ZF; 6S-850	340 0092 10		
--	--------	------------	-------------	--	--

### LF 55

55 170, 180, 220, 250 BE 123 C; CE 136 C; CE 162 C; CE 184 C; (123-184kW)	01.01-	ZF; 6S-850	340 0092 10		
---	--------	------------	-------------	--	--

## IVECO

### EuroCargo IV

110E22 110E22FP, 110E22P F4AFE611A; (162kW)	09.15-	ZF; 6S 800 TO	640 3098 00		
120E22 120E22FP, 120E22P, 120EL22, 120EL22P; 140E22 140E22FP, 140E22P; 140E25 140E25FP, 140E25P F4AFE611A; F4AFE611E; (162-185kW)	09.15-	ZF; 6S 800 TO ZF; 9S 75 TO	640 3098 00		
150E25 150E25FP, 150E25P; 150E25W F4AFE611E; (185kW)	09.15-	ZF; 6S 800 TO	640 3098 00		
160E25 160E25FP, 160E25P; 160E28 160E28FP, 160E28P; 180E25 180E25FP, 180E25P F4AFE611C; F4AFE611E; (185-206kW)	09.15-	ZF; 6S 800 TO ZF; 9S 75 TO	640 3098 00		

## MITSUBISHI

### Canter (FE5, FE6) 6.Generation

Canter 35, 55 BM FB 634 B, FB 634 D, FB 634 E, FB 634 EV, FE 544 B, FE 544 D, FE 544 E 4M42-0AT; (92kW)	09.01-	→02.05; + Europe; BM FE 534; FA6; M025S5; <b>G4</b> →02.05; + Europe; BM FE 544; FA6; M025S5; <b>G5</b> →02.05; + Europe; BM FB631; FA5; M025S5; <b>G5</b> →02.05; + Europe; BM FB 641; FA5; M025S5; <b>G5</b>	628 3319 00	128 0253 60 328 0660 10 500 0791 60	6 5
FE150C1; FE150C3 FE150E3 BM FE83PC4SRFAA, FE83PE4SRFAA 4D34-3AT3B; (100-109kW)	10.97-	01.05→10.08; Nouvelle Zélande; BM FE9; M025S5 07.06→; TR; BM FB 83P; FF7; M025S5	628 3319 00	128 0253 60 328 0660 10 500 0791 60	6 5
Canter 60 BM FE 649 4D34-2AT4; (100kW)	08.96-	BM FE 519; F87; M025S5; <b>G5</b> 05.02→08.05; TR; BM FE 519; F96; M025S5; <b>G5</b>	628 3319 00	128 0253 60 328 0660 10 500 0791 60	6 5

## RENAULT TRUCKS

### Midlum

240.12; 240.13; 240.14; 240.15; 240.16; 240.18; 280.12; 280.13; 280.14; 280.16; 280.18 DXi 7; (177-206kW)	05.06-	ZF; 6AS 1000	640 3082 00		
--	--------	--------------	-------------	--	--

### Premium 2

Distribution 240.18 D; Distribution 270.19, 280.26, 310.18, 310.26, 320.18, 320.26, 340.18, 340.19, 340.26; Distri- bution 280.18 D; Distribution 320.18 D; Lander 270.18, 270.19, 310.19, 310.26, 340.18, 340.19, 340.26 DXi 7; (177-247kW)	10.05-	ZF; 6AS 1000; S2266	640 3082 00		
--	--------	---------------------	-------------	--	--

# MERCEDES-BENZ



## MERCEDES-BENZ

### INTOURO

Intouro BM 633.051, 633.052, 633.251, 633.252 OM 457.965; OM 926.939; (210-220kW)	01.05-	Euro 5; GO 110; ⓘ A4440000225	640 3102 00	140 0230 10 340 0093 10 500 0806 20	6	5
		Euro 5; GO 110; ⓘ A4440000225	340 0093 10			

### TOURINO (O 510)




























TOURINO BM 444.200, 444.203 OM 906.961; OM 906.962; (180-205kW)	10.03-	Euro 4 (D4); ⓘ A4440000225	640 3102 00	140 0230 10 340 0093 10 500 0806 20	6	5
		ⓘ A4440000225; Euro 4 (D4)	340 0093 10			



143 0368 10	DAF	2
340 0092 10	DAF	2
340 0093 10	MERCEDES- BENZ	4
628 3319 00	MITSUBISHI	2
640 3082 00	RENAULT TRUCKS	2
640 3098 00	IVECO	2
640 3102 00	MERCEDES- BENZ	4
643 3438 00	DAF	2



# Liste des Composants

											
628 3319 00	MITSUBISHI	 128 0253 60	277 TBFR								
		 328 0660 10	278 TZFV	29,4X23,7	14						
		 500 0791 60									
640 3082 00	RENAULT TRUCKS	 140 0232 10	395 TBFR								
		 340 0092 10	395 TZFV	1 3/4	10						
		 500 1228 10									
640 3098 00	IVECO	 140 0239 10	400 TBFP								
		 340 0102 10	400 TZFV	1 3/4	10						
		 500 0265 20									
640 3102 00	MERCEDES-BENZ	 140 0230 10	400 TBFR								
		 340 0093 10	395 TZFV	36X40	18						
		 500 0806 20									
643 3438 00	DAF	 143 0368 10	430 ZBFM								
		 343 0150 10	430 TZFV	41X50	10						
		 500 1171 10									



**0...**

001 250 99 15	MERCEDES-BENZ	500 0806 20
002 250 00 15	MERCEDES-BENZ	500 0806 20
002 250 65 15	MERCEDES-BENZ	500 0806 20
007 250 15 04	MERCEDES-BENZ	140 0230 10
024 250 97 03	MERCEDES-BENZ	340 0093 10

**1...**

145 0120	DAF	343 0150 10
166 3220	DAF	343 0150 10
168 5711	DAF	343 0150 10
168 6642	DAF	500 1171 10
169 7725	DAF	500 1171 10
174 6150	DAF	500 1171 10
182 2487	DAF	500 1171 10
182 2997R	DAF	500 1171 10
183 0316	DAF	500 1171 10
184 6414	DAF	343 0150 10
184 6414R	DAF	343 0150 10
185 8564	DAF	143 0368 10
1903899	IVECO	500 0265 20
1903936	IVECO	500 0265 20
191 2687	DAF	500 1171 10

**2...**

2443133	IVECO	500 0265 20
---------	-------	-------------

**4...**

42003473	IVECO	500 0265 20
42063184	IVECO	500 0265 20

**5...**

5000 55479	IVECO	640 3098 00
50 10 545 831	RENAULT TRUCKS	340 0092 10
50 10 545 988	RENAULT TRUCKS	500 1228 10
50 10 613 151	RENAULT TRUCKS	340 0092 10
5042 13753	IVECO	500 0265 20
5042 29179	IVECO	500 0265 20
5042 29188	IVECO	500 0265 20
5801 555053	IVECO	140 0239 10
5801 555666	IVECO	340 0102 10

**7...**

74 20 959 262	RENAULT TRUCKS	340 0092 10
7421 005 308	RENAULT TRUCKS	140 0232 10
74 21 188 863	RENAULT TRUCKS	500 1228 10
74 21 274 770	RENAULT TRUCKS	340 0092 10
74 21 916 049	RENAULT TRUCKS	340 0092 10

**M...**

ME500169	MITSUBISHI	128 0253 60
ME500507	MITSUBISHI	128 0253 60
ME500615	MITSUBISHI	128 0253 60
ME500762	MITSUBISHI	328 0660 10
ME500850	MITSUBISHI	128 0253 60
ME516323	MITSUBISHI	328 0660 10
ME605584	MITSUBISHI	500 0791 60

