

PIÈCES DE SUSPENSION ET DE DIRECTION

Décembre 2018
Additif catalogue



Votre spécialiste de systèmes pour moteurs et châssis



--	--	--	--	--	--

AUDI**Q7 (4L)**

3.0 TDI quattro; 3.0 TFSI quattro; 3.6 FSI quattro; 4.2 FSI quattro; 4.2 quattro; 4.2 TDI quattro; 6.0 TDI quattro (150-368kW)	03.06-08.15	L 201 mm; L 201 mm;		916730	
				916731	

TT II (8J3, 8J9)

1.8 [04]; 1.8 TFSI [04]; 2.0 TDI quattro [04]; 2.0 TFSI [04]; 2.0 TFSI [05]; 2.0 TFSI quattro [04]; 2.0 TTS quattro [04]; 2.5 RS quattro [04]; 2.5 RS quattro [05]; 3.2 V6 quattro [04]; 3.2 V6 quattro [05] (118-265kW)	08.06-06.14		935769	935769	
--	-------------	--	--------	--------	--

BMW**5 (F10, F11)**

518 d [03] (100-120kW)	10.12-	des deux côtés de l'essieu avant, supérieur; 21;	935085	935085	23, 23
520 d [03]; 520 d xDrive [03] (100-155kW)	11.09-	des deux côtés de l'essieu avant, supérieur; 21;	935085	935085	23, 23
520 i [03]; 523 i [03] (120-150kW)	11.09-	des deux côtés de l'essieu avant, supérieur; 21;	935085	935085	23, 23
525 d [03]; 525 d xDrive [03] (150-160kW)	11.09-	des deux côtés de l'essieu avant, supérieur; 21;	935085	935085	23, 23
528 i [03]; 528 i xDrive [03] (180-190kW)	11.09-	des deux côtés de l'essieu avant, supérieur; 21;	935085	935085	23, 23
530 d [03]; 530 d xDrive [03] (180-210kW)	11.09-	des deux côtés de l'essieu avant, supérieur; 21;	935085	935085	23, 23
530 i [03]; 535 d [03] (190-230kW)	03.10-	des deux côtés de l'essieu avant, supérieur; 21;	935085	935085	23, 23
535 d xDrive [03]; 535 i [03] (225-240kW)	11.09-	des deux côtés de l'essieu avant, supérieur; 21;	935085	935085	23, 23
535 i xDrive [03]; 550 i [03] (225-330kW)	07.10-	des deux côtés de l'essieu avant, supérieur; 21;	935085	935085	23, 23
M 550 d xDrive [03] (280kW)	10.10-	des deux côtés de l'essieu avant, supérieur; 21;	935085	935085	23, 23

5 GRAN TURISMO (F07)

520 d [02]; 528 i [02]; 530 d [02]; 530 d xDrive [02]; 535 d [02]; 535 d xDrive [02]; 535 i [02]; 535 i xDrive [02]; 550 i [02]; 550 i xDrive [02] (100-330kW)	01.09-02.17	des deux côtés de l'essieu avant, supérieur; 21;	935085	935085	23, 23
--	-------------	---	--------	--------	--------

6 (F06, F12, F13)**7 (F01, F02, F03, F04)****i8**

hybrid [04] (170-266kW)	03.14-	des deux côtés de l'essieu avant, supérieur; 21;	935085	935085	23, 23
-------------------------	--------	---	--------	--------	--------

BUICK**ENCORE Véhicule tout terrain fermé**

1.4; 1.4 AWD (103-114kW)	09.12-	M12x1,5; L 286 mm	919112		
		M12x1,5; L 286 mm	919113		23

CHEVROLET**TRAX**

1.4; 1.4 AWD; 1.4 Flex; 1.4 LPG; 1.6; 1.7 TD; 1.7 TD AWD; 1.8; 1.8 AWD; 1.8 Flex (85-113kW)	12.12-	M12x1,5; L 286 mm	919112		
		M12x1,5; L 286 mm	919113		23

FIAT**DOBLO (119)**

1.2 (223AXA1A); 1.3 D Multijet; 1.4; 1.6 16V (223AXD1A); 1.6 Natural Power; 1.9 D (223AXB1A); 1.9 D Multijet; 1.9 JTD; 1.9 JTD (223AXE1A) (46-88kW)	03.01-	BD:17X56X78[mm]; BD:17X56X78[mm]; 17; 78; 56 mm	985884	985884	23, 23
---	--------	--	--------	--------	--------

DOBLO Cargo (223)

1.2 (223ZA1A) [03]; 1.3 D Multijet [03]; 1.3 JTD 16V [03]; 1.4 [03]; 1.6 16V (223ZXD1A) [03]; 1.6 Natural Power [03]; 1.9 D (223ZXB1A) [03]; 1.9 JTD [03]; 1.9 JTD (223ZXE1A) [03] (46-77kW)	03.01-	BD:17X56X78[mm]; BD:17X56X78[mm]; 17; 78; 56 mm	985884	985884	23, 23
--	--------	--	--------	--------	--------

					
--	--	--	--	--	--

NISSAN

MICRA IV (K13)

1.0 Flex [02]; 1.2 [02]; 1.2 4WD [02]; 1.2 DIG-S [02]; 1.5 [02]; 1.5 D [02]; 1.5 NISMO S [02]; 1.6 [02]; 1.6 Flex [02] (47-85kW)	05.10-	 ↔; M14x1,5; M12x1,25; L 227 mm	926838	926838	23, 23
--	--------	--	--------	--------	--------

OPEL

ASCONA C (J82) / ASCONA C 3/5 portes (J82)

1.3 N (F11, M11, F69, M69) [01]; 1.3 N (F68, M68) [02]; 1.3 S (F11, M11, F68, M68) [01]; 1.3 S (F68, M68) [02]; 1.6 (F11, F68, M11, M68) [01]; 1.6 (F11, M11, F68, M68) [01]; 1.6 (F68, M68) [02]; 1.6 D (F11, M11, F68, M68) [01]; 1.6 D (F68, M68) [02]; 1.6 i (F11, M11, F68, M68) [01]; 1.6 i (F68, M68) [02]; 1.6 i Cat (F11, M11, F68, M68) [01]; 1.6 i Cat (F68, M68) [02]; 1.6 S (F11, M11, F68, M68) [01]; 1.6 S (F68, M68) [02]; 1.8 (F11, M11, F68, M68) [01]; 1.8 (F68, M68) [02]; 1.8 E (F11, M11, F68, M68) [01]; 1.8 E (F68, M68) [02]; 1.8 i (F11, M11, F68, M68) [01]; 1.8 i (F68, M68) [02]; 2.0 i (F11, M11, F68, M68) [01]; 2.0 i (F68, M68) [02]; 2.0 i Cat (F11, M11, F68, M68) [01]; 2.0 i Cat (F68, M68) [02]; 2.0 i GT (F11, M11, F68, M68) [01]; 2.0 i GT (F68, M68) [02] (40-95kW)	09.81-08.88	 ↔;  M8x1,25; L 155 mm	925326	925326	
---	-------------	--	--------	--------	--

ASTRA H

1.4 (L67) [05]; 1.6 (L67) [05]; 1.6 Turbo (L67) [05]; 1.8 (L67) [05]; 1.9 CDTi (L67) [05]; 2.0 Turbo (L67) [05] (66-147kW)	09.05-10.10	 ; Partie supérieure; BD:24; 24; Support en caoutchouc	985369		23
--	-------------	--	--------	--	----

MERIVA B (S10)

1.3 CDTi (75); 1.4 (75); 1.4 LPG (75); 1.6 CDTi (75); 1.7 CDTi (75) (55-103kW)	06.10-03.17	 ; Partie supérieure; BD:24; 24; Support en caoutchouc	985369		23
--	-------------	---	--------	--	----

MOKKA / MOKKA X (J13)

1.4 ([76]); 1.4 4x4 ([76]); 1.4 LPG ([76]); 1.6 ([76]); 1.6 CDTi ([76]); 1.6 CDTi 4x4 ([76]); 1.7 CDTi ([76]); 1.7 CDTi 4x4 ([76]); 1.8 ([76]); 1.8 4x4 ([76]) (81-112kW)	06.12-	 M12x1,5;  L 286 mm  M12x1,5;  L 286 mm	919112		23
---	--------	--	--------	--	----

SIGNUM 3/5 portes (Z03)

1.8 (F48) [02]; 1.9 CDTi (F48) [02]; 2.0 DTi (F48) [02]; 2.0 Turbo (F48) [02]; 2.2 direct (F48) [02]; 2.2 DTi (F48) [02]; 2.8 V6 Turbo (F48) [02]; 3.0 V6 CDTi (F48) [02]; 3.2 V6 (F48) [02] (74-184kW)	05.03-12.08	 ; Partie supérieure;  61000001 → / 68 →; BD:24; 24; Support en caoutchouc	985369		23
---	-------------	--	--------	--	----

VECTRA C

1.6 (F35) [03]; 1.6 (F68) [02]; 1.6 (F69) [01]; 1.6 16V (F35) [03]; 1.6 16V (F69) [01]; 1.8 (F35) [03]; 1.8 (F68) [02]; 1.8 (F69) [01]; 1.8 16V [01]; 1.8 16V (F68) [02]; 1.9 CDTi (F35) [03]; 1.9 CDTi (F68) [02]; 1.9 CDTi (F69) [01]; 2.0 16V Turbo (F68) [02]; 2.0 16V Turbo (F69) [01]; 2.0 DTi (F35) [03]; 2.0 DTi 16V (F68) [02]; 2.0 DTi 16V (F69) [01]; 2.0 Turbo (F35) [03]; 2.2 16V (F68) [02]; 2.2 16V (F69) [01]; 2.2 DGi (F68) [02]; 2.2 DGi (F69) [01]; 2.2 direct (F35) [03]; 2.2 DTi (F35) [03]; 2.2 DTi 16V (F68) [02]; 2.2 DTi 16V (F69) [01]; 2.8 V6 Turbo (F35) [03]; 2.8 V6 Turbo (F68) [02]; 2.8 V6 Turbo (F69) [01]; 2.8 V6 Turbo OPC (F69) [01]; 3.0 CDTi (F68) [02]; 3.0 CDTi (F69) [01]; 3.0 V6 CDTi (F35) [03]; 3.2 V6 (F35) [03]; 3.2 V6 (F68) [02]; 3.2 V6 (F69) [01] (74-206kW)	04.02-01.09	 ; Partie supérieure;  61000001 → / 68 →; BD:24; 24; Support en caoutchouc	985369		23
--	-------------	--	--------	--	----

OPEL					
ZAFIRA B (A05) / ZAFIRA B Van (A05)					
1.6 (M75); 1.6 CNG (M75); 1.6 CNG Turbo (M75); 1.7 CDTi (M75); 1.8 (M75); 1.9 CDTi (M75); 2.0 (M75); 2.2 (M75) (62-177kW)	07.05-	Partie supérieure; BD:24; 24; Support en caoutchouc	985369		23
PORSCHE					
CAYENNE (9PA, 92A)					
3.0 Diesel; 3.0 S; 3.0 S E-Hybrid; 3.0 TDI; 3.2; 3.6; 3.6 GTS; 3.6 S; 4.2 S Diesel; 4.8 GTS; 4.8 S; 4.8 Turbo; 4.8 Turbo S; GTS 4.8; S 4.5; S 4.8; Turbo 4.5; Turbo 4.8; Turbo S 4.5; Turbo S 4.8 (155-419kW)	09.02-	L 201 mm; L 201 mm;		916730 916731	
VAUXHALL					
ASTRA Mk V (H)					
1.6 (L67) [05]; 1.6 i 16V (L67) [05]; 1.8 (L67) [05]; 1.9 CDTi (L67) [05]; 2.0 (L67) [05]; 2.0 Turbo (L67) [05] (77-147kW)	09.05-08.11	Partie supérieure; BD:24; 24; Support en caoutchouc	985369		23
CAVALIER Mk II					
1.3 S [02]; 1.6 [03]; 1.6 D [01]; 1.6 i [01]; 1.6 i Cat [01]; 1.6 N [01]; 1.6 S [02]; 1.8 i [02]; 1.8 i [03]; 1.8 i Cat [01]; 1600D [02]; 1800i [05]; 2.0 4x4 [02]; 2.0 i [01]; 2.0 i Cat [02]; 2.0 SRi 130 [02]; 2000i [02] (40-95kW)	09.81-10.88	M8x1,25; L 155 mm	925326	925326	
MERIVA Mk II (B) (S10)					
1.3 CDTi; 1.4; 1.4 LPG; 1.6 CDTi; 1.7 CDTi (55-103kW)	06.10-	Partie supérieure; BD:24; 24; Support en caoutchouc	985369		23
MOKKA / MOKKA X (J13)					
1.4; 1.4 4x4; 1.6; 1.6 CDTi; 1.6 CDTi 4x4; 1.7 CDTi; 1.7 CDTi 4x4 (81-112kW)	06.12-	M12x1,5; L 286 mm M12x1,5; L 286 mm	919112 919113		23
SIGNUM (Z03)					
1.8 [02]; 1.9 CDTi [02]; 1.9 CDTi 16V [02]; 1.9 Turbo [02]; 2.0 DTi [02]; 2.0 i Turbo [02]; 2.2 DTi [02]; 2.2 i [02]; 2.8 V6 Turbo [02]; 3.0 CDTi [02]; 3.0 V6 CDTi [02]; 3.2 V6 [02] (74-184kW)	03.03-10.08	Partie supérieure; 61000001→ / 68→; BD:24; 24; Support en caoutchouc	985369		23
VECTRA Mk II (C)					
1.6 [03]; 1.8 [03]; 1.8 16V [01]; 1.8 16V [03]; 1.8 16V Dualfuel [01]; 1.9 CDTi [01]; 1.9 CDTi [03]; 1.9 CDTi 16V [01]; 1.9 CDTi 16V [03]; 2.0 16V Turbo [01]; 2.0 16V Turbo [03]; 2.0 DTi 16V [01]; 2.0 DTi 16V [03]; 2.2 16V [01]; 2.2 direct [01]; 2.2 direct [03]; 2.2 DTi 16V [01]; 2.2 DTi 16V [03]; 2.8 V6 Turbo [03]; 3.0 CDTi [03]; 3.0 V6 CDTi [01]; 3.0 V6 CDTi [03]; 3.2 V6 [01]; 3.2 V6 [03] (74-206kW)	01.00-05.09	Partie supérieure; 61000001→ / 68→; BD:24; 24; Support en caoutchouc	985369		23
VECTRA Mk II (C) GTS (Z02)					
1.8 [02]; 1.8 16V [02]; 1.8 16V Dualfuel [02]; 1.9 CDTi [02]; 1.9 CDTi 16V [02]; 2.0 16V Turbo [02]; 2.0 DTi 16V [02]; 2.2 16V [02]; 2.2 direct [02]; 2.2 DTi 16V [02]; 2.8 V6 Turbo [02]; 3.0 CDTi [02]; 3.0 V6 CDTi [02]; 3.2 V6 [02] (74-206kW)	08.02-05.09	Partie supérieure; 61000001→ / 68→; BD:24; 24; Support en caoutchouc	985369		23
ZAFIRA Mk II (B) (A05)					
1.6; 1.6 CNG; 1.6 CNG Turbo; 1.7 CDTi; 1.8; 1.9 CDTi; 2.0; 2.2 (69-176kW)	04.05-11.14	Partie supérieure; BD:24; 24; Support en caoutchouc	985369		23

								
---	--	--	---	--	---	---	--	--

916730	AUDI	15
916730	PORSCHE	17
916730	VW	18
916731	AUDI	15
916731	PORSCHE	17
916731	VW	18
919112	BUICK	15
919112	CHEVROLET	15
919112	OPEL	16
919112	VAUXHALL	17
919113	BUICK	15
919113	CHEVROLET	15
919113	OPEL	16
919113	VAUXHALL	17
925326	OPEL	16
925326	VAUXHALL	17
926838	NISSAN	16
935085	BMW	15
935769	AUDI	15
985369	OPEL	16, 17
985369	VAUXHALL	17
985884	FIAT	15



Références OE

 	 	 	 
AUDI 7L0 505 465 A 916730 7L0 505 465 B 916730 7L0 505 465 C 916730 7L0 505 465 D 916730 7L0 505 466 A 916731 7L0 505 466 B 916731 7L0 505 466 C 916731 7L0 505 466 D 916731 8J0407151D 935769			
BMW 31 12 6 775 967 935085			
CHEVROLET 95942519 919112 95942520 919113			
FIAT 46767261 985884			
NISSAN D8521-1HA0A 926838			
OPEL 16 03 149 925326 3 50 231 919112 3 50 232 919113 3 50 390 985369 95942519 919112 95942520 919113			
PORSCHE 95533306910 916730 95533306921 916730 95533307010 916731 95533307021 916731			
VAUXHALL 13204070 985369			



↑

CR

RUVILLE

RUVILLE

985883

985884



→

CR

				

				



