

FAG Rolling Bearing Grease

Arcanol VIB3

Properties, applications: Bearing grease for oscillating bearings, especially for small slewing angles, moderate to high loads, low starting temperatures, low starting friction, also for vertical shaft and rotating outer ring

Characteristics	Value	Unit	Test method
Temperature range:	-30 to 150	°C	DIN 51825 / Schaeffler Spec.
Longtime limit temperature	90	°C	
Density:	0.9	kg/dm ³	
Specifications:			
Thickener:	lithium complex		
Type of base oil:	mineral oil		
Base oil viscosity	at 40 °C:	170	mm ² /s
	at 100 °C:	14	mm ² /s
Worked penetration:	200-230	0.1 mm	DIN ISO 2137
NLGI grade:	3		DIN 51518
Drop point:	≥ 250	°C	DIN ISO 2176
Water resistance:	1-90	Range	DIN 51807 - 1
Corrosion Emcor Test:	≤ 0/0	Corr. Grade	DIN 51802
	with 0.5 % NaCl:		Corr. Grade
Copper corrosion after 24 h/120 °C:	≤ 2	Corr. Grade	DIN 51811
FE8 tests run wear behaviour, Running time 500 hours without failure			
536050 - 3000/10-80	vWk50 ≤ 35	mg	DIN 51819
536050 - 7.5/80-RT	vWk50 ≤ 35	mg	DIN 51819
FE9 tests run (grease service lifetime)			
A/1500/6000-150	F50 ≥ 100	h	DIN 51821-02
Speed range:	Unit	Ball bearings and cylindrical roller bearings	Other roller bearings*)
Speed limit n*dm	mm/min	350,000	200,000

*) not cylindrical roller thrust bearings and spherical roller thrust bearings

This copy is not taken into account by the updating service.

The data are based on actual knowledge at the time of print and refer to the respective test method. Guaranteed properties or warranties cannot be taken over.