



Commande des soupapes

Avril 2018

Additif Catalogue



Nouveautés VL

SCHAEFFLER
AUTOMOTIVE AFTERMARKET



						QTY	
MERCEDES-BENZ							
CLASSE C Coupe Sport (CL203)							
C 180; C 200 Kompressor; C 230 Kompressor	03.01-05.02	M 111.951; M 111.955; M 111.981; (95-145kW)				16	8
CLASSE C Break (S202)							
C 180 T; C 200 T; C 200 T Kompressor; C 230 T; C 230 T Kompressor	06.96-03.01	M 111.920; M 111.921; M 111.941; M 111.944; M 111.945; M 111.952; M 111.956; M 111.974; M 111.975; (90-142kW)				16	8
CLASSE C T-Model (S203)							
C 180; C 200 Kompressor	03.01-05.02	M 111.951; M 111.955; (95-120kW)				16	8
CLASSE C (W202)							
C 180; C 200; C 200 Kompressor; C 220; C 230; C 230 Kompressor	03.93-05.00	M 111.920; M 111.921; M 111.941; M 111.944; M 111.945; M 111.961; M 111.974; M 111.975; (89-142kW)				16	8
C 280; C 36 AMG	05.93-05.00	M 104.941; M 104.941 (AMG 3.6); (142-206kW)				24	8
CLASSE C (W203)							
C 180; C 200 Kompressor	05.00-06.02	M 111.951; M 111.955; (95-120kW)				16	8
CLK Décapotable (A208)							
200; 200 Kompressor; 230 Kompressor	03.98-03.02	M 111.941; M 111.944; M 111.945; M 111.956; M 111.973; M 111.975; M 111.982; (100-145kW)				16	8
CLK (C208)							
200; 200 Kompressor; 230 Kompressor	06.97-06.02	M 111.944; M 111.945; M 111.956; M 111.973; M 111.975; M 111.982; (100-145kW)				16	8
COUPE (C124)							
220 CE	10.92-05.93	M 111.960; (110kW)				16	8
300 CE-24; 320 CE	09.89-05.93	M 104.980; M 104.992; (162kW)				24	8
E-CLASS (A124, A124)							
300 CE-24; E 320; E 36 AMG	04.92-03.98	M 104.980; M 104.992; M 104.992 (AMG 3.6); (162-200kW)				24	8
E 200; E 220	06.93-03.98	M 111.940; M 111.960; (100-110kW)				16	8
CLASSE E Coupé (C124)							
E 200; E 220	06.93-06.97	M 111.940; M 111.960; (100-110kW)				16	8
E 320; E 36 AMG	06.93-06.97	M 104.992; M 104.992 (AMG 3.6); (162-200kW)				24	8
E-CLASS (S124, S124)							
200 TE; 220 TE; E 200 T; E 220 T	05.86-06.96	M 111.940; M 111.960; (100-110kW)				16	8
280 TE; 300 TE-24; 320 TE; E 280 T; E 320 T; E 36 T AMG	09.89-06.96	M 104.942; M 104.980; M 104.992; M 104.992 (AMG 3.6); (142-200kW)				24	8
E 300 TE-24 AMG	06.93-06.96	M 104.980; (162kW)		→000282, - AUS →000704, , - AUS →000718, , AUS →003032, AUS 008694→, 040890→,		24	8
CLASSE E Break (S210)							
E 200 T; E 200 T Kompressor; E 230 T	06.96-03.03	M 111.942; M 111.947; M 111.957; M 111.970; (100-137kW)				16	8
E 420 T	06.96-06.97	M 119.985; (205kW)				32	8
E-CLASS (W124, W124)							
200 E; 220 E; E 200; E 220	10.92-06.95	M 111.940; M 111.960; (100-110kW)				16	8
280 E; 300 E-24; 320 E; E 280; E 320	09.88-06.95	M 104.942; M 104.980; M 104.992; (142-162kW)				24	8
400 E 4.2; 500 E; E 420; E 500; E 60 AMG	01.91-06.95	M 119.974; M 119.974 (AMG 6.0); M 119.975; (205-280kW)				32	8
CLASSE E (W210)							
E 200; E 200 Kompressor; E 230	06.95-03.02	M 111.942; M 111.947; M 111.957; M 111.970; (100-137kW)				16	8
E 280; E 320	06.95-06.97	M 104.945; M 104.995; (142-162kW)				24	8
E 420; E 50 AMG	01.96-08.97	M 119.985; M 119.985 (AMG 5.0); (205-255kW)				32	8
G-Model (W463, W463)							
320 GE; G 320	09.94-12.97	M 104.996; (155kW)				24	8
G 36 AMG	01.95-07.98	M 104.996 (AMG 3.6); (200kW)		M104.996		24	8
CLASSE M (W163)							
ML 230	02.98-06.05	M 111.977; (110kW)				16	8

						QTY	
MERCEDES-BENZ							
S-CLASS (W140, C140)							
300 SE, SEL/S320; 300 SE 2.8; S 280	03.91-10.98	M 104.944; M 104.990; M 104.994; (142-170kW)				420 0042 10	24 8
400 SE, SEL/S420; 500 SE, SEL; S 420; S 500; SEC/CL 420; SEC/CL 500	02.91-02.99	M 119.970; M 119.971; M 119.980; M 119.981; (205-240kW)				420 0042 10	32 8
600 SE, SEL; S 600; SEC/CL 600	04.91-02.99	M 120.980; M 120.982; (290-300kW)				420 0042 10	48 8
SL (R129)							
280; 300 SL-24; 320	03.89-10.01	M 104.943; M 104.981; M 104.991; (142-170kW)				420 0042 10	24 8
500; 500 SL	09.89-10.01	M 119.960; M 119.972; M 119.982; (235-240kW)				420 0042 10	32 8
600; 60 AMG	07.92-10.01	M 119.982 (AMG 6.0); M 120.981; M 120.983; (280-290kW)				420 0042 10	48 8
SLK (R170)							
200; 200 Kompressor; 230 Kompressor	09.96-04.04	M 111.943; M 111.946; M 111.958; M 111.973; M 111.983; (100-145kW)				420 0042 10	16 8
Sprinter (901, 902, 901, 902, 901, 902)							
214; 214 NGT	02.95-05.06	M 111.979; M 111.984; (92-105kW)				420 0042 10	16 8
Sprinter (903, 903, 903)							
314; 314 4x4; 314 NGT	02.95-05.06	M 111.979; M 111.984; (92-105kW)				420 0042 10	16 8
Sprinter (904, 904, 904)							
414; 414 4x4	02.96-05.06	M 111.979; M 111.984; (105kW)				420 0042 10	16 8
CLASSE V (638/2)							
V 200; V 230	10.96-07.03	M 111.948; M 111.950; M 111.978; M 111.980; (95-105kW)				420 0042 10	16 8
VITO (638, 638)							
113 2.0; 114 2.3	02.96-07.03	M 111.948; M 111.950; M 111.978; (95-105kW)				420 0042 10	16 8
PUCH							
G-MODELL (W 463)							
G 320	09.94-12.97	M 104.996; (155kW)				420 0042 10	24 8
G 36 AMG	01.95-04.98	M 104.952 (AMG 3,6); (200kW)		M104.996		420 0042 10	24 8
SSANGYONG							
REXTON (GAB_)							
3.2 4x4	04.02-	G32D; (162kW)				420 0042 10	24 8
VW							
LT II 28-35/46 (2DC, 2DF, 2DG, 2DL, 2DB, 2DE, 2DK, 2DA, 2DD, 2DH)							
2.3	05.96-07.06	AGL; (105kW)		AGL		420 0042 10	16 8



Liste numérique

--	--	--	--	--	--	--	--	--

420 0042 10	MERCEDES-BENZ	2, 3
420 0042 10	PUCH	3
420 0042 10	SSANGYONG	3
420 0042 10	VW	3





0...

0000500225	MERCEDES-BENZ	420 0042 10
00A109309	VW	420 0042 10

1...

1040501025	MERCEDES-BENZ	420 0042 10
1040501225	MERCEDES-BENZ	420 0042 10
1110500025	MERCEDES-BENZ	420 0042 10
1190500325	MERCEDES-BENZ	420 0042 10
1190500825	MERCEDES-BENZ	420 0042 10

A...

A0000500225	MERCEDES-BENZ	420 0042 10
A1040501025	MERCEDES-BENZ	420 0042 10
A1040501225	MERCEDES-BENZ	420 0042 10
A1110500025	MERCEDES-BENZ	420 0042 10
A1190500325	MERCEDES-BENZ	420 0042 10
A1190500825	MERCEDES-BENZ	420 0042 10





Correspondance des références

INA 	INA 	INA 
---	---	---

F-346515

420 0042 10



Illustrations

