



Commande des soupapes

Décembre 2018








Additif Catalogue



Nouveautés VL



SCHAEFFLER

						QTY	
<b>AUDI</b>							
<b>A3 (8L1)</b>							
1.9 TDI	09.96-07.01	AGR; AHF; ALH; ASV; (66-81kW)				428 0048 30	7
<b>CITROËN</b>							
<b>C4 I (LC_, LA_)</b>							
2.0 HDi	11.04-07.11	RHF (DW10BTED4); RHR (DW10BTED4); (100-103kW)		exhaust side		428 0168 10	7
<b>C4 Picasso (UA_, UD_)</b>							
2.0 HDi 138	10.06-08.13	RHJ (DW10BTED4); RHR (DW10BTED4); (100kW)		exhaust side		428 0168 10	7
<b>C5 (RE_, RC_, RD_, RW_)</b>							
2.0 HDi; 2.0 HDi 140	09.04-	RHF (DW10BTED4); RHR (DW10BTED4); (100-103kW)		exhaust side		428 0168 10	7
<b>C8 (EA_, EB_)</b>							
2.0 HDi	07.06-	RHK (DW10UTED4); (88kW)		exhaust side		428 0168 10	7
2.0 HDi 135	03.06-	RHD (DW10CB); RHD (DW10CTED4); RHR (DW10BTED4); (100kW)		exhaust side , DW10BTED4		428 0168 10	7
<b>JUMPY II / DISPATCH II (VF7)</b>							
2.0 HDi 120; 2.0 HDi 120 4x4; 2.0 HDi 140	01.07-	RHK (DW10UTED4); RHR (DW10BTED4); (88-100kW)		exhaust side		428 0168 10	7
<b>FIAT</b>							
<b>SCUDO (270_, 272_, 270_, 272_, 270_, 272_)</b>							
2.0 D Multijet; 2.0 D Multijet 4x4	01.07-	RHK; RHR; (88-100kW)		exhaust side		428 0168 10	7
<b>SCUDO Camion plate-forme/Châssis (220_)</b>							
2.0 JTD 16V	05.99-12.06	RHK (DW10UTED4); RHM (DW10ATED4); RHW (DW10ATED4); (80kW)		exhaust side , RHK		428 0168 10	7
<b>SCUDO Camionnette (220_)</b>							
2.0 JTD 16V	05.99-12.06	RHK (DW10UTED4); RHM (DW10ATED4); RHW (DW10ATED4); (80kW)		exhaust side , RHK		428 0168 10	7
<b>ULYSSE (179_)</b>							
2.0 D Multijet	05.06-06.11	RHK; RHR; (88-100kW)		exhaust side		428 0168 10	7
<b>FORD</b>							
<b>C-MAX (DM2)</b>							
2.0 TDCi	02.07-09.10	G6DA; G6DB; G6DC; G6DD; G6DE; G6DF; G6DG; IXDA; (81-100kW)		exhaust side		428 0168 10	7
<b>FOCUS II (DA_, FFS, DS, DA_, HCP, DP, DB_, FCH, DH)</b>							
2.0 TDCi	07.04-09.12	G6DA; G6DB; G6DD; G6DE; G6DF; G6DG; IXDA; (81-100kW)		exhaust side		428 0168 10	7
<b>FOCUS II Décapotable</b>							
2.0 TDCi	10.06-09.10	G6DA; G6DB; G6DD; (100kW)		exhaust side		428 0168 10	7
<b>FOCUS C-MAX</b>							
2.0 TDCi	10.03-03.07	G6DA; G6DB; G6DC; G6DD; G6DE; G6DF; G6DG; (98-100kW)		exhaust side		428 0168 10	7
<b>GALAXY (WM)</b>							
2.0 TDCi	05.06-06.15	AZWA; (96kW)		exhaust side		428 0168 10	7
2.0 TDCi	11.07-06.15	KLWA; TYWA; (85kW)		exhaust side , EURO 4		428 0168 10	7
<b>KUGA I</b>							
2.0 TDCi; 2.0 TDCi 4x4	03.08-11.12	G6DG; UKDA; (100kW)		exhaust side		428 0168 10	7
<b>MONDEO IV (BA7, BA7, BA7)</b>							
2.0 TDCi	03.07-01.15	AZBA; KLBA; LPBA; TYBA; (85-96kW)		exhaust side		428 0168 10	7
<b>S-MAX (WS)</b>							
2.0 TDCi	05.06-12.14	AZWA; (96kW)		exhaust side		428 0168 10	7
2.0 TDCi	11.07-12.14	KLWA; TYWA; (85kW)		exhaust side , EURO 4		428 0168 10	7
<b>HYUNDAI</b>							
<b>ACCENT I / EXCEL I (X-3, X-3)</b>							
1.3; 1.3 i 12V; 1.5 i 12V	10.94-01.00	G4EH; G4EK; (44-65kW)		→09.99		428 0053 30	7
1.5	10.94-12.99	G4EK; (63-69kW)				428 0053 30	7
<b>ACCENT II (LC, LC)</b>							
1.3; 1.5; 1.5 LPG	09.99-12.06	G4EA; G4EH; G4EK; (55-69kW)				428 0053 30	7
1.5	01.00-11.05	G4EB; (66kW)		G4EB (SOHC), →01.08.2002		428 0053 30	7
<b>ACCENT III A trois volumes (MC)</b>							
1.5; 1.5 CNG; 1.5 LPG	01.08-11.10	G4EK; (70-71kW)				428 0053 30	7
<b>ELANTRA (XD, XD)</b>							
1.5 VVTi	08.03-05.06	(77kW)				428 0053 30	7
<b>GETZ (TB)</b>							
1.3	09.03-09.05	G4EA; (63kW)		→08.05		428 0053 30	7

						QTY	
<b>HYUNDAI</b>							
<b>GETZ (TB)</b>							
1.3; 1.3 i	09.02-06.09	G4EA; (60-61kW)				428 0053 30	7
<b>LANTRA II (J-2, J-2)</b>							
1.5 12V	12.96-10.00	G4EK; (65kW)		→07.00		428 0053 30	7
<b>S COUPE (SLC)</b>							
1.5; 1.5 i Turbo	04.91-05.96	G4EK; G4EK-TC; (69-85kW)				428 0053 30	7
1.5 i	04.92-05.96	G4EK; (65kW)		04.94→,  →03.95		428 0053 30	7
<b>LANCIA</b>							
<b>PHEDRA (179_)</b>							
2.0 D Multijet; 2.0 JTD	06.06-11.10	RHK (DW10UTED4); RHR (DW10BTED4); (88-100kW)		exhaust side		428 0168 10	7
<b>LAND ROVER</b>							
<b>FREELANDER 2 (L359)</b>							
3.2 4x4	10.06-10.14	B 6324 S; (171kW)		intake side		427 0023 10	1 7
<b>PEUGEOT</b>							
<b>307 (3E, 3A/C, 3H, 3B)</b>							
2.0 HDi 135	10.03-04.09	RHR (DW10BTED4); (100kW)		exhaust side		428 0168 10	7
<b>308 I (4B_, 4A_, 4C_, 4E_, 4H_)</b>							
2.0 HDi	09.07-	RHF (DW10BTED4); RHR (DW10BTED4); (100-103kW)		exhaust side		428 0168 10	7
2.0 HDi	09.07-	RHR (DW10BTED4); (100kW)		exhaust side , DW10BTED4		428 0168 10	7
				exhaust side		428 0168 10	7
<b>407 (6E_, 6C_, 6D_)</b>							
2.0 HDi; 2.0 HDi 135	05.04-12.10	RHF (DW10BTED4); RHR (DW10BTED4); (100-103kW)		exhaust side		428 0168 10	7
<b>508 (8E_, 8D_)</b>							
2.0 HDi	11.10-	RHA (DW10CTED4); RHF (DW10BTED4); RHR (DW10BTED4); (100-103kW)		exhaust side		428 0168 10	7
<b>607 (9D, 9U)</b>							
2.0 HDi	09.05-07.11	RHR (DW10BTED4); (100kW)		exhaust side		428 0168 10	7
<b>807 (E)</b>							
2.0 HDi	02.06-	RHK (DW10UTED4); (88kW)		exhaust side		428 0168 10	7
2.0 HDi	06.06-	RHD (DW10CTED4); RHR (DW10BTED4); (100kW)		exhaust side , DW10BTED4		428 0168 10	7
<b>Expert (VF3A_, VF3U_, VF3X_)</b>							
2.0 HDi 120; 2.0 HDi 120 4x4; 2.0 HDi 140	01.07-	RHK (DW10UTED4); RHR (DW10BTED4); (88-100kW)		exhaust side		428 0168 10	7
<b>EXPERT Tepee (VF3X_)</b>							
2.0 HDi 120; 2.0 HDi 120 4x4; 2.0 HDi 140	01.07-	RHK (DW10UTED4); RHR (DW10BTED4); (88-100kW)		exhaust side		428 0168 10	7
<b>SEAT</b>							
<b>CORDOBA (6K1, 6K2)</b>							
1.9 TDI	08.96-10.02	1Z; AGR; AHU; ALH; (66kW)		ALH, AGR		428 0048 30	7
1.9 TDI	03.97-10.02	AFN; ASK; ASV; (81kW)		ASK, ASV		428 0048 30	7
<b>CORDOBA Vario (6K5)</b>							
1.9 TDI	08.96-12.02	1Z; AGR; AHU; ALH; (66kW)		AGR, ALH		428 0048 30	7
1.9 TDI	07.97-12.02	AFN; ASK; ASV; (81kW)		ASK, ASV		428 0048 30	7
<b>IBIZA II (6K1)</b>							
1.9 TDI	08.96-02.02	1Z; AGR; AHU; ALH; (66kW)		ALH, AGR		428 0048 30	7
1.9 TDI	02.97-02.02	AFN; ASK; ASV; (81kW)		ASK, ASV		428 0048 30	7
<b>LEON (1M1)</b>							
1.9 TDI	11.99-06.06	AGR; AHF; ALH; ASV; (66-81kW)				428 0048 30	7
<b>TOLEDO II (1M2)</b>							
1.9 TDI	10.98-07.04	AGR; AHF; ALH; ASV; (66-81kW)				428 0048 30	7
<b>SKODA</b>							
<b>OCTAVIA (1U5, 1U2)</b>							
1.9 TDI; 1.9 TDI 4x4	09.96-03.10	AGR; AHF; ALH; ASV; (66-81kW)				428 0048 30	7
<b>VOLVO</b>							
<b>C30 (533)</b>							
2.0 D	10.06-12.12	D 4204 T; (100kW)		exhaust side		428 0168 10	7
<b>C70 II Décapotable (542)</b>							
2.0 D	01.08-10.09	D 4204 T; (100kW)		exhaust side		428 0168 10	7
<b>S40 I (644)</b>							
2.0 D	12.02-06.04	D 4204 T; (100kW)		exhaust side		428 0168 10	7



						QTY	
<b>VOLVO</b>							
<b>S40 II (544)</b>							
2.0 CDI; 2.0 D; 2.0 D4	01.04-12.10	D 4204 T; D 4204 T2; (96-100kW)		exhaust side	428 0168 10		7
<b>S60 II (134)</b>							
3.0 T AWD; T6 AWD	04.10-12.15	B 6304 T3; B 6304 T4; B 6304 T5; (224-258kW)		intake side	427 0023 10	1	7
<b>S80 II (124)</b>							
2.0 TDi	02.08-03.11	D 4204 T; (100kW)		exhaust side	428 0168 10		7
3.2; 3.2 AWD; T6 AWD	03.06-12.16	B 6304 T2; B 6304 T4; B 6324 S; B 6324 S5; (168-224kW)		intake side	427 0023 10	1	7
<b>V40 Break (645)</b>							
2.0 D	12.02-06.04	D 4204 T; (100kW)		exhaust side	428 0168 10		7
<b>V50 (545)</b>							
2.0 CDI; 2.0 D	12.03-12.10	D 4204 T; D 4204 T2; (98-100kW)		exhaust side	428 0168 10		7
<b>V60 (155, 157)</b>							
3.0 T AWD; T6; T6 AWD	07.10-12.15	B 6304 T3; B 6304 T4; B 6304 T5; (224-258kW)		intake side	427 0023 10	1	7
<b>V70 III (135)</b>							
2.0 D	10.07-12.15	D 4204 T; (100kW)		exhaust side	428 0168 10		7
3.2; 3.2 AWD; T6 AWD	04.07-12.15	B 6304 T2; B 6304 T4; B 6324 S; B 6324 S5; (175-224kW)		intake side	427 0023 10	1	7
<b>XC60 (156)</b>							
3.2; 3.2 AWD; T6; T6 AWD	05.08-02.17	B 6304 T2; B 6304 T3; B 6304 T4; B 6324 S; B 6324 S5; (168-242kW)		intake side	427 0023 10	1	7
<b>XC70 II (136)</b>							
3.2; 3.2 AWD; T6 AWD	08.07-12.14	B 6304 T2; B 6304 T4; B 6324 S; B 6324 S5; (175-224kW)		intake side	427 0023 10	1	7
<b>XC90 I (275)</b>							
3.2; 3.2 AWD	03.06-09.14	B 6324 S; B 6324 S5; (175-179kW)		intake side	427 0023 10	1	7
<b>VW</b>							
<b>BORA (1J2, 1J6)</b>							
1.9 TDI; 1.9 TDI 4motion	10.98-05.05	AGR; AHF; ALH; ASV; (66-81kW)			428 0048 30		7
<b>CADDY II Camionnette (9K9A)</b>							
1.9 TDI	09.96-01.04	1Z; AHU; ALH; (66kW)		ALH	428 0048 30		7
<b>CADDY II Break (9K9B)</b>							
1.9 TDI	10.96-01.04	AHU; ALE; ALH; (66kW)		ALH	428 0048 30		7
<b>GOLF IV (1J1, 1J5)</b>							
1.9 TDI; 1.9 TDI 4motion	08.97-05.06	AGR; AHF; ALH; ASV; (66-81kW)			428 0048 30		7
<b>NEW BEETLE (9C1, 1C1)</b>							
1.9 TDI	01.98-06.04	ALH; (66kW)			428 0048 30		7
<b>FLIGHT CLASSIC (6V2)</b>							
90 1.9 TDI	09.96-09.01	AGR; AHU; ALE; ALH; (66kW)		ALH, AGR	428 0048 30		7
<b>POLO Variant (6V5)</b>							
1.9 TDI	05.97-09.01	AGR; AHU; ALE; ALH; (66kW)		ALH, AGR	428 0048 30		7



427	0023	10	LAND ROVER	3
427	0023	10	VOLVO	4
428	0048	30	AUDI	2
428	0048	30	SEAT	3
428	0048	30	SKODA	3
428	0048	30	VW	4
428	0053	30	HYUNDAI	2, 3
428	0168	10	CITROËN	2
428	0168	10	FIAT	2
428	0168	10	FORD	2
428	0168	10	LANCIA	3
428	0168	10	PEUGEOT	3
428	0168	10	VOLVO	3, 4



## Références OE



0...		
038109101K	VW	428 0048 30
050109309H	VW	428 0048 30
0801AE	CITROËN	428 0168 10
0801AE	PEUGEOT	428 0168 10
1...		
1231970	FORD	428 0168 10
13230AA110	HYUNDAI	428 0053 30
1495923	FORD	428 0168 10
2...		
2410022012	HYUNDAI	428 0053 30
2461022010	HYUNDAI	428 0053 30
2461022020	HYUNDAI	428 0053 30
2461022600	HYUNDAI	428 0053 30
3...		
30725026	VOLVO	428 0168 10
31251224	VOLVO	427 0023 10
3M5Q6A273BA	FORD	428 0168 10
3M5Q6A273BB	FORD	428 0168 10
9...		
9654973580	FIAT	428 0168 10

427 0023 10



428 0048 30



428 0053 30

428 0168 10

