



# Commande des soupapes

Février 2019

Additif Catalogue



Nouveautés VL

						QTY	
<b>BMW</b>							
<b>1 (F20, F21)</b>							
114 d; 116 d; 118 d; 118 d xDrive; 120 d; 120 d xDrive; 125 d	12.10-	N47 D16 A; N47 D20 C; N47 D20 D; (70-160kW)		09.13→	420 0260 10	16	7
114 d; 116 d; 116 i; 118 i	03.15-	B37 D15 A; B38 B15 A; (70-100kW)			420 0260 10	12	7
118 d; 118 d xDrive; 120 d; 120 d xDrive; 120 i; 125 d; 125 i	05.13-	B47 D20 A; B47 D20 B; B48 B20 A; B48 B20 B; N47 D20 C; (105-165kW)			420 0260 10	16	7
M 140 i; M 140 i xDrive	09.15-	B58 B30 A; (250kW)			420 0260 10	24	7
<b>2 (F22, F87, F23)</b>							
218 d; 220 d; 220 d xDrive; 220 i; 225 d; 230 i	10.12-11.14	B47 D20 A; B47 D20 B; B48 B20 A; B48 B20 B; N47 D20 C; N47 D20 D; (100-185kW)			420 0260 10	16	7
218 i	03.15-	B38 B15 A; (100kW)			420 0260 10	12	7
M 240 i; M 240 i xDrive	09.15-	B58 B30 A; (250kW)			420 0260 10	24	7
<b>2 (F45, F46)</b>							
214 d; 216 d; 216 i; 218 i; 225 xe	11.13-02.18	B37 C15 A; B38 A15 A; (70-165kW)			420 0260 10	12	7
218 d; 218 d xDrive; 220 d; 220 d xDrive; 220 i; 225 i; 225 i xDrive	11.13-02.18	B47 C20 A; B47 C20 B; B47 D20 A; B48 A20 A; B48 A20 B; B48 A20 F; (100-170kW)			420 0260 10	16	7
<b>3 Décapotable (E93)</b>							
320 d	01.08-12.13	N47 D20 C; (120-147kW)		09.13→	420 0260 10	16	7
330 d	01.09-12.13	N57 D30 A; (180kW)		09.13→	420 0260 10	24	7
<b>3 (F31, F34, F30, F80)</b>							
316 d; 318 d; 320 d; 320 d xDrive	04.11-	B47 D20 A; N47 D20 C; (85-120kW)		09.13→, N47 B47	420 0260 10	16	7
318 d; 318 d xDrive; 320 d; 320 d xDrive; 325 d	03.11-03.16	B47 D20 A; N47 D20 C; N47 D20 D; (100-160kW)		09.13→	420 0260 10	16	7
318 d; 318 d xDrive; 320 d; 320 d xDrive; 320 i; 320 i xDrive; 325 d; 330 e; 330 i; 330 i xDrive	09.14-	B47 D20 A; B47 D20 B; B48 B20 A; B48 B20 B; (110-185kW)			420 0260 10	16	7
318 i	01.15-	B38 B15 A; (100kW)			420 0260 10	12	7
330 d; 330 d xDrive; 335 d xDrive	01.12-	N57 D30 A; N57 D30 B; (190-230kW)		09.13→	420 0260 10	24	7
330 d; 330 d xDrive; 335 d xDrive; 340 i; 340 i xDrive	01.14-	B58 B30 A; N57 D30 A; N57 D30 B; (190-265kW)			420 0260 10	24	7
<b>4 (F32, F82, F36, F33, F83)</b>							
418 d; 420 d; 420 d xDrive; 420 i; 420 i xDrive; 425 d; 430 i; 430 i xDrive	07.13-07.15	B47 D20 A; B47 D20 B; B48 B20 A; B48 B20 B; N47 D20 C; N47 D20 D; (100-185kW)			420 0260 10	16	7
418 i	07.15-	B38 B15 A; (100kW)			420 0260 10	12	7
420 d	07.13-03.15	N47 D20 C; (135kW)		09.13→	420 0260 10	16	7
430 d; 430 d xDrive; 435 d xDrive; 440 i; 440 i xDrive	10.13-	B58 B30 A; N57 D30 A; N57 D30 B; (190-265kW)			420 0260 10	24	7
<b>5 (F11, F10)</b>							
518 d; 520 d	01.09-10.16	B47 D20 A; N47 D20 C; (100-120kW)		09.13→, N47 B47	420 0260 10	16	7
518 d; 520 d; 520 d xDrive; 525 d; 525 d xDrive	11.09-10.16	N47 D20 C; N47 D20 D; (105-160kW)		09.13→	420 0260 10	16	7
518 d; 520 d; 520 d xDrive	11.09-10.16	B47 D20 A; N47 D20 C; (110-155kW)			420 0260 10	16	7
530 d; 530 d xDrive; 535 d; 535 d xDrive; M 550 d xDrive	07.10-10.16	N57 D30 A; N57 D30 B; N57 D30 C; (190-280kW)		09.13→	420 0260 10	24	7
M5; M5 Competition; M5 Edition 30	10.10-10.16	S63 B44 B; (412-441kW)			420 0260 10	32	7
<b>5 (G31, G30, F90)</b>							
520 d; 520 d xDrive; 525 d; 530 e iPerformance; 530 i; 530 i xDrive	09.16-	B46 B20 B; B47 D20 A; B47 D20 B; B48 B20 B; (135-185kW)			420 0260 10	16	7
530 d; 530 d xDrive; 540 d xDrive; 540 i; 540 i xDrive; M 550 d xDrive	09.16-	B57 D30 A; B57 D30 B; B57 D30 C; B58 B30 A; (195-294kW)			420 0260 10	24	7
M 550 i xDrive	03.17-	N63 B44 C; (340kW)			420 0260 10	32	7
<b>5 Gran Turismo (F07)</b>							
520 d	04.11-02.17	N47 D20 C; (135kW)		09.13→	420 0260 10	16	7
530 d; 530 d xDrive; 535 d; 535 d xDrive	07.12-02.17	N57 D30 A; N57 D30 B; (190-230kW)		09.13→	420 0260 10	24	7
<b>6 (F13, F06, F12)</b>							
640 d; 640 d xDrive	11.10-	N57 D30 B; (230kW)		09.13→	420 0260 10	24	7
M6	01.12-	S63 B44 B; (412-441kW)			420 0260 10	32	7
<b>7 (F01, F02, F03, F04)</b>							
730 d; 730 d xDrive; 740 d; 740 d xDrive; 750 d xDrive	02.08-12.15	N57 D30 A; N57 D30 B; N57 D30 C; (155-280kW)		09.13→	420 0260 10	24	7
<b>7 (G11, G12)</b>							
725 d, Ld; 730 i, Li; 740 e, Le; 740 e, Le xDrive	09.15-	B47 D20 B; B48 B20 B; (170-240kW)			420 0260 10	16	7



						QTY	
<b>BMW</b>							
<b>7 (G11, G12)</b>							
730 d; 730 d, Ld xDrive; 730 d xDrive; 740 d, Ld xDrive; 740 i, Li; 740 i, Li xDrive; 750 d, Ld xDrive	09.15-	B57 D30 A; B57 D30 B; B57 D30 C; B58 B30 A; (155-294kW)				420 0260 10	24 7
750 i, Li; 750 i, Li xDrive	09.15-	N63 B44 C; (330kW)				420 0260 10	32 7
<b>i8 (I12)</b>							
hybrid	03.14-	B38 K15 A; (170kW)				420 0260 10	16 7
<b>X1 (E84)</b>							
sDrive 16 d; sDrive 18 d; sDrive 20 d; xDrive 18 d; xDrive 20 d; xDrive 23 d; xDrive 25 d	03.09-06.15	N47 D20 C; N47 D20 D; (85-160kW)			09.13→	420 0260 10	16 7
<b>X1 (F48)</b>							
sDrive 16 d; sDrive 18 i	11.14-05.17	B37 C15 A; B38 A15 A; (85-100kW)				420 0260 10	12 7
sDrive 18 d; sDrive 20 d; sDrive 20 i; xDrive 18 d; xDrive 20 d; xDrive 20 i; xDrive 25 d; xDrive 25 i	11.14-	B46 A20 B; B47 C20 A; B47 C20 B; B48 A20 A; B48 A20 B; (100-170kW)				420 0260 10	16 7
<b>X3 (F25)</b>							
sDrive 18 d; xDrive 20 d	09.10-	N47 D20 C; (100-135kW)			09.13→	420 0260 10	16 7
xDrive 30 d; xDrive 35 d	05.11-	N57 D30 A; N57 D30 B; (190-230kW)			09.13→	420 0260 10	24 7
<b>X4 (F26)</b>							
xDrive 20 d	04.14-03.18	B47 D20 A; (120-140kW)				420 0260 10	16 7
xDrive 30 d; xDrive 35 d	04.14-03.18	N57 D30 A; N57 D30 B; (155-230kW)				420 0260 10	24 7
<b>X5 (F15, F85)</b>							
M	12.14-	S63 B44 B; (423kW)				420 0260 10	32 7
M 50 d; xDrive 30 d; xDrive 40 d	07.13-	N57 D30 A; N57 D30 B; N57 D30 C; (204-280kW)				420 0260 10	24 7
sDrive 25 d; xDrive 25 d	11.13-	B47 D20 B; N47 D20 D; (155-170kW)				420 0260 10	16 7
xDrive 30 d	07.13-	N57 D30 A; (190kW)			09.13→	420 0260 10	24 7
<b>X6 (E71, E72)</b>							
M 50 d; xDrive 30 d; xDrive 40 d	07.09-07.14	N57 D30 A; N57 D30 B; N57 D30 C; (155-280kW)			09.13→	420 0260 10	24 7
<b>X6 (F16, F86)</b>							
M	12.14-	S63 B44 B; (423kW)				420 0260 10	32 7
M 50 d; xDrive 30 d; xDrive 40 d	08.14-	N57 D30 A; N57 D30 B; N57 D30 C; (155-280kW)				420 0260 10	24 7
<b>MINI</b>							
<b>MINI (F54, F57, F55, F56, F60)</b>							
Cooper; Cooper ALL4; Cooper D; Cooper SE ALL4; One; One D; One First	09.13-10.17	B36 A15 A; B37 C15 A; B38 A12 A; B38 A15 A; (55-165kW)				420 0260 10	12 7
Cooper D; Cooper D ALL4; Cooper S; Cooper S ALL4; Cooper SD; Cooper SD ALL4; John Cooper Works; John Cooper Works ALL4	09.13-	B46 A20 A; B47 C20 A; B47 C20 B; B48 A20 A; B48 A20 B; B48 A20 F; (110-170kW)				420 0260 10	16 7
<b>TOYOTA</b>							
<b>AURIS (_E18_, _E18_)</b>							
1.6 D4-D	04.15-	1WW; (82kW)				420 0260 10	16 7
<b>AVENSIS T27 (_T27_, _T27_)</b>							
1.6 D4-D; 2.0 D-4D	04.15-	1WW; 2WW; (82-105kW)				420 0260 10	16 7
<b>RAV 4 IV (_A4_)</b>							
2.0 D	10.15-	2WW; (105kW)				420 0260 10	16 7
<b>VERSO (_R2_)</b>							
1.6 D4-D	11.13-	1WW; (82kW)				420 0260 10	16 7





# Liste numérique

--	--	--	--	--	--	--	--	--

420 0260 10	BMW	2, 3
420 0260 10	MINI	3
420 0260 10	TOYOTA	3





1...

11338614951	BMW	420 0260 10
11338679835	BMW	420 0260 10
13750WA011	TOYOTA	420 0260 10
13750WA012	TOYOTA	420 0260 10

8...

8614951	BMW	420 0260 10
8679835	BMW	420 0260 10





# Correspondance des références

INA		INA		INA	
-----	---	-----	---	-----	---

F-46327.22	<b>420 0260 10</b>
F-46327.25.ASEH-AM	<b>420 0260 10</b>
F-46342.01	<b>420 0260 10</b>
F-46342.02	<b>420 0260 10</b>
F-46342.06	<b>420 0260 10</b>



