



Entraînement de la distribution



Février 2019



SCHAEFFLER

					
---	---	---	---	---	---

AUDI**50 (86)**

1.1; 1.3	08.74-07.78	HB; HC; HH; (37-44kW)		530 0717 30	7
----------	-------------	-----------------------	---	-------------	---

80 (81, 85, B2)

1.3	09.78-07.81	FY; FZ; (40-44kW)	 FZ	530 0717 30	7
-----	-------------	-------------------	---	-------------	---

FIAT**BRAVO I / BRAVA (182)**

1.4; 1.4 12 V	10.95-10.01	182 A3.000; 182 A5.000; (55-59kW)	 705.145→	530 0221 31	7
---------------	-------------	-----------------------------------	---	-------------	---

MAREA (185)

1.4 80 12V	09.96-05.02	182 A3.000; (59kW)	 705.145→	530 0221 31	7
------------	-------------	--------------------	---	-------------	---

LADA**GRANTA (2190)**

1.6	10.11-	VAZ-11186; (64kW)		530 0663 30	7
-----	--------	-------------------	---	-------------	---

KALINA (111_)

1.6	06.13-	VAZ-11186; (64kW)		530 0663 30	7
-----	--------	-------------------	---	-------------	---


LANCIA**Y (840_)**

1.4 12V	03.96-09.03	840 A2.000; 840 A4.000; (55-59kW)	 705.145→	530 0221 31	7
---------	-------------	-----------------------------------	---	-------------	---

VW**DERBY (86)**

0.9; 1.1; 1.3	02.77-09.81	HA; HB; HH; (29-44kW)		530 0717 30	7
---------------	-------------	-----------------------	---	-------------	---

DERBY (86C, 80)

1.0; 1.1; 1.3	08.81-12.84	GK; GL; HB; HH; HK; (29-55kW)		530 0717 30	7
---------------	-------------	-------------------------------	---	-------------	---


GOLF I (17)

1.1; 1.3	04.74-07.83	FA; FJ; GF; GG; (37-44kW)		530 0717 30	7
----------	-------------	---------------------------	---	-------------	---

GOLF II (19E, 1G1)

1.0; 1.3	08.83-06.87	GN; HK; MH; (33-40kW)		530 0717 30	7
----------	-------------	-----------------------	---	-------------	---

1.0	08.85-10.91	HZ; (37kW)	 →786022	530 0717 30	7
-----	-------------	------------	--	-------------	---

1.3 Cat	06.86-12.92	2G; MH; NZ; (40kW)	 NZ,  →12.90,  →200 000	530 0717 30	7
---------	-------------	--------------------	--	-------------	---

JETTA I (16)

1.1	08.79-02.84	GG; (37kW)	 GG	530 0717 30	7
-----	-------------	------------	---	-------------	---

1.3	08.79-02.84	GF; (44kW)		530 0717 30	7
-----	-------------	------------	---	-------------	---

JETTA II (19E, 1G2)

1.3	01.84-06.87	HK; MH; (40kW)		530 0717 30	7
-----	-------------	----------------	---	-------------	---

1.3 Cat	06.87-12.91	2G; MH; NZ; (40kW)	 NZ 2G,  →200 000 262 739	530 0717 30	7
---------	-------------	--------------------	--	-------------	---

PASSAT (32)

1.3	05.73-07.80	FY; (40kW)		530 0717 30	7
-----	-------------	------------	---	-------------	---

PASSAT (32B)

1.3	08.80-07.83	FY; (40kW)		530 0717 30	7
-----	-------------	------------	---	-------------	---

PASSAT Variant (33)

1.3	05.73-07.80	FY; (40kW)		530 0717 30	7
-----	-------------	------------	---	-------------	---


PASSAT Variant (33B)




1.3	08.80-07.83	FY; (40kW)		530 0717 30	7
-----	-------------	------------	---	-------------	---

POLO (86)

0.9; 1.1; 1.3	03.75-09.81	HA; HB; HC; HH; (29-44kW)		530 0717 30	7
---------------	-------------	---------------------------	---	-------------	---

POLO I (86C, 80)

0.9; 1.0; 1.1; 1.3	10.81-09.89	GK; GL; HA; HB; HH; HK; MH; (29-55kW)		530 0717 30	7
--------------------	-------------	---------------------------------------	---	-------------	---

1.0	01.85-09.94	AAK; AAU; HZ; (33kW)	 AAU,  →015 867 HZ,  →786 022	530 0717 30	7
-----	-------------	----------------------	---	-------------	---

1.0	08.85-01.92	HZ; (33kW)	 AAK →786 022	530 0717 30	7
-----	-------------	------------	--	-------------	---


VW
POLO I (86C, 80)

1.0 Cat	08.89-09.94	AAK; AAU; ACM; (33kW)	+ AAK AAU, →015 867	530 0717 30	7
1.3; 1.3 Cat	10.89-09.94	3F; (55-57kW)	+ →008 526	530 0717 30	7
1.3 Cat	07.87-08.94	2G; AAV; MH; NZ; (40kW)	+ MH NZ, →200 000 2G, →262 739	530 0717 30	7
1.3 Cat	07.87-09.94	2G; AAV; MH; NZ; (40kW)	+ MH NZ, →200 000 + MH NZ, →200 000 2G, →262 739	530 0717 30	7
1.3 G40	01.87-09.94	PY; (83-85kW)	+ →002 177	530 0717 30	7

POLO II (6NF, 86CF)

1.0	08.92-07.94	AAU; (33kW)	+ →015 867	530 0717 30	7
-----	-------------	-------------	---------------	-------------	---

SANTANA (32B)

1.3	08.81-07.83	FZ; (44kW)	+ optional	530 0717 30	7
-----	-------------	------------	---------------	-------------	---

SCIROCCO (53)

1.1; 1.3	04.74-07.80	FA; GF; (37-44kW)	+	530 0717 30	7
----------	-------------	-------------------	---	-------------	---

SCIROCCO (53B)

1.3	08.80-12.83	GF; (44kW)	+	530 0717 30	7
-----	-------------	------------	---	-------------	---



Liste numérique / Liste numérique










530 0221 31	FIAT	2
530 0221 31	LANCIA	2
530 0663 30	LADA	2
530 0717 30	AUDI	2
530 0717 30	VW	2, 3





Liste des composants / Liste des composants


						DAYCO	 CONTITECH	GATES
530 0663 30	536 0409 10	1	7	113	17,0			KP15670XS
	538 0742 10	1						
	531 0898 10	1						
530 0221 31	536 0173 10	1	7	134	18,0			
	538 0142 10	1						
	531 0254 30	1						



530 0221 31



530 0663 30



530 0717 30

