



Additif Catalogue



Embrayages

Avril 2019

Nouveautés PL



SCHAEFFLER



RENAULT TRUCKS

C-Serie

320P 320PK; 280P 280PK; 250FG P, PK; 320FG P, PK; 280FG P, PK; 250P 250PK DTI8-122HQ; DTI8-122HR; DTI8-122HS; (184-235kW)	01.13-	ZF; ZTO1006/ 6S-1000 FLYHSAE 2; ZF; ZTO 1109/ 9S-1110	340 0086 10		
--	--------	--	-------------	--	--

D-Serie

12 P 210, 240; 16 P 210, 240; 16 KP 210, 240; 14 P 210, 240; 14 KP 210, 240; 13 P 210, 240; 13 KP 210, 240; 10 P 210, 240 DTI5-122HN; DTI5-122HP; (154-177kW)	01.13-	ZF; ZTO1109/ 9S-1110	340 0086 10		
16 KP 250, 280; 13 P 250, 280; 13 KP 250, 280; 26 P 250, 280, 320; 26 KP 250, 280, 320; 25 P 250, 280, 320; 18 P 250, 280, 320; 18 T 280, 320; 12 KP 250, 280; 14 P 250, 280; 14 KP 250, 280; 16 P 250, 280; 12 P 250, 280; 18 KP 250, 280, 320 DTI8-122HQ; DTI8-122HR; DTI8-122HS; (184-235kW)	01.13-	ZF; ZTO1006/ 6S-1000 FLYHSAE 2; ZF; ZTO 1109/ 9S-1110	340 0086 10		

Midium

150.08/B; 150.10/B; 150.12/B; 180.08/B; 180.10/B; 180.12/B 180.12/C; 210.08/B 220.08/B; 210.10/B 220.10/B dCi 4B; dCi 4C; dci 6W; MIDR 04.02.26 B/4; MIDR 06.02.26 W/4; (110-158kW)	01.00-	Eaton; 9 vitesses	340 0086 10		
210.16/C 22.16/D, 220.16/C dci 6W; MIDR 06.02.26 W/4; (154-158kW)	01.00-	dci 6W; Eaton; 8309A; 9 vitesses	340 0086 10		
220.12; 220.15; 220.16; 220.18/D dci 6W; (158kW)	10.01-	Eaton; 8309A; 9 vitesses	340 0086 10		
220.14 dci 6W; (158kW)	10.01-	Eaton; 9 vitesses Eaton; 8309A; 9 vitesses	340 0086 10 340 0086 10		
240.12; 240.13; 240.14; 240.15; 240.16; 240.18; 280.12; 280.13; 280.14; 280.16; 280.18 DXi 7; (177-206kW)	05.06-	ZF; 6S-850 OD; G6 ZF; 6S-1000; G6 ZF; 9S-1110	340 0086 10		
270.12/C; 270.13/C 270.13/D; 270.16/C 270.16/D; 270.18/D dci 6A; (195kW)	10.01-	Eaton; 6406A; G6 Eaton; 8309A; 9 vitesses	340 0086 10		

Premium

Distribution 210.18D, 220.18 dci 6W; MIDR 06.02.26 W/4; (154-158kW)	04.96-	dci 6W; Eaton; 8309A; 9 vitesses	340 0086 10		
Distribution 270.18 dci 6A; (195kW)	08.00-	Eaton; 8309A; 9 vitesses	340 0086 10		

Premium 2

Distribution 240.18 D; Distribution 270.19, 280.26, 310.18, 310.26; Distribution 280.18 D; Lander 270.18, 270.19, 310.19, 310.26 DXi 7; (177-224kW)	10.05-	ZF; 6S-1000; G6 ZF; 9S-1110	340 0086 10		
Lander 340.18, 340.19 DXi 7; (247kW)	10.06-	ZF; 6S-1000	340 0086 10		

VOLVO

FE

FE 240-18, 240-22, 240-26, 260-18, 260-26 D7E240; D7F240; D7F260; (177-191kW)	05.06-	ZF; ZTO 1006 ZF; ZTO 1109	340 0086 10		
--	--------	------------------------------	-------------	--	--

FE II

FE 250-18, 250-26, 280-18, 280-26, 320-18, 320-26 D8K250; D8K280; D8K320; (184-235kW)	05.12-	ZF; ZTO 1006/ 6S-1000 FLYHSAE 2; ZF; ZTO 1109/ 9S-1110	340 0086 10		
--	--------	---	-------------	--	--

FL II

FL 240-12, 240-14, 240-15, 240-16, 240-18, 260-12, 260-14, 260-15, 260-16, 260-18, 280-12, 280-14, 280-15, 280-16, 280-18, 290-12, 290-14, 290-16, 290-18	05.06-	ZF; ZTO 1006 ZF; ZTO 1109	340 0086 10		
---	--------	------------------------------	-------------	--	--



VOLVO



VOLVO

FL II

D7E240; D7E280; D7F240; D7F260; D7F290; (177-213kW)	05.06-				
--	--------	--	--	--	--

FL III

FL 250-12, 250-14, 250-16, 250-18, 280-12, 280-14, 280-16, 280-18 D8K250; D8K280; (184-206kW)	05.13-	ZTO 1006 ZTO 1109	340 0086 10		
---	--------	----------------------	-------------	--	--

IRISBUS



IRISBUS

CROSSWAY

12m 12.8m; 10.6m 12.8m, 12m
(194-243kW)

06.06-

F4AE0682, F4AE0682L, F4AE3882A; ZF; 6S-1200
 F4AE0682; ZF; 6S-1600

340 0086 10





340 0086 10	RENAULT TRUCKS	15
340 0086 10	VOLVO	15, 16
340 0086 10	IRISBUS	18





2...

20812550	VOLVO	340 0086 10
21949595	VOLVO	340 0086 10

5...

50 10 452 514	RENAULT TRUCKS	340 0086 10
50 10 545 831	RENAULT TRUCKS	340 0086 10
50 10 613 151	RENAULT TRUCKS	340 0086 10

7...

74 20 959 262	RENAULT TRUCKS	340 0086 10
74 21 916 049	RENAULT TRUCKS	340 0086 10

8...

85000790	VOLVO	340 0086 10
85006790	VOLVO	340 0086 10



CR