

FAG

Additif Catalogue



Wheel Bearing Kits

Kits de Roulement de Roue

Juillet 2018



SCHAEFFLER

**DAEWOO****LEGANZA (KLAV)**

| | | | | | |
|--|-------------|----------------|--|-------------|----|
| 2.0 16V [01]; 2.2 16V [01] (93-100kW) | 06.97-04.04 | ABS; ④ ④ ④ ④ 5 | | 713 6447 70 | 20 |
|--|-------------|----------------|--|-------------|----|

HONDA**CIVIC IV (EC, ED, EE, EG)**

| | | | | | |
|-----------------------------------|-------------|-----|--|-------------|----|
| 1.6 16V Vtec (EG5) [02] (92kW) | 10.91-11.95 | ABS | | 713 6178 00 | 20 |
|-----------------------------------|-------------|-----|--|-------------|----|

CIVIC V (EG, EH, EJ)

| | | | | | |
|------------------------|-------------|--------|--|-------------|----|
| 1.6 4x4 [01] (92kW) | 01.92-10.95 | ABS; ④ | | 713 6178 00 | 20 |
|------------------------|-------------|--------|--|-------------|----|

| | | | | | |
|---|-------------|-----|--|-------------|----|
| 1.6 16V Vtec (EH9) [01]; 1.6 VTi (EG9) [01] (92-118kW) | 10.91-11.95 | ABS | | 713 6178 00 | 20 |
|---|-------------|-----|--|-------------|----|

CIVIC VI (EJ, EK, EM1, MA, MB, MC)

| | | | | | |
|---|-------------|---|--|-------------|----|
| 1.4 16V (MB8) [03]; 1.4 i (MA8, MB2) [02]; 1.5 16V (MB3) [02]; 1.5 16V (MB9) [03]; 1.5 i Vtec-E (MA9) [02] (55-84kW) | 09.94-02.01 | ④ | | 713 6178 00 | 20 |
|---|-------------|---|--|-------------|----|

| | | | | | |
|---------------------------|-------------|--------|--|-------------|----|
| 1.6 i Vtec [01] (92kW) | 11.95-02.01 | ABS; ④ | | 713 6178 00 | 20 |
|---------------------------|-------------|--------|--|-------------|----|

| | | | | | |
|------------------------------|-------------|-----|--|-------------|----|
| 1.6 16V (MC1) [03] (85kW) | 04.98-02.01 | ABS | | 713 6178 00 | 20 |
|------------------------------|-------------|-----|--|-------------|----|

| | | | | | |
|-------------------------------|-------------|---|--|-------------|----|
| 2.0 i TD (MB7) [02] (63kW) | 01.97-02.01 | ④ | | 713 6178 00 | 20 |
|-------------------------------|-------------|---|--|-------------|----|

| | | | | | |
|--|-------------|--------|--|-------------|----|
| 2.0 TDiC [02]; 2.0 TDiC (MB7) [02] (77kW) | 11.98-10.00 | ABS; ④ | | 713 6178 00 | 20 |
|--|-------------|--------|--|-------------|----|

CONCERTO (HW, HWW)

| | | | | | |
|---|-------------|--|--|-------------|----|
| 1.4 [01]; 1.5 i 16V [01]; 1.5 i 16V [02] (61-66kW) | 08.89-05.95 | | | 713 6178 00 | 20 |
|---|-------------|--|--|-------------|----|

| | | | | | |
|---|-------------|-----|--|-------------|----|
| 1.6 [02]; 1.6 16V [01]; 1.6 i 16V [01] (78-96kW) | 08.89-03.95 | ABS | | 713 6178 00 | 20 |
|---|-------------|-----|--|-------------|----|

CRX III (EH, EG)

| | | | | | |
|-------------------------|-------------|--------|--|-------------|----|
| 1.6 ESi (EH6) (92kW) | 03.92-12.98 | ABS; ④ | | 713 6178 00 | 20 |
|-------------------------|-------------|--------|--|-------------|----|

| | | | | | |
|----------------------------|-------------|-----|--|-------------|----|
| 1.6 i VTi (EG2) (118kW) | 03.92-12.98 | ABS | | 713 6178 00 | 20 |
|----------------------------|-------------|-----|--|-------------|----|

NISSAN**PIXO (UA0)**

| | | | | | |
|--------------------|--------|--|--|-------------|----|
| 1.0 [02] (50kW) | 06.09- | | | 713 6441 00 | 20 |
|--------------------|--------|--|--|-------------|----|

OPEL**AGILA (A) (H00)**

| | | | | | |
|--|-------------|--|--|-------------|----|
| 1.0 (F68) [02]; 1.0 12V (F68) [02]; 1.2 16V (F68) [02]; 1.2 16V Twinport (F68) [02] (43-59kW) | 09.00-12.07 | | | 713 6441 00 | 20 |
|--|-------------|--|--|-------------|----|

ROVER**2000-3500 3/5 portes (SD1)**

| | | | | | |
|--|-------------|--|--|-------------|----|
| 2000 [02]; 2300 [02]; 2400 TD [02]; 2600 [02]; 2600 S [02]; 3500 [02]; 3500 Vitesse [02] (67-142kW) | 06.76-10.86 | | | 713 6178 00 | 20 |
|--|-------------|--|--|-------------|----|

SUZUKI**ALTO (GF)**

| | | | | | |
|-----------------------------|--------|--|--|-------------|----|
| 1.0 (AMF310) [02] (50kW) | 01.09- | | | 713 6441 00 | 20 |
|-----------------------------|--------|--|--|-------------|----|

CELERIO (LF)

| | | | | | |
|-----------------------------|--------|--|--|-------------|----|
| 1.0 (AVK310) [02] (50kW) | 03.14- | | | 713 6441 00 | 20 |
|-----------------------------|--------|--|--|-------------|----|

WAGON R+ Hatchback (MM)

| | | | | | |
|---|--------|--|--|-------------|----|
| 1.3 (RB 413) [02]; 1.3 4WD (RB 413) [02] (56-69kW) | 05.00- | | | 713 6441 00 | 20 |
|---|--------|--|--|-------------|----|



Liste numérique



| | | |
|-------------|--------|----|
| 713 6178 00 | HONDA | 15 |
| 713 6178 00 | ROVER | 15 |
| 713 6441 00 | NISSAN | 15 |
| 713 6441 00 | OPEL | 15 |
| 713 6441 00 | SUZUKI | 15 |
| 713 6447 70 | DAEWOO | 15 |



**FAG****FAG****FAG****FAG****DAEWOO**

| | |
|----------|--------------------|
| 96219448 | 713 6447 70 |
| 96219450 | 713 6447 70 |
| 96219472 | 713 6447 70 |
| 96219474 | 713 6447 70 |

HONDA

| | |
|---------------|--------------------|
| 42200-SK3-E01 | 713 6178 00 |
| 42200-SR3-A02 | 713 6178 00 |
| 42200-SR3-A03 | 713 6178 00 |
| 42200-SR3-A04 | 713 6178 00 |
| 42200-SR3-A05 | 713 6178 00 |
| 42200-SR3-A06 | 713 6178 00 |
| 42200-ST3-E01 | 713 6178 00 |
| 42200-ST3-E02 | 713 6178 00 |

NISSAN

| | |
|-------------|--------------------|
| 40210-4A00G | 713 6441 00 |
|-------------|--------------------|

OPEL

| | |
|-----------|--------------------|
| 47 00 322 | 713 6441 00 |
| 92 03 934 | 713 6441 00 |

ROVER


| | |
|-----------|--------------------|
| RLB100131 | 713 6178 00 |
|-----------|--------------------|


SUZUKI

| | |
|-----------------|--------------------|
| 43440-58J00-000 | 713 6441 00 |
| 43440-68K10 | 713 6441 00 |
| 43440-78A00 | 713 6441 00 |
| 43440-78A00-000 | 713 6441 00 |
| 43440-84F00-000 | 713 6441 00 |
| 43440-M68K00 | 713 6441 00 |
| 43440-M79F00 | 713 6441 00 |

Correspondance des références

| SKF | FAG | SNR | FAG | RUVILLE | FAG |
|------------|--------------------|---------|--------------------|---------|--------------------|
| BAF-4086 A | 713 6447 70 | R153.35 | 713 6441 00 | 5335 | 713 6441 00 |
| VKBA 3571 | 713 6441 00 | R174.16 | 713 6178 00 | 7447 | 713 6178 00 |
| VKBA3782 | 713 6178 00 | R174.43 | 713 6178 00 | 9009 | 713 6447 70 |
| VKBA3789 | 713 6447 70 | | | | |
| VKBA3790 | 713 6447 70 | | | | |

| | | | | |
|------------|--|--|--|--|
| FAG |  | | | |
| | | | | |

| | | | | |
|------------|--|--|--|--|
| FAG |  | | | |
| | | | | |



Illustrations

713 6178 00



713 6441 00



713 6447 70

