



## Catalog Supplement

Katalognachtrag

Additif catalogue

Suplemento de catálogo

Informazione di catalogo supplementare



## Pompes à eau

Juillet 2019

Nouveautés VL - VUL



FAG



SCHAEFFLER

**BMW**

**BMW**

<b>1 (F20, F21)</b>						
118 d; 118 d xDrive; 120 d; 120 d xDrive; 125 d	03.15-	B47 D20 A; B47 D20 B; (110-165kW)	, avec poulie à gorge,	<b>538 0802 10</b>	8	
<b>2 (F22, F23)</b>						
218 d; 220 d; 220 d xDrive; 225 d	03.14-	B47 D20 A; B47 D20 B; (100-165kW)	, avec poulie à gorge,	<b>538 0802 10</b>	8	
<b>3 (F30, F31, F34)</b>						
316 d; 318 d; 318 d xDrive; 320 d; 320 d xDrive; 325 d	04.11-10.18	B47 D20 A; B47 D20 B; N47 D20 C; (85-165kW)	, avec poulie à gorge,	<b>538 0802 10</b>	8	
<b>4 (F32, F33, F36)</b>						
418 d; 420 d; 420 d xDrive; 425 d	03.15-	B47 D20 A; B47 D20 B; (110-165kW)	, avec poulie à gorge,	<b>538 0802 10</b>	8	
<b>5 (F10, F11)</b>						
518 d; 520 d; 520 d xDrive	10.13-02.17	B47 D20 A; (110-155kW)	, avec poulie à gorge,	<b>538 0802 10</b>	8	
<b>5 (G30, G31)</b>						
520 d; 520 d xDrive	09.16-	B47 D20 A; (140kW)	, avec poulie à gorge,	<b>538 0802 10</b>	8	
<b>X3 (F25)</b>						
sDrive 18 d; xDrive 20 d	04.14-08.17	B47 D20 A; (110-140kW)	, avec poulie à gorge,	<b>538 0802 10</b>	8	
<b>X4 (F26)</b>						
xDrive 20 d	04.14-03.18	B47 D20 A; (120-140kW)	, avec poulie à gorge,	<b>538 0802 10</b>	8	
<b>X5 (F15)</b>						
sDrive 25 d; xDrive 25 d	08.15-07.18	B47 D20 B; (170kW)	, avec poulie à gorge,	<b>538 0802 10</b>	8	

**HONDA**

<b>ACCORD VII (CL, CM, CN)</b>						
2.0; 2.0 Tracção integral; 2.4	02.03-05.08	K20A6; K24A; K24A3; (114-140kW)	,	<b>538 0803 10</b>	8	
<b>ACCORD VII (CL, CM)</b>						
2.0; 2.4	04.03-05.08	K20A6; K24A; (114-140kW)	,	<b>538 0803 10</b>	8	
<b>STREAM (RN)</b>						
2.0 16V	05.01-	K20A1; (115kW)	,	<b>538 0803 10</b>	8	

**MAN**

<b>TGE Camionnette (UY_)</b>						
2.0 TDI; 2.0 TDI AWD	02.17-	DAVA; (130kW)		<b>538 0807 10</b>	8	
<b>TGE Camion plate-forme/Châssis (UZ_)</b>						
2.0 TDI; 2.0 TDI AWD	11.16-	DAVA; (130kW)		<b>538 0807 10</b>	8	

**MERCEDES-BENZ**

<b>C-CLASS (C204)</b>						
C 220 CDI; C 250 CDI	06.11-	OM 651.911; (120-150kW)	, VC,	<b>538 0804 10</b>	8	
<b>C-CLASS (S204)</b>						
C 180 CDI; C 200 CDI; C 220 CDI; C 250 CDI; C 250 CDI 4-matic	12.08-08.14	OM 651.911; OM 651.912; OM 651.913; (88-150kW)	, VC,	<b>538 0804 10</b>	8	
<b>C-CLASS (W204)</b>						
C 180 CDI; C 200 CDI; C 220 CDI; C 220 CDI 4-matic; C 250 CDI; C 250 CDI 4-matic	01.07-01.14	OM 646.811; OM 651.911; OM 651.912; OM 651.913; (88-150kW)	, VC,	<b>538 0804 10</b>	8	
<b>CLASSE S (W221)</b>						
S 250 CDI	01.11-12.13	OM 651.961; (150kW)	, VC,	<b>538 0804 10</b>	8	
<b>CLS (C218)</b>						
CLS 220 BlueTEC / d; CLS 250 BlueTEC / d 4-matic; CLS 250 CDI / BlueTEC / d	04.11-	OM 651.924; (120-150kW)	, VC,	<b>538 0804 10</b>	8	
<b>CLS Shooting Brake (X218)</b>						
CLS 220 BlueTEC / d; CLS 250 BlueTEC / d 4-matic; CLS 250 CDI / BlueTEC / d	10.12-	OM 651.924; (120-150kW)	, VC,	<b>538 0804 10</b>	8	
<b>E-CLASS (_207)</b>						
E 220 CDI; E 220 CDI / BlueTEC / d; E 220 CDI / d; E 250 CDI / BlueTEC / d	01.09-	OM 651.911; (120-150kW)	, VC,	<b>538 0804 10</b>	8	
<b>E-CLASS (S212)</b>						
E 200 CDI / BlueTEC; E 220 BlueTEC 4-matic; E 220 CDI / BlueTEC; E 220 CDI; E 250 CDI / BlueTEC; E 250 CDI / BlueTEC 4-matic; E 300 Hybrid / BlueTEC Hybrid	08.09-	OM 651.924; OM 651.925; (100-150kW)	, VC,	<b>538 0804 10</b>	8	
<b>E-CLASS (W212)</b>						
E 200 CDI / BlueTEC; E 220 BlueTEC 4-matic; E 220 CDI; E 220 CDI / BlueTEC; E 250 CDI / Blue-	01.09-	OM 651.924; OM 651.925; (100-150kW)	, VC,	<b>538 0804 10</b>	8	


**MERCEDES-BENZ**

<b>E-CLASS (W212)</b>					
TEC; E 250 CDI / BlueTEC 4-matic; E 300 Hybrid / BlueTEC Hybrid	01.09-	OM 651.924; OM 651.925; (100-150kW)			
<b>GLK-CLASS (X204)</b>					
200 CDI; 220 CDI; 220 CDI 4-matic; 250 CDI 4-matic	12.08-06.15	OM 651.912; OM 651.913; OM 651.916; (100-150kW)		538 0804 10	8
<b>M-CLASS (W166)</b>					
ML 250 CDI / BlueTEC 4-matic	06.11-12.15	OM 651.960; (150kW)		538 0804 10	8
<b>SLK (R172)</b>					
250 CDI / d	01.12-	OM 651.980; (150kW)		538 0804 10	8
<b>V-CLASS (W447)</b>					
V 200 CDI / d; V 200 CDI / d 4-matic; V 220 CDI / d; V 220 CDI / d 4-matic; V 250 BlueTEC / d; V 250 BlueTEC / d 4-matic	03.14-	OM 651.950; (100-140kW)		538 0804 10	8
<b>VITO (W447)</b>					
114 CDI / 114 BlueTEC; 114 CDI / 114 BlueTEC 4-matic; 114 CDI; 114 CDI 4-matic; 114 CDI 4x4; 116 CDI / 116 BlueTEC; 116 CDI / 116 BlueTEC 4-matic; 116 CDI; 116 CDI 4-matic; 116 CDI 4x4; 119 BlueTEC; 119 BlueTEC 4-matic; 119 CDI / 119 BlueTEC; 119 CDI / 119 BlueTEC 4-matic; 119 CDI / BlueTEC; 119 CDI / BlueTEC 4x4	10.14-	OM 651.950; (100-140kW)		538 0804 10	8

**SEAT**

<b>IBIZA IV (6J5, 6P1)</b>					
1.0; 1.0 TSI	05.15-	CHYB; CHZB; CHZC; (55-81kW)		538 0746 10	8
<b>IBIZA IV SPORTCOUPE (6J1, 6P5)</b>					
1.0; 1.0 TSI	05.15-	CHYB; CHZB; CHZC; (55-81kW)		538 0746 10	8
<b>IBIZA IV ST (6J8, 6P8)</b>					
1.0; 1.0 TSI	05.15-	CHYB; CHZB; CHZC; (55-81kW)		538 0746 10	8
<b>IBIZA V (KJ1)</b>					
1.0	01.17-	CHYB; (55kW)		538 0746 10	8
<b>Mii (KF1)</b>					
1.0; 1.0 EcoFuel	10.11-	CHYA; CHYB; CPGA; DAFA; (44-55kW)		538 0746 10	8

**SKODA**













<b>CITIGO</b>					
1.0; 1.0 CNG	10.11-	CHYA; CHYB; CPGA; (44-55kW)		538 0746 10	8
<b>FABIA (NJ3, NJ5)</b>					
1.0	08.14-	CHYA; CHYB; (44-55kW)		538 0746 10	8

**VOLVO**



















































<b>S60 II (134)</b>					
2.0 D2; 2.0 D3; 2.0 D4; 2.0 D5; D4	09.13-12.15	D 4204 T11; D 4204 T14; D 4204 T20; D 4204 T4; D 4204 T5; D 4204 T8; D 4204 T9; (88-165kW)	19	538 0808 10	8
<b>S80 II (AS)</b>					
D4	09.13-	D 4204 T5; (133kW)	19	538 0808 10	8
<b>S90 II (234)</b>					
2.0 D3; 2.0 D4; 2.0 D4 AWD; 2.0 D5 AWD; 2.0 T5; 2.0 T6 AWD	03.16-	B 4204 T23; B 4204 T27; D 4204 T14; D 4204 T16; D 4204 T23; D 4204 T9; (110-235kW)	19	538 0808 10	8
<b>V40 (VW)</b>					
D2; D3; D4	05.14-	D 4204 T13; D 4204 T14; D 4204 T16; D 4204 T8; D 4204 T9; (88-140kW)	19	538 0808 10	8
<b>V60</b>					
2.0 D2; 2.0 D3; 2.0 D4; D4; D5	10.13-12.15	D 4204 T11; D 4204 T14; D 4204 T20; D 4204 T4; D 4204 T5; D 4204 T8; D 4204 T9; (88-165kW)	19	538 0808 10	8
<b>V70 III</b>					
D2; D3; D4	10.13-	D 4204 T20; D 4204 T5; D 4204 T9; (88-133kW)	19	538 0808 10	8
<b>V90 II</b>					
2.0 D3; 2.0 D3 AWD; 2.0 D4; 2.0 D4 AWD; 2.0 D5 AWD; 2.0 Hybrid AWD; 2.0 T5; 2.0 T6 AWD	03.16-	B 4204 T23; B 4204 T27; B 4204 T35; D 4204 T14; D 4204 T16; D 4204 T23; D 4204 T4; D 4204 T9; (110-235kW)	19	538 0808 10	8

					
---	---	---	---	---	---

**VOLVO**

<b>XC60 I</b>					
D3; D4	10.13-02.17	D 4204 T14; D 4204 T4; D 4204 T5; (110-140kW)	   19	538 0808 10	8
<b>XC60 II (246)</b>					
2.0 D4 AWD; 2.0 D5 AWD; 2.0 T8 Hybrid AWD	03.17-	B 4204 T35; D 4204 T14; D 4204 T23; (140-235kW)	   19	538 0808 10	8
<b>XC70 II (136)</b>					
D4	10.13-	D 4204 T5; (133kW)	   19	538 0808 10	8
<b>XC90 II (256)</b>					
2.0 T5 AWD; D4; D4 AWD; D5 AWD; T5 AWD; T6 AWD	09.14-	B 4204 T23; B 4204 T27; D 4204 T11; D 4204 T14; D 4204 T23; D 4204 T6; (140-235kW)	   19	538 0808 10	8

**VW**

<b>CRAFTER (SY, SZ)</b>					
2.0 TDI; 2.0 TDI 4motion	09.16-	DAVA; (130kW)	 	538 0807 10	8
<b>LOAD UP (121, 122, BL1, BL2)</b>					
1.0; 1.0 EcoFuel	12.14-	CHYA; CPGA; DAFA; (44-50kW)		538 0746 10	8
<b>MULTIVAN VI (SGF, SGM, SGN)</b>					
2.0 TDI	04.15-	CAAB; CXGB; (75kW)	    CXGB,  11.16→	538 0807 10	8
2.0 TDI; 2.0 TDI 4motion	04.15-	CXFA; CXHA; CXHB; (84-110kW)	   11.16→	538 0807 10	8
2.0 TDI	04.15-	CXGA; (62kW)	   CXGA,  11.16→	538 0807 10	8
2.0 TDI; 2.0 TDI 4motion	06.15-	CXEB; (150kW)	   05.17→	538 0807 10	8
<b>POLO VIII (6R_)</b>					
1.0	01.14-	CHYA; CHYB; (44-55kW)		538 0746 10	8
<b>TRANSPORTER T6 (SFD, SFE, SFL, SFZ)</b>					
2.0 TDI	04.15-	CAAB; CXGB; (75kW)	   CXGB,  11.16→	538 0807 10	8
2.0 TDI	04.15-06.16	CAAA; CXGA; (62kW)	   CXGA	538 0807 10	8
2.0 TDI; 2.0 TDI 4motion	08.15-	CXFA; CXHA; CXHB; (84-110kW)	   11.16→	538 0807 10	8
2.0 TDI; 2.0 TDI 4motion	05.16-	CXEB; (150kW)	   05.17→	538 0807 10	8
<b>TRANSPORTER T6 (SGA, SGB, SGG, SGH, SGJ)</b>					
2.0 TDI	04.15-	CAAB; CXGB; (75kW)	   CXGB,  11.16→	538 0807 10	8
2.0 TDI; 2.0 TDI 4motion	04.15-	CXFA; CXHA; CXHB; (84-110kW)	   11.16→	538 0807 10	8
2.0 TDI	04.15-	CAAA; CXGA; (62kW)	   CXGA,  11.16→	538 0807 10	8
2.0 TDI	04.15-06.16	CAAA; CXGA; (62kW)	   CXGA	538 0807 10	8
2.0 TDI; 2.0 TDI 4motion	06.15-	CXEB; (150kW)	   05.17→	538 0807 10	8
<b>UP (121, 122, BL1, BL2)</b>					
1.0; 1.0 EcoFuel	08.11-	CHYA; CHYB; CPGA; DAFA; (44-55kW)		538 0746 10	8



538 0746 10	SEAT	3
538 0746 10	SKODA	3
538 0746 10	VW	4
538 0802 10	BMW	2
538 0803 10	HONDA	2
538 0804 10	MERCEDES-BENZ	2, 3
538 0807 10	MAN	2
538 0807 10	VW	4
538 0808 10	VOLVO	3, 4





**Références OE / Références OE**

**0...**

04C121004E	SEAT	<b>538 0746 10</b>
04C121004E	SKODA	<b>538 0746 10</b>
04C121004E	VW	<b>538 0746 10</b>
04C121004F	SEAT	<b>538 0746 10</b>
04C121004F	SKODA	<b>538 0746 10</b>
04C121004F	VW	<b>538 0746 10</b>
04C121004J	SEAT	<b>538 0746 10</b>
04C121004J	SKODA	<b>538 0746 10</b>
04C121004J	VW	<b>538 0746 10</b>
04C121600J	SEAT	<b>538 0746 10</b>
04C121600J	SKODA	<b>538 0746 10</b>
04C121600J	VW	<b>538 0746 10</b>
04C121600L	SEAT	<b>538 0746 10</b>
04C121600L	SKODA	<b>538 0746 10</b>
04C121600L	VW	<b>538 0746 10</b>
04L121011H	VW	<b>538 0807 10</b>
04L121011HX	VW	<b>538 0807 10</b>
04L121011M	VW	<b>538 0807 10</b>

**1...**

11518591016	BMW	<b>538 0802 10</b>
19200RAAA01	HONDA	<b>538 0803 10</b>
19200RAD003	HONDA	<b>538 0803 10</b>
19200RBB003	HONDA	<b>538 0803 10</b>
19200RBB013	HONDA	<b>538 0803 10</b>
19200RFE003	HONDA	<b>538 0803 10</b>

**3...**




31368179	VOLVO	<b>538 0808 10</b>
----------	-------	--------------------

**A...**

A6512000300	MERCEDES-BENZ	<b>538 0804 10</b>
A6512001901	MERCEDES-BENZ	<b>538 0804 10</b>
A6512007701	MERCEDES-BENZ	<b>538 0804 10</b>




Correspondance des références / Correspondance des références

RUVILLE 	RUVILLE 	RUVILLE 
67405 538 0803 10		




Illustrations / Illustrations


538 0746 10




538 0802 10




538 0803 10



538 0804 10



538 0807 10



538 0808 10

