



Commande des soupapes

Octobre 2018

Additif Catalogue



Nouveautés VL

SCHAEFFLER
AUTOMOTIVE AFTERMARKET




						QTY	
DAEWOO							
LANOS (KLAT, KLAT)							
1.3; 1.5	05.97-	A13SMS; A14SMS; A15SMS; (55-63kW)			422 0039 10	8	7
NEXIA							
1.5	02.95-08.97	G15MF; (44-55kW)			422 0039 10	8	7
OPEL							
ASCONA B (81_, 86_, 87_, 88_)							
1.3 N; 1.3 S	03.79-08.81	13 N; 13 S; (44-55kW)			422 0039 10	8	7
ASCONA C (J82)							
1.3 N; 1.3 S; 1.6; 1.6 D; 1.6 i; 1.6 i Cat; 1.6 S; 1.8; 1.8 E; 1.8 i; 2.0 i; 2.0 i Cat; 2.0 i GT	09.81-08.88	13 N; 13 S; 16 D; 16 DA; 16 N; 16 SH; 16 SV; 18 E; 20 NE; 20 SEH; C 16 LZ; C 16 NZ; C 18 NE; C 20 NE; E 16 LZ; E 16 NZ; E 18 NV; S 18 NV; (40-95kW)			422 0039 10	8	7
ASCONA C 3/5 portes (J82)							
1.3 N; 1.3 S; 1.6; 1.6 D; 1.6 i; 1.6 i Cat; 1.6 S; 1.8; 1.8 E; 1.8 i; 2.0 i; 2.0 i Cat; 2.0 i GT	09.81-08.88	13 N; 13 S; 16 D; 16 DA; 16 N; 16 SH; 16 SV; 18 E; 20 NE; 20 SEH; C 16 LZ; C 16 NZ; C 18 NE; C 20 NE; E 16 NZ; E 18 NV; S 18 NV; (40-95kW)			422 0039 10	8	7
ASTRA F (T92, T92, T92, T92, T92, T92, T92, T92)							
1.4; 1.4 i; 1.4 Si; 1.6; 1.6 i; 1.6 Si; 1.7 D; 1.7 TD; 1.8 i; 2.0 i	09.91-01.05	14 NV; 14 SE; 16 LZ2; 16 NZR; 17 D; 17 DR; C 14 NZ; C 14 SE; C 16 NZ; C 16 SE; C 18 NZ; C 20 NE; X 14 NZ; X 16 SZ; X 16 SZR; X 17 DTL; (42-85kW)			422 0039 10	8	7
ASTRA G (T98, T98, T98, F70, T98, T98)							
1.6; 1.7 TD	02.98-04.05	X 16 SZR; X 17 DTL; Z 16 SE; (50-62kW)			422 0039 10	8	7
1.8 16V	06.00-10.05	Z 18 XE; (92kW)			428 0052 30		7
ASTRA H (A04, A04, A04, A04)							
1.8	01.04-10.10	Z 18 XE; (92kW)			428 0052 30		7
CALIBRA A (C89)							
2.0 i; 2.0 i 4x4	08.89-07.97	C 20 NE; (85kW)			422 0039 10	8	7
COMBO (71_)							
1.2; 1.4	07.94-10.01	C 12 NZ; C 14 NZ; C 14 SE; X 12 SZ; X 14 SZ; (33-60kW)			422 0039 10	8	7
COMBO C							
1.6	10.01-	Z 16 SE; (64kW)			422 0039 10	8	7
CORSA A (S83, S83, S83)							
1.2; 1.2 N	09.82-08.90	12 NC; E 12 GV; (33kW)			422 0039 10	8	7
1.2; 1.2 i; 1.2 S; 1.3; 1.3 i; 1.3 S; 1.4 i; 1.4 S; 1.4 Si; 1.6 GSI; 1.6 GSI Cat	09.82-03.93	12 S; 12 ST; 13 NB; 13 SB; 14 NV; C 12 NZ; C 13 N; C 14 NZ; C 14 SE; C 16 NZ; C 16 SE; E 16 SE; (33-74kW)			422 0039 10	8	7
CORSA B (S93, S93)							
1.2 i; 1.4 i; 1.4 Si	03.93-09.00	12 NZ; C 14 NZ; C 14 SE; X 14 SZ; (33-60kW)			422 0039 10	8	7
CORSA C (X01)							
1.8	09.00-12.09	Z 18 XE; (92kW)			428 0052 30		7
FRONTERA A Sport (U92)							
2.0 i	03.92-10.98	C 20 NE; X 20 SE; (85kW)			422 0039 10	8	7
KADETT D (31_-34_, 41_-44_)							
1.2; 1.3 N; 1.3 S; 1.6 D; 1.6 S; 1.8 GT/E	08.79-08.84	12 N; 12 ST; 13 N; 13 S; 16 D; 16 SH; 18 E; (39-85kW)			422 0039 10	8	7
KADETT D (32_,37_,39_, 42)							
1.3 S	08.79-08.84	13 S; (55kW)			422 0039 10	8	7
KADETT D Break (35_, 36_, 45_, 46_)							
1.2; 1.3 N; 1.3 S; 1.6 D; 1.6 S	08.79-08.84	12 N; 13 N; 13 S; 16 D; 16 SH; (39-66kW)			422 0039 10	8	7
KADETT E (T85, T85, T85, T85, T85, T85)							
1.2; 1.3 i Cat; 1.3 N; 1.3 S; 1.4 i; 1.4 S; 1.6; 1.6 D; 1.6 i; 1.6 i Cat; 1.6 S; 1.7 D; 1.8 E; 1.8 GSI; 1.8 i; 1.8 S; 2.0 GSI; 2.0 GSI Cat; 2.0 i; 2.0 i Cat	08.84-07.94	12 SC; 13 N; 13 NB; 13 S; 14 NV; 16 D; 16 DA; 16 SH; 16 SV; 17 D; 17 DR; 18 E; 18 SE; 18 SV; 20 NE; 20 SE; 20 SEH; 20 SER; C 13 N; C 14 NZ; C 14 SE; C 16 LZ; C 16 NZ; C 18 NE; C 18 NT; C 18 NZ; C 20 NE; E 16 NZ; E 18 NV; S 18 NV; (40-95kW)			422 0039 10	8	7
MANTA B (58_, 59_)							
1.3 S; 1.8 S	08.81-08.87	13 S; 18 S; (55-66kW)			422 0039 10	8	7
MANTA B CC (53_, 55_)							
1.3 S; 1.8 S	08.79-08.87	13 S; 18 S; (55-66kW)			422 0039 10	8	7



						QTY	
OPEL							
MERIVA A Monospace (X03)							
1.6	05.03-05.10	Z 16 SE; (64kW)			422 0039 10	8	7
1.8	05.03-05.10	Z 18 XE; (92kW)			428 0052 30		7
OMEGA A (V87, V87)							
1.8; 1.8 N; 1.8 S; 2.0; 2.0 i	09.86-04.94	18 NV; 18 SEH; 18 SV; 20 SE; C 20 NE; E 18 NVR; (60-90kW)			422 0039 10	8	7
OMEGA B (V94, V94)							
2.0	03.94-12.00	20 SE; X 20 SE; (85kW)			422 0039 10	8	7
REKORD E (17_, 19_, 11_, 14_, 16_)							
1.8; 1.8 S	11.82-08.86	18 N; 18 S; (55-66kW)			422 0039 10	8	7
REKORD E Break (61_, 66_, 67_)							
1.8; 1.8 S	11.82-08.86	18 N; 18 S; (55-66kW)			422 0039 10	8	7
SIGNUM 3/5 portes (Z03)							
1.8	05.03-07.05	Z 18 XE; (90kW)			428 0052 30		7
TIGRA TwinTop (X04)							
1.8	06.04-12.10	Z 18 XE; (92kW)			428 0052 30		7
VECTRA A (J89, J89)							
1.4 S; 1.6; 1.6 i; 1.6 S; 1.7 D; 1.8 i; 1.8 i Cat; 1.8 S; 1.8 S 4x4; 2.0 i; 2.0 i 4x4; 2.0 i Cat; 2.0 i Cat 4x4; 2.0 i GT	04.88-11.95	14 NV; 16 SV; 17 D; 17 DR; 18 SV; 20 NE; 20 SEH; C 16 NZ; C 16 NZ2; C 18 NZ; C 20 NE; E 16 NZ; E 18 NVR; X 16 SZ; (42-95kW)			422 0039 10	8	7
1.6 i Cat	09.88-11.95	C 16 NZ; C 16 NZ2; (55kW)			C16NZ 422 0039 10	8	7
VECTRA B (J96, J96, J96)							
1.6 i	10.95-07.03	X 16 SZR; (55kW)			422 0039 10	8	7
1.8 i 16V	09.00-07.03	Z 18 XE; (92kW)			428 0052 30		7
VECTRA C (Z02, Z02, Z02)							
1.8; 1.8 16V	04.02-09.08	Z 18 XE; Z 18 XEL; (81-90kW)			428 0052 30		7
ZAFIRA A Monospace (T98)							
1.8 16V	09.00-06.05	Z 18 XE; (92kW)			428 0052 30		7
SAAB							
9-3 (YS3F, YS3F)							
1.8 i	01.04-02.15	Z 18 XE; (90kW)			428 0052 30		7
9-3 Break (YS3F)							
1.8 i	03.05-02.15	Z 18 XE; (90kW)			428 0052 30		7




Liste numérique



422 0039 10	DAEWOO	2
422 0039 10	OPEL	2, 3
428 0052 30	OPEL	2, 3
428 0052 30	SAAB	3




5...

5636970	OPEL	428 0052 30
5636970	VAUXHALL	428 0052 30

6...

636039	OPEL	428 0052 30
636039	VAUXHALL	428 0052 30
636040	OPEL	428 0052 30
636040	VAUXHALL	428 0052 30
640020	OPEL	428 0052 30
640020	VAUXHALL	428 0052 30
640579	OPEL	422 0039 10
640580	OPEL	422 0039 10
640581	OPEL	422 0039 10
640582	OPEL	422 0039 10
640587	OPEL	422 0039 10
640588	OPEL	422 0039 10

9...

90128143	OPEL	422 0039 10
90128143	VAUXHALL	422 0039 10
90234847	OPEL	422 0039 10
90271222	OPEL	422 0039 10
90271222	VAUXHALL	422 0039 10
90298390	OPEL	428 0052 30
90298390	VAUXHALL	428 0052 30
90323514	OPEL	422 0039 10
90323514	VAUXHALL	422 0039 10
90398840	OPEL	422 0039 10
90409632	OPEL	422 0039 10
90502282	OPEL	422 0039 10
90502282	VAUXHALL	422 0039 10
90512282	OPEL	422 0039 10
9158623	OPEL	428 0052 30
9158623	VAUXHALL	428 0052 30
9158629	OPEL	428 0052 30
9158629	VAUXHALL	428 0052 30
93174076	OPEL	428 0052 30
93174076	VAUXHALL	428 0052 30



422 0039 10



428 0052 30

