



Additif Catalogue



Entraînement de la distribution

Septembre 2019

Nouveautés VL



SCHAEFFLER

BMW			
1 (F20, F21)			
114 i; 116 i; 118 i 07.11-06.19 B38 B15 A; N13 B16 A; (75-125kW)			
	WP	532 0912 10	13
3 (F30, F31, F34)			
316 i; 320 i; 320 i xDrive 11.12-06.19 B48 B20 A; N13 B16 A; N20 B20 B; (100-135kW)			
	WP	532 0912 10	13
CITROËN			
BERLINGO			
1.6 VTi 120; 1.6 VTi 95 11.09- 5FK (EP6CB); 5FS (EP6C); (72-88kW)			
	WP	532 0912 10	13
C3			
1.4 LPG; 1.4 VTi; 1.4 VTi 95; 1.6 VTi 120 11.09- 5FS (EP6C); 8FN (EP3); 8FP (EP3); 8FR (EP3); (70-88kW)			
	WP	532 0912 10	13
C3 Picasso			
1.4 VTi 95; 1.4 VTi 95 LPG; 1.6 VTi; 1.6 VTi 120 02.09- 5FP (EP6); 5FS (EP6C); 5FW (EP6); 8FN (EP3); 8FP (EP3); 8FS (EP3); (70-88kW)			
	WP	532 0912 10	13
C4 I (LC_) / (LA_)			
1.6 THP; 1.6 THP 140; 1.6 THP 150; 1.6 VTi 120 06.08-07.11 5FT (EP6DT); 5FW (EP6); 5FX (EP6DT); (88-110kW)			
	WP	532 0912 10	13
C4 II (B7)			
1.4 VTi 95; 1.6 THP 155; 1.6 VTi 120; 1.6 VTi 120 LPG 11.09-12.16 5FS (EP6C); 5FV (EP6CDT); 8FP (EP3); (70-115kW)			
	WP	532 0912 10	13
C4 Picasso			
1.6 16V; 1.6 THP 140; 1.6 THP 155; 1.6 VTi 120 07.08-08.13 5FT (EP6DT); 5FV (EP6CDT); 5FW (EP6); 5FX (EP6DT); (88-115kW)			
	WP	532 0912 10	13
C4 Picasso II			
1.6 THP 150; 1.6 THP 155; 1.6 THP 165; 1.6 VTi 120 02.13- 5FS (EP6C); 5FV (EP6CDT); 5FX (EP6DT); 5GZ (EP6FDT); (88-121kW)			
	WP	532 0912 10	13
C4 SPACETOURER (3D_)			
1.6 THP 165 04.18- 5GZ (EP6FDT); (121kW)			
	WP	532 0912 10	13
C5			
1.6 THP 150; 1.6 THP 155; 1.6 VTi 120; 1.6 VTi 120 04.09- 5FN (EP6CDT); 5FS (EP6C); 5FV (EP6CDT); (88-115kW)			
	WP	532 0912 10	13
C5 AIRCROSS			
1.6 PureTech 180 11.18- 5GF (EP6FADTXD); (133kW)			
	WP	532 0912 10	13
DS3			
1.4 VTi 95; 1.4 VTi 95 LPG; 1.4 VTi 98; 1.6 Racing; 1.6 THP 150; 1.6 THP 155; 1.6 THP 165; 1.6 VTi 120 11.09-07.15 5FD (EP6DTS); 5FF (EP6DTS); 5FM (EP6DT); 5FN (EP6CDT); 5FR (EP6DT); 5FS (EP6C); 5FV (EP6CDT); 5FX (EP6DT); 5GZ (EP6FDT); 8FN (EP3); 8FP (EP3); 8FR (EP3); (70-152kW)			
	WP	532 0912 10	13

CITROËN			
DS4			
1.6 THP 155; 1.6 THP 160; 1.6 THP 200; 1.6 VTi 120 04.11-07.15 5FM (EP6DT); 5FS (EP6C); 5FU (EP6DXT); 5FV (EP6CDT); (88-147kW)			
	WP	532 0912 10	13
DS5			
1.6 THP 155; 1.6 THP 165 Hybrid; 1.6 THP 200 11.11-07.15 5FU (EP6DXT); 5FV (EP6CDT); 5GZ (EP6FDT); (115-147kW)			
	WP	532 0912 10	13
GRAND C4 SPACETOURER (3A_, 3E_)			
1.6 PureTech 180; 1.6 THP 165 04.18- 5GF (EP6FADTXD); 5GZ (EP6FDT); (121-133kW)			
	WP	532 0912 10	13
DS			
DS 3 / DS 3 Décapotable			
1.6 THP; 1.6 THP 165; 1.6 THP 208 07.15- 5GR (EP6DXT); 5GZ (EP6FDT); (120-153kW)			
	WP	532 0912 10	13
DS 4 / DS 4 CROSSBACK / DS 5			
1.6 THP 165; 1.6 THP 210 04.15- 5GM (EP6DXT); 5GZ (EP6FDT); (121-155kW)			
	WP	532 0912 10	13
DS 7 Crossback			
1.6 PureTech 180; 1.6 PureTech 225 09.17- 5GC (EP6FADTX); 5GF (EP6FADTXD); (133-165kW)			
	WP	532 0912 10	13
FORD			
MONDEO I (GBP, BNP)			
1.6 i 16V; 1.8 i 16V; 1.8 i 16V 4x4; 2.0 i 16V; 2.0 i 16V 4x4 01.93-08.96 L1F; L1J; NGA; RKA; RKB; (65-100kW)			
		530 0102 30	
1.8 i 16V 4x4 04.93-08.96 RKA; (85kW)			
		530 0102 30	
2.0 i 16V 4x4 04.93-08.96 NGA; (100kW)			
		530 0102 30	
		530 0102 30	
MONDEO II (BAP, BFP, BNP)			
1.6 i; 1.8 i; 2.0 i 08.96-09.00 L1J; NGA; NGB; NGC; NGD; RKB; RKF; RKH; RKJ; RKK; (66-96kW)			
		530 0102 30	
		530 0102 30	
JAGUAR			
XF (X250) / XF SPORTBRAKE (X250)			
3.0 D 03.09-04.15 306DT; AJV6D; (177-202kW)			
	NW, INJP	530 0731 10	13
XJ (X351)			
3.0 SDV6 10.09-12.15 AJV6D; (202kW)			
	NW, INJP	530 0731 10	13
LAND ROVER			
DISCOVERY III (TAA)			
2.7 TD 4x4 07.04-09.09 276DT; (140kW)			
	NW, INJP, EURO 4	530 0734 10	13



MINI



LAND ROVER

DISCOVERY IV (LA)

2.7 TD 4x4
 09.09-
 276DT; (140kW)
 NW, INJP | 530 0734 10 | 13

3.0 SDV6 4x4; 3.0 TD 4x4
 09.09-
 306DT; (155-188kW)
 NW, INJP | 530 0731 10 | 13

RANGE ROVER IV (LG)

3.0 SDV6 4x4; 3.0 TDV6 4x4
 08.12-
 306DT; (183-190kW)
 NW, INJP | 530 0731 10 | 13

RANGE ROVER SPORT (L320, L494)

2.7 D 4x4
 02.05-03.13
 276DT; (140kW)
 NW, INJP, →09.09, EURO 4 | 530 0734 10 | 13

3.0 D 4x4; 3.0 SDV6 4x4; 3.0 TDV6 4x4
 09.09-03.13
 306DT; 30DDTX; (155-215kW)
 NW, INJP | 530 0731 10 | 13

MINI

MINI (R55, R56, R57)

Cooper; Cooper S; Cooper S John Cooper Works; John Cooper Works; John Cooper Works GP; One
 09.06-06.15
 N12 B14 A; N12 B16 A; N14 B16 A; N14 B16 AB; N14 B16 C; N16 B16 A; N18 B16 A; N18 B16 C; (55-160kW)
 WP | 532 0912 10 | 13

MINI (R58, R59)

Cooper; Cooper S; Cooper S JCW; John Cooper Works
 12.10-05.15
 N14 B16 A; N14 B16 C; N16 B16 A; N18 B16 A; N18 B16 C; (85-155kW)
 WP | 532 0912 10 | 13

MINI (R60, R61)

Cooper; Cooper ALL4; Cooper S; Cooper S ALL4; John Cooper Works
 03.12-09.16
 N16 B16 A; N18 B16 A; N18 B16 C; (88-160kW)
 WP | 532 0912 10 | 13

OPEL

ANTARA (L07)

2.0 CDTi; 2.0 CDTi 4x4
 01.16-
 B 20 DTH; (125kW)
 gauche supérieur | 532 0885 10 | 13

CASCADA (W13)

2.0 CDTi
 07.15-
 B 20 DTH; (125kW)
 gauche supérieur | 532 0885 10 | 13

INSIGNIA A (G09)

2.0 CDTi; 2.0 CDTi 4x4
 11.14-03.17
 B 20 DTH; (125kW)
 gauche supérieur | 532 0885 10 | 13

INSIGNIA A Country Tourer (G09)

2.0 CDTi; 2.0 CDTi 4x4
 11.14-03.17
 B 20 DTH; (125kW)
 gauche supérieur | 532 0885 10 | 13

INSIGNIA A Saloon (G09)

2.0 CDTi; 2.0 CDTi 4x4
 11.14-03.17
 B 20 DTH; (125kW)
 gauche supérieur | 532 0885 10 | 13



OPEL

INSIGNIA A Sports Tourer (G09)

2.0 CDTi; 2.0 CDTi 4x4
 11.14-12.16
 B 20 DTH; (125kW)
 gauche supérieur | 532 0885 10 | 13

INSIGNIA B Country Tourer (Z18)

2.0 CDTi; 2.0 CDTi 4x4
 06.17-
 D 20 DTH; D 20 DTR; (125-154kW)
 gauche supérieur | 532 0885 10 | 13

INSIGNIA B Grand Sport (Z18)

2.0 CDTi; 2.0 CDTi 4x4
 03.17-
 B 20 DTH; D 20 DTH; D 20 DTR; (125-154kW)
 gauche supérieur | 532 0885 10 | 13

INSIGNIA B Sports Tourer (Z18)

2.0 CDTi; 2.0 CDTi 4x4
 03.17-
 B 20 DTH; D 20 DTH; D 20 DTR; (125-154kW)
 gauche supérieur | 532 0885 10 | 13

ZAFIRA C

2.0 CDTi
 01.15-
 B 20 DTH; D 20 DTH; (125kW)
 gauche supérieur | 532 0885 10 | 13

PEUGEOT

207

1.4 16V; 1.6 16V; 1.6 16V RC; 1.6 16V Turbo; 1.6 16V VTi; 1.6 VTi
 02.06-10.13
 5FR (EP6DT); 5FS (EP6C); 5FW (EP6); 5FX (EP6DT); 5FY (EP6DTS); 8FR (EP3); 8FS (EP3); EP3; EP3C; EP6; (70-128kW)
 WP | 532 0912 10 | 13

207 CC

1.6 16V; 1.6 16V Turbo
 02.07-12.13
 5FR (EP6DT); 5FS (EP6C); 5FV (EP6CDT); 5FW (EP6); 5FX (EP6DT); EP6; (88-115kW)
 WP | 532 0912 10 | 13

208

1.4 GPL; 1.4 VTi; 1.6; 1.6 GTi; 1.6 THP 165
 03.12-
 5FS (EP6C); 5FU (EP6CDTX); 5FV (EP6CDT); 5GR (EP6FDTX); 5GZ (EP6FDT); 8FS (EP3); EP3; EP6; EP6CDTX; (70-153kW)
 WP | 532 0912 10 | 13

308 I

1.4 16V; 1.6 16V; 1.6 GTi; 1.6 THP
 09.07-12.14
 5FT (EP6DT); 5FU (EP6CDT); 5FW (EP6); 5FX (EP6DT); 5FY (EP6DTS); 8FR (EP3); 8FS (EP3); EP3; EP6; EP6CDTX; (70-147kW)
 WP | 532 0912 10 | 13

308 II


























1.6; 1.6 GT 205; 1.6 GTi; 1.6 PureTech 225; 1.6 THP 125; 1.6 THP 155; 1.6 THP 163
 09.13-
 5FA (EP6CDT); 5FM (EP6CDTM); 5FV (EP6CDT); 5GN (EP6FDTR); 5GP (EP6FDTR); 5GT (EP6FDTX); GGR (EP6FADTX); (92-200kW)
 WP | 532 0912 10 | 13

508

1.6; 1.6 THP; 1.6 VTi
 11.10-
 5FH (EP6C); 5FS (EP6C); 5FV (EP6CDT); 5GZ (EP6FDT); (85-121kW)
 WP | 532 0912 10 | 13

508 II (FB_, F3_, FE_) / 508 SW II (FE_, F4_)

1.6 PureTech 180; 1.6 PureTech 225; 1.6 THP 165
 09.18-
 5GF (EP6FADTXD); 5GG (EP6FADTX); 5GY (EP6FDTM); GCR (EP6FADTX); GFR (EP6FADTXD); (121-165kW)
 WP | 532 0912 10 | 13

			
PEUGEOT			
2008			
1.6 VTi  03.13-  5FS (EP6C); (88kW)			
	WP	532 0912 10	13
3008			
1.6 THP; 1.6 Turbo; 1.6 VTi  06.09-08.16  5FE (EP6CDTM); 5FE (EP6CDTMD); 5FS (EP6C); 5FV (EP6CDT); 5FW (EP6); 5FX (EP6DT); 5GZ (EP6FDT); EP6; (88-121kW)			
	WP	532 0912 10	13
3008 SUV (M_)			
1.6 PureTech 180; 1.6 THP 165  05.16-  5GF (EP6FADTXD); 5GZ (EP6FDT); (121-133kW)			
	WP	532 0912 10	13
5008			
1.6 16V; 1.6 THP 150; 1.6 THP 163; 1.6 THP 165  09.09-03.17  5FS (EP6C); 5FV (EP6CDT); 5FW (EP6); 5FX (EP6DT); 5GZ (EP6FDT); EP6; (88-121kW)			
	WP	532 0912 10	13
5008 II			
1.6 THP 165  12.16-  5GY (EP6FDTM); 5GZ (EP6FDT); (121kW)			
	WP	532 0912 10	13
PARTNER			
1.6; 1.6 VTi  09.09-04.16  5FK (EP6CB); 5FS (EP6C); (72-88kW)			
	WP	532 0912 10	13
RCZ			
1.6 16V; 1.6 THP 270  03.10-12.15  5FG (EP6CDTR); 5FV (EP6CDT); EP6CDTX; (115-199kW)			
	WP	532 0912 10	13







Numerical listing / Liste numérique







530 0102 30	FORD	3
530 0731 10	JAGUAR	3
530 0731 10	LAND ROVER	4
530 0734 10	LAND ROVER	3, 4
532 0885 10	OPEL	4
532 0912 10	BMW	3
532 0912 10	CITROËN	3
532 0912 10	DS	3
532 0912 10	MINI	4
532 0912 10	PEUGEOT	4, 5



		1 2 3 KIT				
				DAYCO	CONTITECH	GATES
530 0102 30	531 0657 20	1	0			KP35360XS-1 Z80153 KP35360XS1 T42033
	532 0016 10	1				
	532 0093 10	1				
	536 0120 10	1				
530 0734 10	531 0578 10	1	13	KTB775		K035624XS
	531 0771 10	1				
	532 0461 10	1				
	536 0312 10	1				
	536 0423 10	1				






OE references / Références OE

 			 		
1...			C...		
1112530	FORD	530 0102 30	C2C24828	JAGUAR	530 0731 10
1112531	FORD	530 0102 30	C2D7052	JAGUAR	530 0731 10
11517545958	BMW	532 0912 10	C2D7052	JAGUAR	530 0731 10
11517545958	BMW	532 0912 10	F...		
11517571012	BMW	532 0912 10	F5RZ6K254A	FORD	530 0102 30
11517571012	BMW	532 0912 10	F5RZ6K254A	FORD	530 0102 30
11517619020	BMW	532 0912 10	F5RZ6M250A	FORD	530 0102 30
11517619020	BMW	532 0912 10	F5RZ6M250A	FORD	530 0102 30
120447	CITROËN	532 0912 10	F5RZ6M250A	FORD	530 0102 30
120447	CITROËN	532 0912 10	F5RZ6M250B	FORD	530 0102 30
120447	PEUGEOT	532 0912 10	F5RZ6M250B	FORD	530 0102 30
120447	PEUGEOT	532 0912 10	J...		
120454	CITROËN	532 0912 10	JAGUCDI004	JAGUAR	530 0731 10
120454	CITROËN	532 0912 10	JD61536	JAGUAR	530 0731 10
120454	PEUGEOT	532 0912 10	JD61536	JAGUAR	530 0731 10
120454	PEUGEOT	532 0912 10	L...		
120459	CITROËN	532 0912 10	LANDCDI002	LAND ROVER	530 0731 10
120459	CITROËN	532 0912 10	LR004708	LAND ROVER	530 0734 10
120459	PEUGEOT	532 0912 10	LR016655	LAND ROVER	530 0731 10
120459	PEUGEOT	532 0912 10	LR016655	LAND ROVER	530 0731 10
1311306	LAND ROVER	530 0731 10	LR016656	LAND ROVER	530 0731 10
1311306	LAND ROVER	530 0731 10	LR016656	LAND ROVER	530 0731 10
1311306	LAND ROVER	530 0734 10	LR016656	LAND ROVER	530 0731 10
1311306	LAND ROVER	530 0734 10	LR016656	LAND ROVER	530 0731 10
1324388	LAND ROVER	530 0731 10	LR016656	LAND ROVER	530 0731 10
1324388	LAND ROVER	530 0731 10	LR016656	LAND ROVER	530 0731 10
1663391	FORD	530 0102 30	Y...		
1663392	FORD	530 0102 30	YS7J6268AB	FORD	530 0102 30
5...			YS7J6268AB	FORD	530 0102 30
55505280	OPEL	532 0885 10	YS7J6268BA	FORD	530 0102 30
55505280	VAUXHALL	532 0885 10	YS7J6268BA	FORD	530 0102 30
6...			YS7J6268BA	FORD	530 0102 30
6635941	FORD	530 0102 30	C...		
6635942	FORD	530 0102 30	C2C24828	JAGUAR	530 0731 10
6744307	FORD	530 0102 30			
6764161	FORD	530 0102 30			
6764162	FORD	530 0102 30			
7...					
7545958	BMW	532 0912 10			
7545958	BMW	532 0912 10			
7571012	BMW	532 0912 10			
7571012	BMW	532 0912 10			
7619020	BMW	532 0912 10			
7619020	BMW	532 0912 10			
9...					
928M6268A1A	FORD	530 0102 30			
928M6268A1A	FORD	530 0102 30			
928M6268A1B	FORD	530 0102 30			
928M6268A1B	FORD	530 0102 30			
928M6268A2C	FORD	530 0102 30			
928M6268A2C	FORD	530 0102 30			
928M6268A2D	FORD	530 0102 30			
928M6268A2D	FORD	530 0102 30			
928M6K254AC	FORD	530 0102 30			
928M6K254AC	FORD	530 0102 30			
928M6M250BC	FORD	530 0102 30			
928M6M250BC	FORD	530 0102 30			
928M6M250DC	FORD	530 0102 30			
928M6M250DC	FORD	530 0102 30			
928M6M250DC	FORD	530 0102 30			
9X2Q6K254DA	LAND ROVER	530 0731 10			
9X2Q6K254DA	LAND ROVER	530 0734 10			






Cross references / Correspondance des références

DAYCO 	DAYCO 	DAYCO 
APV2978 APV2978F KTB775	532 0912 10 532 0912 10 530 0734 10	






Cross references / Correspondance des références

GATES 	GATES 	GATES 
K035624XS KP35360XS1 KP35360XS1 T42033 Z80153	530 0734 10 530 0102 30 530 0102 30 530 0102 30 530 0102 30	






Cross references / Correspondance des références

INA		INA		INA	
F-608413.05	532 0885 10				
F60841305	532 0885 10				
F-633182	532 0885 10				
F633182	532 0885 10				



Cross references / Correspondance des références

SKF 	SKF 	SKF 
---	---	---

VKMA07261

530 0734 10



