



## LuK Lever Kits.

The tractor clutch repair solution from the world's leading OE manufacturer.



**SCHAEFFLER**



**FAG**



# 24/7

## **LuK Tractor Clutches: No. 1 in the field at all times!**

Tractor clutches do not only have to ensure operability. They often have to run secondary machines via PTO, too. All leading tractor manufacturers rely on the durability, the cost efficiency and the outstanding damping qualities of LuK tractor clutch systems. Our large product range provides the right clutch for every purpose – best quality and operating comfort included. It's not without reason that LuK is the global leader in clutches sold per year.



## **LuK Lever Kits.**

### **Your advantages at a glance:**

- LuK – worldwide number one for tractor clutches
- LuK Lever Kits contain all the OE quality components you need to carry out a professional tractor clutch repair
- OEM quality for both original equipment and as replacement parts

**To maintain optimum performance and reliability, Schaeffler engineers have issued the following advice regarding LuK Lever Kit installation:**

- Only genuine LuK components should be used in conjunction with a LuK Lever Kit
- The new levers must be installed using the relevant tractor manufacturer's recommended settings and specifications
- Care must be taken during lever removal



## **Serving you quality 24/7.**

Whether pulling or ploughing, high demands are made on a tractor's clutch – every single day. LuK Clutches always meet these demands – for both original equipment and as replacement parts. That is why LuK is the worldwide number one for tractor clutches.

Our product range includes clutch discs, clutch pressure plates and release systems, as well as the complete LuK RepSet for easy and professional clutch replacement. The product portfolio also offers a highly effective system to dampen vibrations for more comfort regardless of the conditions.

Now we offer a genuine repair option in the form of our comprehensive range of LuK Lever Kits containing all of the OE quality components you need to carry out a professional tractor clutch repair.



# Fitting Guide – LuK Clutch › LuK Lever Kit\*\*

## Double Clutches

Clutch Part Number	Bolt Depth (mm)*	Captive Disc Lever Kit	Loose Disc Lever Kit
223 0008 11	29	433 0287 10	433 0262 10
223 0008 11	69	433 0286 10	433 0103 10
223 0021 11	29	433 0287 10	433 0262 10
223 0021 11	69	433 0286 10	433 0103 10
223 0024 10	29	433 0287 10	433 0262 10
223 0024 10	69	433 0286 10	433 0103 10
223 0025 10	29	433 0287 10	433 0262 10
223 0025 10	69	433 0286 10	433 0261 10
223 0028 10	29	433 0287 10	433 0262 10
223 0028 10	69	433 0286 10	433 0103 10
223 0032 10	71	433 0176 10	433 0177 10
225 0044 11	11	433 0002 10	433 0001 10
225 0049 12	28	433 0174 10	433 0258 10
225 0049 12	78	433 0209 10	433 0210 10
225 0050 12	28	433 0174 10	433 0258 10
225 0050 12	78	433 0209 10	433 0211 10
225 0055 10	24	433 0174 10	433 0175 10
225 0055 10	74	433 0174 10	433 0257 10
228 0003 14	31	433 0197 10	433 0196 10
228 0003 14	79	433 0197 10	433 0196 10
228 0003 15	31	433 0198 10	433 0196 10
228 0003 15	79	433 0066 10	433 0059 10
228 0007 15	31	433 0195 10	433 0196 10
228 0007 15	79	433 0072 10	433 0249 10
228 0007 16	31	433 0195 10	433 0196 10
228 0007 16	79	433 0072 10	433 0249 10
228 0013 11	81	433 0058 10	433 0053 10
228 0019 12	81	433 0248 10	433 0053 10
228 0027 14	34	433 0296 10	433 0272 10
228 0027 14	81	433 0058 10	433 0053 10
228 0031 10	35	433 0198 10	433 0196 10
228 0031 10	81	433 0065 10	433 0024 10
228 0038 10	34	433 0296 10	433 0272 10
228 0038 10	81	433 0058 10	433 0053 10
228 0046 10	34	433 0295 10	433 0268 10
228 0046 10	81	433 0187 10	433 0188 10
228 0047 10	34	433 0198 10	433 0196 10
228 0047 10	81	433 0065 10	433 0251 10
228 0067 11	81	433 0004 10	433 0220 10
228 0072 10	81	433 0301 10	433 0259 10
228 0073 11	34	433 0198 10	433 0196 10

Clutch Part Number	Bolt Depth (mm)*	Captive Disc Lever Kit	Loose Disc Lever Kit
228 0073 11	81	433 0052 10	433 0249 10
228 0077 10	81	433 0207 10	433 0252 10
228 0077 12	81	433 0207 10	433 0252 10
228 0077 14	35	433 0198 10	433 0196 10
228 0077 14	81	433 0065 10	433 0251 10
228 0077 17	35	433 0198 10	433 0196 10
228 0077 17	81	433 0065 10	433 0251 10
228 0079 11	35	433 0198 10	433 0274 10
228 0079 11	81	433 0065 10	433 0251 10
228 0087 10	81	433 0238 10	433 0246 10
228 0088 10	81	433 0239 10	433 0247 10
228 0091 10	31	433 0198 10	433 0196 10
228 0091 10	79	433 0052 10	433 0042 10
228 0093 11	35	433 0198 10	433 0196 10
228 0093 11	81	433 0065 10	433 0251 10
228 0098 10	81	433 0207 10	433 0252 10
228 0098 11	35	433 0198 10	433 0196 10
228 0099 10	30	433 0185 10	433 0181 10
228 0115 10	30	433 0183 10	433 0180 10
228 0121 10	34	433 0198 10	433 0196 10
228 0121 10	81	433 0052 10	433 0249 10
228 0128 10	35	433 0198 10	433 0196 10
228 0128 10	81	433 0065 10	433 0251 10
228 0128 11	35	433 0198 10	433 0196 10
228 0128 11	81	433 0065 10	433 0251 10
228 0130 11	30	433 0185 10	433 0181 10
228 0131 10	18	433 0290 10	433 0279 10
228 0132 10	31	433 0195 10	433 0196 10
228 0132 10	79	433 0291 10	433 0250 10
228 0133 10	31	433 0198 10	433 0196 10
228 0133 10	79	433 0291 10	433 0250 10
228 0133 11	31	433 0195 10	433 0196 10
228 0133 11	79	433 0291 10	433 0250 10
228 0136 10	30	433 0185 10	433 0181 10
228 0144 10	81	433 0207 10	433 0252 10
228 0146 10	79	433 0207 10	433 0252 10
228 0147 10	29	433 0241 10	433 0242 10
228 0151 10	29	433 0199 10	433 0181 10
228 0153 10	29	433 0199 10	433 0182 10
228 0154 10	31	433 0195 10	433 0196 10
228 0154 10	79	433 0066 10	433 0059 10

# Fitting Guide – LuK Clutch › LuK Lever Kit\*\*

## Double Clutches

Clutch Part Number	Bolt Depth (mm)*	Captive Disc Lever Kit	Loose Disc Lever Kit
228 0155 10	29	433 0185 10	433 0182 10
228 0156 10	29	433 0185 10	433 0269 10
228 0159 10	34	433 0197 10	433 0196 10
228 0159 10	81	433 0052 10	433 0249 10
228 0161 10	26	433 0194 10	433 0193 10
228 0177 10	79	433 0207 10	433 0253 10
228 0181 10	30	433 0185 10	433 0181 10
228 0184 10	30	433 0185 10	433 0181 10
228 0185 10	79	433 0297 10	433 0273 10
228 0186 10	23	433 0292 10	433 0265 10
228 0194 10	23	433 0198 10	433 0265 10
228 0204 10	79	433 0066 10	433 0059 10
228 0207 10	30	433 0185 10	433 0181 10
228 0208 10	30	433 0293 10	433 0267 10
228 0212 10	81	433 0289 10	433 0264 10
228 0216 10	30	433 0184 10	433 0182 10
229 0001 11	11	433 0002 10	433 0001 10
229 0001 12	11	433 0002 10	433 0001 10
230 0002 11	23	433 0013 10	433 0015 10
230 0003 11	23	433 0013 10	433 0014 10
230 0011 14	81	433 0004 10	433 0003 10
230 0017 11	33	433 0298 10	433 0277 10
230 0017 11	81	433 0284 10	433 0256 10
230 0018 10	30	433 0295 10	433 0275 10
230 0028 10	34	433 0295 10	433 0268 10
230 0028 10	81	433 0187 10	433 0188 10
230 0031 10	34	433 0295 10	433 0271 10
230 0031 10	81	433 0289 10	433 0260 10
230 0033 10	42	433 0192 10	433 0191 10
230 0033 11	42	433 0192 10	433 0191 10
230 0112 10	45	433 0296 10	433 0276 10
231 0020 14	52	433 0115 10	433 0114 10
231 0020 14	85	433 0115 10	433 0114 10
231 0021 11	50	433 0021 10	433 0113 10
231 0021 11	81	433 0021 10	433 0113 10
231 0023 14	50	433 0205 10	433 0255 10
231 0023 14	81	433 0037 10	433 0123 10
231 0026 11	81	433 0299 10	433 0278 10
231 0030 10	28	433 0101 10	433 0168 10
231 0030 10	91	433 0029 10	433 0030 10
231 0031 11	49	433 0021 10	433 0113 10

Clutch Part Number	Bolt Depth (mm)*	Captive Disc Lever Kit	Loose Disc Lever Kit
231 0031 11	81	433 0021 10	433 0113 10
231 0033 12	49	433 0173 10	433 0172 10
231 0033 12	81	433 0173 10	433 0172 10
231 0033 13	49	433 0173 10	433 0172 10
231 0033 13	81	433 0173 10	433 0172 10
231 0042 10	26	433 0200 10	433 0168 10
231 0043 10	26	433 0200 10	433 0168 10
231 0046 11	28	433 0215 10	433 0213 10
231 0049 11	28	433 0101 10	433 0206 10
231 0049 19	28	433 0101 10	433 0206 10
231 0050 10	91	433 0171 10	433 0125 10
231 0051 11	81	433 0037 10	433 0204 10
231 0052 11	81	433 0037 10	433 0204 10
231 0060 10	28	433 0101 10	433 0206 10
231 0067 10	28	433 0101 10	433 0206 10
231 0087 10	49	433 0173 10	433 0172 10
231 0087 10	81	433 0173 10	433 0172 10
231 0088 10	28	433 0101 10	433 0221 10
231 0089 10	28	433 0101 10	433 0221 10
231 0098 10	18	433 0288 10	433 0279 10
231 0100 10	78	433 0037 10	433 0204 10
231 0102 10	47	433 0283 10	433 0343 10
231 0102 10	81	433 0283 10	433 0343 10
231 0103 10	49	433 0173 10	433 0172 10
231 0103 10	81	433 0173 10	433 0172 10
231 0105 10	28	433 0101 10	433 0222 10
231 0106 10	28	433 0101 10	433 0206 10
231 0109 10	28	433 0101 10	433 0263 10
231 0110 10	28	433 0101 10	433 0206 10
231 0116 10	28	433 0101 10	433 0212 10
231 0117 10	28	433 0101 10	433 0223 10
231 0122 10	28	433 0308 10	433 0270 10
232 0001 10	49	433 0282 10	433 0280 10
233 0001 14	81	433 0111 10	433 0112 10
233 0004 10	23	433 0016 10	433 0203 10
233 0006 12	30	433 0050 10	433 0043 10
233 0010 11	30	433 0027 10	433 0043 10
233 0016 10	23	433 0016 10	433 0224 10
233 0020 12	30	433 0050 10	433 0043 10
233 0021 12	49	433 0205 10	433 0254 10
233 0021 12	81	433 0037 10	433 0208 10

# Fitting Guide – LuK Clutch > LuK Lever Kit\*\*

## Double Clutches

Clutch Part Number	Bolt Depth (mm)*	Captive Disc Lever Kit	Loose Disc Lever Kit	Clutch Part Number	Bolt Depth (mm)*	Captive Disc Lever Kit	Loose Disc Lever Kit
233 0026 10	30	433 0166 10	433 0167 10	233 0040 10	81	433 0037 10	433 0208 10
233 0027 10	30	433 0178 10	433 0179 10	233 0045 10	81	433 0205 10	433 0216 10
233 0027 11	30	433 0178 10	433 0179 10	233 0045 11	49	433 0282 10	433 0281 10
233 0033 11	47	433 0037 10	433 0217 10	233 0051 10	28	433 0285 10	433 0266 10
233 0033 11	50	433 0282 10	433 0280 10	235 0004 10	97	433 0170 10	433 0169 10
233 0034 10	49	433 0282 10	433 0281 10	235 0006 10	97	433 0170 10	433 0169 10
233 0034 10	81	433 0205 10	433 0216 10	235 0007 14	30	433 0109 10	433 0110 10
233 0034 12	49	433 0282 10	433 0281 10	235 0025 10	97	433 0170 10	433 0342 10
233 0034 12	81	433 0205 10	433 0216 10	235 0026 10	97	433 0170 10	433 0169 10
233 0035 10	30	433 0178 10	433 0179 10	235 0027 10	97	433 0170 10	433 0169 10
233 0036 10	30	433 0178 10	433 0179 10	235 0056 10	97	433 0170 10	433 0169 10
233 0039 10	49	433 0205 10	433 0254 10	235 0057 10	97	433 0170 10	433 0169 10
233 0039 10	81	433 0037 10	433 0208 10				
233 0040 10	49	433 0205 10	433 0254 10				

## Single & Double Sequential Clutches

Clutch	Lever Kit	Clutch	Lever Kit	Clutch	Lever Kit
125 0038 50	433 0225 10	130 0011 41	433 0201 10	133 0208 40	433 0201 10
128 0029 10	433 0218 10	130 0015 41	433 0201 10	223 0007 11	433 0007 10
128 0045 50	433 0236 10	130 0020 41	433 0201 10	228 0023 10	433 0219 10
128 0047 50	433 0237 10	131 0039 11	433 0201 10	228 0057 41	433 0202 10
128 0073 10	433 0189 10	131 0051 10	433 0201 10	230 0013 42	433 0201 10
128 0302 10	433 0186 10	133 0007 10	433 0201 10	230 0015 42	433 0201 10
130 0009 40	433 0201 10	133 0008 11	433 0201 10		

\* Check housing bolt depth for correct fitment.

\*\* Part numbers are for reference purposes only.

For accurate model information please refer to the latest catalogue information.



**To maintain optimum performance and reliability, Schaeffler engineers have issued the following advice regarding LuK Lever Kit installation:**

- +** Only genuine LuK components should be used in conjunction with a Lever Kit.
- +** The new levers must be installed using the relevant tractor manufacturer's recommended settings and specifications.
- +** Care must be taken during lever removal!

## More than four strong brands.

### ... more expertise

For decades, the name Schaeffler has stood for high-quality OEM repair solutions for engine, transmission and chassis – in passenger cars, commercial vehicles, and tractors. That alone marks us out as an expert partner to manufacturers, distributors and garages.

### ... more quality

As an OE manufacturer, we are committed to uncompromising quality and ongoing innovation that you can rely on.

### ... more services

- REPERT – our online garage portal providing technical knowledge
- Online catalog detailing the very latest product ranges
- Service hotline – for instant help
- Technical training – online and offline
- Special tools – custom-made for trouble-free repairs

### Further information:

[www.schaeffler-aftermarket.com](http://www.schaeffler-aftermarket.com)