
# BARDEN Ball Screw Support Bearings





## **BEARING NOMENCLATURE**

# Series BSB Example: BSB2047DUH 0-9 Series L Example: L150HX205DBTT1500 0-9



# Design/Applications

Barden Series L and BSB Series ball screw support bearings are manufactured specifically for high performance ball screw applications, where extreme rigidity requirements preclude the use of standard angular contact bearings. The internal configuration has been designed to provide an optimum combination of high rigidity, low drag torque, exceptional control of axial runout, higher running speeds and longer life.


Series L and BSB Series nonseparable angular contact bearings have cutaway shoulders on both the inner and outer rings. They can support very high thrust loads in one direction or combinations of radial and thrust loads, but not radial loading alone. Series L and BSB Series bearings are designed to provide machine tool drive systems with extreme axial rigidity, low drag tor que and minimal axial runout. They are intended for specific applications in machine tools, e.g., ball screw supports, cross slides, X-Y table positioners and transfer tables. They should not be used in place of standard angular contact spindle bearings.

These bearings are available in standard duplex or

quadruplex sets. In addition, we will supply custom combination sets to meet specialized application needs.

## Limiting Speeds

Limiting speeds shown in table are useful guidelines. Actual speed limits must be based on the application characteristics. Life requirements, heat transfer conditions, loading



# Preloads

Standard values (heavy) shown in table will be supplied unless otherwise specified. Barden recognizes that some applications do not require the full axial stif fness (compliance) of the standard preload and will supply bearings with custom-ground preloads if r equired.

## Seals

Some ball screw support bearings may also be available in sealed versions. Ask your Barden sales engineer for details.

## Cages

BSB Series bearings have a molded nylon, glass fiber r einforced polyamide cage with spherical ball pockets. Series L bearings have a land-piloted cage of reinforced phenolic, pre-

cision-machined, with evenly spaced ball pockets.

BSB Series Molded Nylon Cage

> Series L Phenolic Cage

All metric (BSB Series) ball screw support bearings come with the molded nylon cage, standard. Series L bearings are equipped with the phenolic cage, standard.

## Mounting and Fitting

Normal fitting practice is line-to-line to loose for both shaft and housing fits, as shown in table at right.

All bearing pairs and sets are match-marked on their outside diameter surfaces to indicate correct positioning of each bearing. Barden packaging also contains detailed instructions for proper installation.


Recommendations for shaft and housing shoulder diameters are based on maximum support of duplexmounted bearings (see table). In circumstances with other mounting arrangements, consult Barden Product Engineering.

# Life Calculations

Most ball screw support bearing applications are subject to duty-cycle loading with constantly changing feeds, speeds and operating loads. These factors, in combination with the heavy preloads built into the bearings, make life calculations difficult. Consult Barden Product Engineering for information which can be used in specific cases.

# Materials

All ball screw support bearings (rings and balls) are made from 52100 steel. Bearings are also available with X-life ultra rings and ceramic (silicon nitride) balls for



## ENGINEERING DATA SUMMARY

#### Configurations

Standard configuration includes a cage; some sizes are also available in a full complement version (X205 suffix). Please consult Barden.

Maximum Shaft/Housing Fillet Radius Which Bearing Corner Will Clear .040" (1.00 mm)

#### Attainable Speeds

Limits given are for DU mounted sets with standard heavy pr eload.

#### Material

SAE 52100 bearing steel is standard.

#### Duplexing


All bearings are universally ground D and can be mounted DU (Universal), DF (Face-to-Face), or DB (Back-to-Back), in pairs or in various combinations — three, four or more bearings as r equired. Standard preloads for pa irs are shown. For quads (DUH), multiply the duplex preload indicated by 2.


#### Tolerances

Standard precision class for Series L and BSB Series is ABEC 7, except for a tighter maximum raceway runout with side .0001" (2.5  $\mu m$  ).

#### Lubricant:

Desired lubrication should be specified when ordering, based on torque, speed and temperature conditions of the application. Barden strongly recommends G-73, a NLGI Class 2 gr ease with EP additives. Consult Barden for details.





QUADRUPLEX SET

| Bore<br>Diameter<br>d |        | Outside<br>Diameter<br>D |        | DUPLEX<br>Width<br>B |        | Basic Bearing |      |        | Standard<br>Preloads | Ho<br>Sho<br>Diar<br>(in.) : | ft and<br>using<br>oulder<br>neters<br>±.005" | Fitti<br>Practic<br>(Line-tر<br>to Lo |
|-----------------------|--------|--------------------------|--------|----------------------|--------|---------------|------|--------|----------------------|------------------------------|---|---------------------------------------|
| mm                    | inch   | mm                       | inch   | mm                   | inch   | Nomenclature* | Oil  | Grease | (lbs.)**             | Shaft                        | Housing                                       | Shaft                                 |
| 20                    | .7874  | 47                       | 1.8504 | 30                   | 1.181  | BSB2047DUH    | 6700 | 5000   | 500                  | 1.065                        | 1.520   | .0004                                 |
| 20                    | .7874  | 47                       | 1.8504 | 31.75                | 1.2500 | L078HDF       | 4000 | 2800   | 750                  | 1.065                        | 1.520   | .0004                                 |
| 23.838                | .9385  | 62                       | 2.4409 | 31.75                | 1.2500 | L093HDF       | 2400 | 1680   | 1000                 | 1.590                        | 2.130   | .0004                                 |
| 25                    | .9843  | 62                       | 2.4409 | 30                   | 1.181  | BSB2562DUH    | 5000 | 3800   | 750                  | 1.590                        | 2.130   | .0004                                 |
| 30                    | 1.1811 | 62                       | 2.4409 | 30                   | 1.181  | BSB3062DUH    | 5000 | 3800   | 650                  | 1.590                        | 2.130   | .0004                                 |
| 35                    | 1.3780 | 72                       | 2.8346 | 30                   | 1.181  | BSB3572DUH    | 4300 | 3200   | 750                  | 1.880                        | 2.430   | .0004                                 |
| 38.1                  | 1.5000 | 72                       | 2.8346 | 31.75                | 1.2500 | L150HDF       | 1600 | 1100   | 1500                 | 1.880                        | 2.430   | .0004                                 |
| 38.1                  | 1.5000 | 72                       | 2.8346 | 31.75                | 1.2500 | L150HX4DF     | 1600 | 1100   | 1500                 | 1.880                        | 2.480   | .0004                                 |
| 40                    | 1.5748 | 72                       | 2.8346 | 30                   | 1.181  | BSB4072DUH    | 4000 | 3000   | 650                  | 1.880                        | 2.430   | .0004                                 |
| 44.475                | 1.7510 | 76.2                     | 3.0000 | 31.75                | 1.2500 | L175HDF       | 1400 | 1000   | 1500                 | 2.140                        | 2.680   | .0004                                 |
| 57.150                | 2.2500 | 90                       | 3.5433 | 31.75                | 1.2500 | L225HDF       | 1200 | 850    | 1750                 | 2.610                        | 3.145   | .0004                                 |
| 76.2                  | 3.0000 | 110                      | 4.3307 | 31.75                | 1.2500 | L300HDF       | 800  | 600    | 2250                 | 3.385                        | 3.915   | .0005                                 |

\* Certain sizes listed in table may not be in current production. Check for availability. \*\* Duplex preloads. For quad sebarts multiply by 2

|   | -  |                                      |   |  |
|---|--|--------------------------------------|---|--|
| ing<br>e (in.)<br>o-Line<br>ose)<br>Housing | Axial<br>Spring<br>Constant<br>(×10° lbs./in.)<br>Duplex | Drag Torque<br>(in.– lbs.)<br>Duplex | Dynamic<br>Thrust<br>Capacity<br>(Ibs.)<br>Duplex | Static<br>Thrust<br>Capacity<br>(Ibs.)<br>Duplex |
| .0005                                       | 4.28   | 0.44                                 | 4,300   | 5,600  |
| .0005                                       | 5.0  | 2.00                                 | 3,300   | 4,700  |
| .0005                                       | 6.6  | 2.80                                 | 3,850   | 6,500  |
| .0005                                       | 5.42   | 0.75                                 | 6,400   | 9,300  |
| .0005                                       | 5.14   | 0.75                                 | 5,800   | 8,800  |
| .0005                                       | 6.0  | 1.02                                 | 6,700   | 11,200   |
| .0005                                       | 8.4  | 4.00                                 | 4,000   | 7,500  |
| .0005                                       | 7.8  | 4.00                                 | 5,500   | 10,000   |
| .0005                                       | 6.0  | 1.02                                 | 6,300   | 11,000   |
| .0005                                       | 9.1  | 4.50                                 | 4,100   | 8,200  |
| .0005                                       | 11.6   | 6.00                                 | 4,400   | 10,000   |
| .0007                                       | 14.3   | 8.00                                 | 4,850   | 12,900   |

BARDEN



### The Barden Corporation

P.O. Box 2449 • 200 Park Avenue Danbury, Connecticut 06813-2449 Phone: 203/744-2211 • Fax: 203/744-3756 E-mail: sales@bardenbearings.com www.bardenbearings.com

## The Barden Corporation (UK)

Plymbridge Road • Estover Plymouth PL6 7LH • Devon Phone: +44(0)1752/735555 • Fax: +44(0)1752/733481 E-Mail: sales@barden.co.uk www.bardenbearings.co.uk

## FAG Aircraft/Super Precision Bearings Gmbh

Georg-Schäfer-Str. 30 • D-97421 Schweinfurt Phone: +49(0)9721/911911 • Fax +49(0)9721/913666 Email: acsp\_gmbh@fag.de www.fag.com