

FACT SHEET ROUND 2

FORMULA E KUALA LUMPUR

NOVEMBER 22

SCHAEFFLER



Spark SRT_01E
Audi Sport Abt Formula E Team



31 laps
maximum 60 minutes

- Full points after 75% of the distance covered (24 laps)
- 25 pts for the winner, 1 pt for 10th
- 3 pts for pole, 2 pts for fastest lap

FIA FORMULA E 2014/15

- First FIA racing series with electric vehicles
- Identical-specification car in the 2014/15 season
- 9 ePrix in the season (Buenos Aires, Miami, Berlin, London and others)
- 11 teams with two drivers and four cars each
- One mandatory pit stop with car change per driver
- Energy boost for three drivers by fan voting (#FanBoost)
- Complete Formula E info: www.fiaformulae.com



LUCAS' VIEW

Lucas di Grassi: "Compared to Beijing, Putrajaya is shorter and at first glance seems to feature a few more demanding turns and sections. It's going to be a great challenge that we've got to adjust to as quickly as possible. Formula E is unpredictable. Everybody's got the same material, the gaps are minimal and on a new track the relative strengths can pan out in a totally different way again. Our aim remains the same before each race: We're set on winning. And if that shouldn't be possible then we'd at least like to finish on the podium and take home valuable points."

2.29 kWh
maximum energy available per lap (qualifying)



78%
driven at full throttle

5 and **7**
12 turns per lap

3

drivers with largest number of votes in #FanBoost have 30 kW more power output for 5 seconds

fanboost.fiaformulae.com



56 kWh
of energy is available to a driver per race



2-person household (6 days)

Refrigerator, 150 l (210 days)

Light bulb, 60W (39 days non-stop)

TV set (15 days non-stop)

Dishwasher (70 washing cycles)

SCHAEFFLER FACTS

>80,000 employees
2,100 patents filed in 2013
170 locations worldwide
60 Schaeffler parts in automobiles worldwide (average)
4 titles for Schaeffler touring cars in the DTM

#11

LUCAS DI GRASSI (30)

Date of birth
August 11, 1984
Place of birth
São Paulo (BR)
Residence
Monaco (MC)
Height / weight
1.79 m / 75 kg



#66

DANIEL ABT (21)

Date of birth
December 3, 1992
Place of birth
Kempten (D)
Residence
Kempten (D)
Height / weight
1.79 m / 70 kg

twitter.com/SchaefflerPress

SCHAEFFLER

youtube.com/Schaeffler



SPARK SRT_01E

- **Vehicle:** formula car, carbon/aluminum monocoque chassis
- **Power unit:** rear-wheel drive from two motor generator units (MGUs)
- **Transmission:** sequential 5-speed, with paddle shifters
- **Output (practice and qualifying):** 200 kW (270 hp)
- **Output (race):** 150 kW (202.5 hp), additional power output of 30 kW (40.5 hp) by #FanBoost for three drivers
- **Acceleration:** 0-100 km/h in 2.9 sec
- **Top speed:** 225 km/h
- **Minimum weight (incl. driver):** 888 kg
- **Length:** 5,000 mm, width: 1,800 mm, height: 1,250 mm
- **Tires:** low profile tires (front: 9R18, rear: 11R18)