



## Water pump bearings

Integral shaft bearings

SCHAEFFLER



## Foreword

### High load carrying capacity

Water pump bearings do not have an inner ring but instead have raceways directly machined into the shaft. As a result, there is more space available for the rolling elements, giving a higher load carrying capacity than in solutions with conventional single bearings. In water pump bearings, rows of balls and rollers can be economically combined with each other. This gives a broad range of load carrying capacity values.

### No misalignment defects

The use of a common outer ring for two or more rows of rolling elements prevents misalignment defects, eliminating the risk of undesirable distortion of the bearings.

### Ready-to-fit units

In water pump bearings, the ends of the shaft normally extend beyond the outer ring on both sides. The length and diameter of these extended sections can be matched to the specific application. The ready-to-fit bearing unit is predominantly used in coolant pumps for road vehicles.

### Application

Water pump bearings are not only used in coolant pumps, however, and are therefore also described as integrated shaft bearings.

Due to the characteristics stated, they have a wide range of possible applications, for example in:

- fans
- tension pulleys
- vane pumps
- angle grinders.

The bearing solution appropriate to the specific application is developed, by agreement, by the application engineers responsible for the region, see page 40.

# Foreword

## Worldwide

Water pump bearings are manufactured locally by Schaeffler around the world.

At all manufacturing plants, the design and production are standardised by means of identical:

- specifications
- processes
- quality guidelines
- designations
- design guidelines.

Bearings from the different manufacturing plants differ from each other only in the indication on the shaft of the country of manufacture and the brand logo used, *Figure 1*.



*Figure 1*  
Manufacturing locations,  
brand logos


# Water pump bearings

	Page	
<b>Product overview</b>	Water pump bearings.....	4
<b>Features</b>	Bearing unit.....	5
	Designs .....	6
	Sealing .....	9
	Lubrication .....	10
	Designation.....	11
<b>Design and safety guidelines</b>	Rating life .....	12
	Design of bearing arrangements.....	12
	Mounting.....	14
<b>Dimension tables</b>	Water pump bearings, double row, ball/ball .....	18
	Water pump bearings, double row, roller/ball .....	27
	Water pump bearings, triple row, roller/ball/roller .....	38
	Water pump bearings, double decker, ball/ball and roller/ball.....	39
<b>Appendix</b>	Addresses .....	40


## Product overview Water pump bearings

### Double row

WA, WB




WF, WR, WT



0007DB8C6

### Triple row


WM



0007DB8BD

### Double decker

WD



0007DB8B9


# Water pump bearings

## Features

Water pump bearings are used predominantly in coolant pumps for road vehicles, *Figure 1*.

- ① Coolant pump for passenger car
- ② Water pump bearing

*Figure 1*  
Coolant pump



00019A39


## Bearing unit

A water pump bearing is a ready-to-fit bearing unit. It comprises a shaft that is supported by means of several rows of rolling elements in a through hardened outer ring. The standard material for the shaft and outer ring is 100Cr6/SAE52100. In special cases, the shaft is made from case hardened steel 16MnCr5.

The bearings are greased for life and are protected against environmental influences by seals, *Figure 2*.

- ① Shaft
- ② Seal
- ③ Cage
- ④ Rolling element row
- ⑤ Outer ring

*Figure 2*  
Structure of water pump bearing



00018026


# Water pump bearings

## Designs

Water pump bearings with a single bearing level are available in double row and triple row designs. The double decker design has two bearing levels.

### Double row design, ball/ball

The simplest and most economical design is the ball/ball design as a deep groove or angular contact ball bearing, *Figure 3*. This design is used for moderate loads.




### Double row design, roller/ball

Under heavier loads, water pump bearings of the roller/ball design are used. The function can be significantly improved in the case of this design too by a combination of a row of rollers with a three or four point contact bearing, *Figure 4*.

- ① Roller bearing/  
deep groove ball bearing (WR)
- ② Roller bearing/  
three point contact bearing (WT)
- ③ Roller bearing/  
four point contact bearing (WF)

*Figure 4*  
Double row design,  
roller/ball




000180A7

# Water pump bearings

## Triple row design


A water pump bearing with three bearing rows has particularly high load carrying capacity, *Figure 5*. This design is particularly suitable for use in fans.



*Figure 5*  
Triple row design

## Double decker

With a water pump bearing of the double decker design, two components can be supported for rotation independently of each other, *Figure 6*. A typical application is in adjustable coolant pumps.



*Figure 6*  
Double decker design

The bearing solution appropriate to the specific application is developed, by agreement, by the application engineers responsible for the region, see page 40.

## Sealing

Seals give protection against the ingress of contaminant and the egress of grease. Selection of the correct seals is a decisive factor for the operating life of the bearing. The appropriate material and type must be selected.



No seal can give absolute protection in the long term against the ingress of water.

## Material


Three different elastomer materials are available for the seals:

- FPM
- HNBR
- NBR.

The appropriate material is selected in accordance with the application and the environmental influences; seals made from different materials can be used on the two sides of the bearing.

## Type

Four different types of seals can be used, *Figure 7*.



*Figure 7*  
Seals, types

Since the seal undercuts are of a standardised design, single lip, double lips and R-SAFE seals are interchangeable with each other.

# Water pump bearings

<b>Single lip seal</b>	This is the most economical seal, offers minimum protection and has low frictional resistance. Single lip seals are still widely used at present but are being replaced in the medium term by double lip seals.
<b>Double lip seal</b>	The double lip seal has slightly higher frictional resistance than the single lip seal. It is economical and offers a higher level of protection against contamination than the single lip seal. Double lip seals are currently the standard seals used in water pump bearings.
<b>R-SAFE seal</b>	This seal was specially developed for sealing the impeller-facing side of water pump bearings. The R-SAFE has demonstrated superior sealing action against the ingress of water and water vapour over many years, including usage in high volume production.
<b>Rotary shaft seal</b>	The rotary shaft seal is used in preference in water pumps driven by chains or gears.
<b>Lubrication</b>	Water pump bearings are lubricated for life. The standard lubricant used has been selected in relation to use in water pump bearings. We check and ensure its compatibility with the seals used.  Never use seals other than the original seals. Unsuitable seals will be attacked by the lubricant and will lose their sealing effect. Lubricant will then escape, while water and contamination will penetrate the bearing. The bearing will then be destroyed very quickly.

**Designation** The design of the bearing can be deduced from the designation, *Figure 8.*

- ① Design
- ② Number of shaft shoulders
- ③ Number, consecutive
- ④ Variant, such as seal

*Figure 8*  
Designation



0007F26A

The two letters indicate the design, see table.

**Design**

Code letters	Design
WA	Double row, asymmetrical angular contact ball bearing
WB	Double row, symmetrical deep groove or angular contact ball bearing
WD	Double decker
WF	Double row, roller bearing and four point contact bearing
WM	Triple row
WR	Double row, roller bearing and deep groove ball bearing
WT	Double row, roller bearing and three point contact bearing

The first digit indicates the number of shaft shoulders, see table.

**Shaft shoulders**

Code	Shaft shoulders
0	No shaft shoulder
1	One end of the shaft has a shoulder
2	Both ends of the shaft have a shoulder

# Water pump bearings

## Design and safety guidelines

The specifications in the section Technical principles, Catalogue HR 1, Rolling Bearings, also apply to water pump bearings.

### Rating life

The rating life of water pump bearings is calculated using the calculation methods for rolling bearings. The decisive influencing factors are the loads, speeds, lubrication, temperature, bearing clearance and load plane or load planes. In many cases, a practical application is highly complex. We can provide support in design by means of appropriate software.



Excessive load will lead to premature failure of the bearing.  
Never subject the bearing to a heavier load than intended.  
If it is not possible to determine the load clearly, please consult the application engineers responsible for the region.

### Design of bearing arrangements

Water pump bearings are normally located in the housing by means of a press fit.

### Housing tolerances

When determining a suitable press fit, the material combination of the housing and bearing must be taken primarily into consideration. As approximate guide values, we recommend housing fits in accordance with the table.

### Housing material and fits

Housing material	Fit according to ISO
Pressure diecast aluminium	S6, S7 to X6, X7
Flake graphite cast iron	P6, P7 to R6, R7


For precise calculation of the required press fit, please consult the relevant application engineers.

## Mounting dimensions

Water pumps are standardised in terms of their outer ring diameter, *Figure 9*. Appropriate diameter of the standard shaft and preferred lengths of the outer ring: see table.

D = outer ring diameter  
d<sub>k</sub> = diameter of standard shaft  
C = preferred length of outer ring

*Figure 9*  
Mounting dimensions



00018049

Water pump bearings with standard dimensions according to the table can be supplied quickly and economically in large quantities.

## Standard dimensions

D mm	d <sub>k</sub> mm	C mm
24	12,038	27
30	15,918	22 – 27 – 30 – 34 – 38,9 – 44
	17,2	23 – 30 – 38,9
34	17,008	38,9 – 47
35	18	30 – 36 – 38,9
38,1	18,961	47 – 54
40	20,004	50
42	22	32 – 46 – 56
47	24	38 – 50
55	25,061	60
	30	60

# Water pump bearings

## Mounting

Correct mounting is a prerequisite for a long rating life of the bearing arrangement.




Damaged raceways or rolling elements can lead to premature failure of the bearing.

Mounting forces must be transmitted via the shaft or outer ring. Transmission of mounting forces via the rolling elements must always be avoided.

Mounting in a housing:


- Place the housing on a flat support surface.
- Align the outer ring of the bearing concentrically and axially parallel to the bore of the housing.
- Apply the mounting force uniformly to the end face of the outer ring, *Figure 10*.



*Figure 10*  
Mounting in a housing

**Mounting of a coolant seal:**


- Place the shaft and outer ring simultaneously on a flat support surface.
- Align the coolant seal concentrically and axially parallel to the shaft and bore in the housing.
- Apply the mounting force uniformly to the coolant seal, *Figure 11*.



## Water pump bearings

Mounting of a drive pulley and impeller:

- Place the opposite end of the shaft on a flat support surface.
- Align the drive pulley and impeller concentrically and axially parallel to the shaft.
- Apply the mounting force uniformly to the drive pulley and impeller, *Figure 12*.




**Fans** If angular offset or axial offset are present as a result of incorrect design or mounting, imbalance forces will occur in operation, *Figure 13*.

The resulting bearing load will increase with the square of the speed. In the case of heavy components such as fans, the load may increase rapidly to such an extent that it exceeds the material strength of the bearing components.



If heavy and sharp-edged parts break away from the water pump bearing at high velocity, this can lead to injury and in the worst case to loss of life.


Never subject the components to a heavier load than permissible. If it is not possible to determine the bearing load clearly, please consult the relevant application engineers.



*Figure 13*  
Imbalance

# Water pump bearings

Double row  
Ball/ball



WA, WB

**Dimension table** - Dimensions in mm

Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
WB02030.01 <sup>3)</sup>	24	56,9	9	28	19,9	12,038	-	-	-	-	-
WB01919 <sup>3)</sup>	24	59,9	9	31	19,9	12,038	-	-	-	-	-
WB21849 <sup>1)4)</sup>	24	62	7	30,4	24,5	12,038	-	-	5,6	10	-
WB11857 <sup>1)</sup>	24	64	8	34,1	21,9	12,038	-	-	-	-	-
WB01693.05 <sup>3)</sup>	24	65	14	31,1	19,9	12,038	-	-	-	-	-
WB01351.01 <sup>1)4)</sup>	24	76,6	13,3	36,4	26,9	12,055	-	-	-	-	-
WB01700.03	24	77	13,6	36,6	26,9	12,008	-	-	-	-	-
WB01027.03	24	80	16,6	36,5	26,9	12,008	-	-	-	-	-
WB01028.01	24	81,5	19	32,6	29,9	12,038	-	-	-	-	-
WB01632 <sup>1)4)</sup>	24	81,6	18,3	36,4	26,9	12,055	-	-	-	-	-
WB01083	24	85	21	37,1	26,9	12,038	-	-	-	-	-
WB01210	24	86,6	14,2	39,02	33,38	12,738	-	-	-	-	-
WB01902 <sup>3)</sup>	24	89,9	20	50	19,9	12	-	-	-	-	-
WB11875 <sup>1)3)4)</sup>	24	98,5	30,48	41,12	26,9	12,038	-	-	21	-	-
WB11768	24	100	16	57,1	26,9	12,055	10	-	15	-	-
WB01842 <sup>1)</sup>	24	104,5	8	76,6	19,9	12,038	-	-	-	-	-
WB01852 <sup>1)4)</sup>	24	109,6	46,3	36,4	26,9	12,055	-	-	-	-	-
WB21838 <sup>1)</sup>	30	64	8	32,6	23,4	15,918	12	12,038	7	30,3	-
WB11098	30	65	14,2	28,9	21,9	15,918	-	10	-	27,4	-
WA07066	30	65,85	25,01	2,04	38,8	15,918	-	-	-	-	WS2263
WB21225	30	66,65	8,4	31,35	26,9	15,918	13,038	12,038	6,5	30,2	-
WB11743.02 <sup>1)4)</sup>	30	66,9	9	31	26,9	15,918	-	12,038	-	28,7	-
WB01005	30	68	3,7	25,5	38,8	16	-	-	-	-	-
WB07486 <sup>6)</sup>	30	68,12	13,6	27,62	26,9	15,918	-	-	-	-	-
WB21848 <sup>1)4)</sup>	30	68,9	8,5	33,5	26,9	15,918	12,5	12,038	6,6	31,2	-
WB11853 <sup>1)4)</sup>	30	69,4	9	33,5	26,9	15,918	-	12,038	-	31,2	-
WB11825 <sup>4)</sup>	30	69,5	11,6	31	26,9	15,918	-	12	-	29,05	-
WB21318.01 <sup>1)5)6)</sup>	30	71	14	39	17,8	15,918	-	12,038	11	31,3	-
WB11519.01 <sup>3)</sup>	30	71,12	13,1	35,12	22,9	17,2	-	12	-	32,02	-

<sup>1)</sup> Special shaft.

<sup>2)</sup> Flinger sleeve.

<sup>3)</sup> R-SAFE seal.

<sup>4)</sup> Rotary shaft seal.

<sup>5)</sup> No seal.


<sup>6)</sup> Special outer ring.

<sup>7)</sup> Rolling element sets laterally transposed.

# Water pump bearings

Double row

Ball/ball



WA, WB

**Dimension table** (continued) · Dimensions in mm

Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
<b>WB07385<sup>1)6)</sup></b>	<b>30</b>	73,41	4,18	30,43	38,8	15,918	—	—	—	—	W2289-3.T1545
<b>WB07072<sup>6)</sup></b>	<b>30</b>	73,41	4,05	30,56	38,8	15,918	—	—	—	—	W2289
<b>WB07073<sup>1)6)</sup></b>	<b>30</b>	73,41	4,05	30,56	38,8	15,918	—	—	—	—	W2289-1.T1805
<b>WB07082<sup>1)6)</sup></b>	<b>30</b>	74,63	4,08	31,75	38,8	15,918	—	—	—	—	W2293.T1638
<b>WB17250.03<sup>6)</sup></b>	<b>30</b>	77,95	12,45	38,6	26,9	15,918	—	12,038	—	36,3	—
<b>WB11294.06<sup>6)</sup></b>	<b>30</b>	77,95	15	36,05	26,9	15,918	—	12	—	34,95	—
<b>WB11597</b>	<b>30</b>	77,95	15	36,05	26,9	15,918	—	12,038	—	34,95	—
<b>WA11698.01<sup>3)7)</sup></b>	<b>30</b>	78	19,1	32	26,9	15,918	—	12,038	—	29,7	—
<b>WB11831.01<sup>3)</sup></b>	<b>30</b>	78,2	17,7	37,6	22,9	15,918	—	12	—	35,3	—
<b>WB07012<sup>1)6)</sup></b>	<b>30</b>	79,1	13,6	38,6	26,9	15,918	—	—	—	—	WS2311
<b>WB01138.01</b>	<b>30</b>	80	14,1	38	27,9	15,918	—	—	—	—	—
<b>WB11647<sup>3)</sup></b>	<b>30</b>	80	15,5	41,6	22,9	17,2	—	12	—	39,2	—
<b>WB07068<sup>6)</sup></b>	<b>30</b>	80,04	15,85	37,29	26,9	15,918	—	—	—	—	WS2315-2
<b>WB07075<sup>6)</sup></b>	<b>30</b>	82,55	4,06	39,69	38,8	15,918	—	—	—	—	W2325
<b>WB11753<sup>3)</sup></b>	<b>30</b>	82,8	14,5	38,4	29,9	15,918	—	12	—	36,1	—
<b>WB01069</b>	<b>30</b>	83,15	16,05	42,1	25	15,918	—	—	—	—	—
<b>WB11357</b>	<b>30</b>	83,32	16,15	37,27	29,9	15,918	—	12,738	—	30,84	—
<b>WA11280</b>	<b>30</b>	83,5	15,5	40,1	27,9	15,918	—	12,038	—	38	—
<b>WB05090</b>	<b>30</b>	84,3	15,4	41,5	27,4	15,912	—	—	—	—	—
<b>WB11413</b>	<b>30</b>	84,3	20,8	36,6	26,9	15,918	—	12,008	—	34,5	—
<b>WA11680<sup>3)</sup></b>	<b>30</b>	84,4	16,9	40,6	26,9	15,918	—	12	—	38,3	—
<b>WB07071<sup>1)6)</sup></b>	<b>30</b>	84,5	17,34	40,26	26,9	15,977	—	—	—	—	WS6332-1
<b>WB17069<sup>6)</sup></b>	<b>30</b>	84,63	17,37	40,36	26,9	15,918	—	12,038	—	38,06	WS2333-3
<b>WA11065.03</b>	<b>30</b>	85	17	40,1	27,9	15,918	—	12,038	—	38	—
<b>WA11238.01</b>	<b>30</b>	85	13,5	43,6	27,9	15,918	—	12,038	—	38	—
<b>WA27126</b>	<b>30</b>	85	17	41,1	26,9	15,918	15,008	12,038	14,2	38,8	WS2334-6
<b>WB11074</b>	<b>30</b>	85	17	41,1	26,9	15,918	—	12,038	—	35	—
<b>WB11074.08</b>	<b>30</b>	85	17	41,1	26,9	15,918	—	12,038	—	35	—
<b>WB07076<sup>1)6)</sup></b>	<b>30</b>	85,89	3	44,09	38,8	15,918	—	—	—	—	W2338.T2363

<sup>1)</sup> Special shaft.

<sup>2)</sup> Flinger sleeve.

<sup>3)</sup> R-SAFE seal.

<sup>4)</sup> Rotary shaft seal.


<sup>5)</sup> No seal.

<sup>6)</sup> Special outer ring.

<sup>7)</sup> Rolling element sets laterally transposed.

# Water pump bearings

Double row  
Ball/ball



WA, WB

**Dimension table (continued) · Dimensions in mm**

Designation	Dimensions									Previous designation	
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>		
<b>WA11349.02<sup>3)</sup></b>	<b>30</b>	86,5	13,5	46,1	26,9	15,918	—	12,038	—	44	—
<b>WA12006</b>	<b>30</b>	86,5	16,5	43,1	26,9	15,918	—	12,038	—	40,8	—
<b>WB01001<sup>2)</sup></b>	<b>30</b>	87,5	13,6	38	35,9	15,008	—	—	—	—	—
<b>WB11132.02<sup>6)</sup></b>	<b>30</b>	87,5	15,5	50,1	21,9	15,918	—	12,038	—	48,5	—
<b>WB01070</b>	<b>30</b>	88	18,1	43	26,9	15,918	—	—	—	—	—
<b>WB11397</b>	<b>30</b>	88	16,1	45	26,9	15,918	—	12,038	—	42	—
<b>WB11073</b>	<b>30</b>	88,6	14,2	44,5	29,9	15,918	—	12,038	—	39	—
<b>WB11097.01</b>	<b>30</b>	89	21	41,1	26,9	15,918	—	12	—	35	—
<b>WB17070<sup>6)</sup></b>	<b>30</b>	89	18,1	44	26,9	15,918	—	12,038	—	41,7	WS2350-1
<b>WB01322</b>	<b>30</b>	90,1	16	49,1	25	15,918	—	—	—	—	—
<b>WB17305<sup>6)</sup></b>	<b>30</b>	90,19	15,6	35,79	38,8	15,918	—	12	—	33,49	W2355S
<b>WA11721</b>	<b>30</b>	90,5	17,5	46,1	26,9	15,918	—	12,038	—	43,8	—
<b>WB05119</b>	<b>30</b>	92,2	15,3	49,4	27,5	15,918	—	—	—	—	F-45566.3
<b>WB11464</b>	<b>30</b>	92,5	15,6	50	26,9	15,918	—	12,038	—	47	—
<b>WB17653<sup>6)</sup></b>	<b>30</b>	94	18,1	49	26,9	15,918	—	12,038	—	46,7	—
<b>WA15158</b>	<b>30</b>	94,35	17,55	38	38,8	15,918	—	12,008	—	34,95	—
<b>WB01121.01</b>	<b>30</b>	94,35	17,5	38,05	38,8	15,918	—	—	—	—	—
<b>WB15077</b>	<b>30</b>	94,35	17,5	38,05	38,8	15,918	—	12,008	—	34,95	—
<b>WB11529.01<sup>4)</sup></b>	<b>30</b>	94,37	20,91	46,56	26,9	15,918	—	12	—	44,61	—
<b>WA17129</b>	<b>30</b>	95,43	20,91	47,62	26,9	15,918	—	12	—	45,32	WS2376.J3760
<b>WA11425</b>	<b>30</b>	95,8	16	41	38,8	15,918	—	12,038	—	38,9	—
<b>WB01176</b>	<b>30</b>	97,5	23,6	35,1	38,8	15,008	—	—	—	—	—
<b>WB07381<sup>1)<sup>6)</sup></sup></b>	<b>30</b>	97,79	4,23	54,76	38,8	15,918	—	—	—	—	W2385-2.TJ1427
<b>WB05074</b>	<b>30</b>	98	17,1	42,1	38,8	15,918	—	—	—	—	F-110398
<b>WA01086</b>	<b>30</b>	98	17,1	42,1	38,8	15,918	—	—	—	—	—
<b>WB05092</b>	<b>30</b>	98	17,1	42,1	38,8	15,918	—	—	—	—	F-112009
<b>WB07151<sup>1)<sup>6)</sup></sup></b>	<b>30</b>	98	17,1	42,1	38,8	15,977	—	—	—	—	W6385
<b>WB17078<sup>6)</sup></b>	<b>30</b>	98,5	22,54	37,16	38,8	15,918	—	12	—	34,86	W2387S
<b>WB27131<sup>1)<sup>6)</sup></sup></b>	<b>30</b>	100,99	24,09	38,1	38,8	15,921	14,051	12,05	21,79	35,8	W6397-2S

<sup>1)</sup> Special shaft.

<sup>2)</sup> Flinger sleeve.

<sup>3)</sup> R-SAFE seal.

<sup>4)</sup> Rotary shaft seal.

<sup>5)</sup> No seal.


<sup>6)</sup> Special outer ring.

<sup>7)</sup> Rolling element sets laterally transposed.

# Water pump bearings

Double row

Ball/ball



WA, WB

**Dimension table** (continued) · Dimensions in mm

Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
WB17160 <sup>1)6)</sup>	30	101,5	17,59	45,11	38,8	15,989	—	12,089	—	42,81	W7399-2S
WB07079 <sup>1)6)</sup>	30	102	17,1	46,1	38,8	15,918	—	—	—	—	W2401-3
WB07152 <sup>1)6)</sup>	30	102	17,04	46,16	38,8	15,977	—	—	—	—	W6401-3
WB21780	30	105	15	51,2	38,8	15,918	12	12	14,5	48,9	—
WB07138 <sup>1)6)</sup>	30	105,4	20,39	46,21	38,8	15,918	—	—	—	—	W2415-1
WB07153 <sup>1)6)</sup>	30	105,4	20,39	46,21	38,8	15,977	—	—	—	—	W6415-1
WB07306 <sup>1)6)</sup>	30	105,66	31,93	34,93	38,8	15,918	—	—	—	—	W2416.T1447
WB05104	30	105,9	21,3	45,8	38,8	15,918	—	—	—	—	F-112045
WB07139 <sup>1)6)</sup>	30	105,97	20,74	46,43	38,8	15,918	—	—	—	—	W2417-2
WB17140 <sup>6)</sup>	30	105,99	30,09	37,1	38,8	15,918	—	12,007	—	34,8	W2417S
WB01158	30	106	20	47,16	38,84	15,918	—	—	—	—	—
WB12171	30	106	18,1	61	26,9	15,918	—	12,038	—	52,45	—
WB11136	30	109,5	25,12	45,54	38,84	15,918	—	12,038	—	42,22	—
WB07141 <sup>6)</sup>	30	109,52	14,72	56	38,8	15,918	—	—	—	—	W2431
WB07154 <sup>1)6)</sup>	30	110,39	21,45	50,14	38,8	15,977	—	—	—	—	W6434
WB07379 <sup>1)6)</sup>	30	110,39	21,45	50,14	38,8	15,918	—	—	—	—	W2434-1
WB07506 <sup>1)6)</sup>	30	103,17	23,5	40,87	38,8	15,918	—	—	—	—	W2406-1
WB07429 <sup>1)6)</sup>	30	113,19	33,44	40,95	38,8	15,918	—	—	—	—	W2445-5.T2425
WB07386 <sup>1)6)</sup>	30	113,51	27,49	47,22	38,8	15,918	—	—	—	—	W2446
WB05089 <sup>1)</sup>	30	115,5	36,7	40	38,8	15,008	—	—	—	—	F-112002
WB01006	30	115,75	26,95	50	38,8	15,918	—	—	—	—	—
WB07142 <sup>1)6)</sup>	30	119,04	37,4	42,84	38,8	15,918	—	—	—	—	W2468
WB05094 <sup>1)</sup>	30	119,1	37,4	42,9	38,8	15,918	—	—	—	—	F-112017
WB07143 <sup>1)6)</sup>	30	119,89	36,62	44,47	38,8	15,918	—	—	—	—	W2472
WB07443 <sup>1)6)</sup>	30	120,9	29,55	52,55	38,8	15,977	—	—	—	—	W6476
WB17144 <sup>6)</sup>	30	122,5	26,38	57,32	38,8	15,918	—	12,038	—	55,22	W2482S.J3177
WB07155 <sup>1)6)</sup>	30	123	19,09	65,11	38,8	15,977	—	—	—	—	W6484-1
WB07145 <sup>1)6)</sup>	30	123,19	19,49	64,9	38,8	15,918	—	—	—	—	W2485
WB07146 <sup>1)6)</sup>	30	123,67	31,84	53,03	38,8	15,918	—	—	—	—	W2486-2

<sup>1)</sup> Special shaft.

<sup>2)</sup> Flinger sleeve.

<sup>3)</sup> R-SAFE seal.

<sup>4)</sup> Rotary shaft seal.


<sup>5)</sup> No seal.

<sup>6)</sup> Special outer ring.

<sup>7)</sup> Rolling element sets laterally transposed.

# Water pump bearings

Double row  
Ball/ball



WA, WB

**Dimension table (continued) · Dimensions in mm**

Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
<b>WB17650<sup>6)</sup></b>	<b>30</b>	124,5	20,92	64,78	38,8	15,918	–	12,038	–	62,48	–
<b>WA11733<sup>3)</sup></b>	<b>30</b>	125,5	11,1	75,6	38,8	15,918	–	12	–	73,3	–
<b>WB05095<sup>1)</sup></b>	<b>30</b>	126,1	44,5	42,8	38,8	15,918	–	–	–	–	F-112022
<b>WB05096</b>	<b>30</b>	127,1	25,6	62,7	38,8	15,918	–	–	–	–	F-112023
<b>WB07156<sup>1)6)</sup></b>	<b>30</b>	127,79	25,9	63,09	38,8	15,977	–	–	–	–	W6503
<b>WB07157<sup>1)6)</sup></b>	<b>30</b>	128,98	31,84	58,34	38,8	15,977	–	–	–	–	W6507
<b>WB07161<sup>1)6)</sup></b>	<b>30</b>	132,13	40,27	53,06	38,8	15,989	–	–	–	–	W7520-2
<b>WB05097</b>	<b>30</b>	133	29,96	64,24	38,8	15,918	–	–	–	–	F-112025
<b>WB07147<sup>1)6)</sup></b>	<b>30</b>	133,9	25	70,1	38,8	15,918	–	–	–	–	W2527-2.T3706
<b>WB05098</b>	<b>30</b>	136,4	39,16	58,53	38,8	15,918	–	–	–	–	F-112027
<b>WB07158<sup>1)6)</sup></b>	<b>30</b>	136,4	39,16	58,44	38,8	15,977	–	–	–	–	W6537
<b>WB07458<sup>1)6)</sup></b>	<b>30</b>	138,11	40,97	58,34	38,8	15,977	–	–	–	–	W6543
<b>WB07159<sup>1)6)</sup></b>	<b>30</b>	142,87	40,12	63,95	38,8	15,977	–	–	–	–	W6562
<b>WB07148<sup>1)6)</sup></b>	<b>30</b>	151,59	23,84	88,95	38,8	15,918	–	–	–	–	W2596.T2556
<b>WB05099<sup>1)</sup></b>	<b>30</b>	161,9	58,4	64,7	38,8	15,918	–	–	–	–	F-112029
<b>WB07149<sup>1)6)</sup></b>	<b>30</b>	162,31	40,96	82,55	38,8	15,918	–	–	–	–	W2639.T2358
<b>WB07150<sup>1)6)</sup></b>	<b>30</b>	168,28	58,44	71,04	38,8	15,918	–	–	–	–	W2662.T1652
<b>WA21622.01<sup>3)</sup></b>	<b>34</b>	78	14,3	33,8	29,9	17,008	15,918	12,038	13,3	31,5	–
<b>WB21472.02</b>	<b>34</b>	78	14,3	33,8	29,9	17,008	15,918	12,038	13,3	31,5	–
<b>WB11272.01</b>	<b>34</b>	80	12,1	34	33,9	17,008	–	12,038	–	33	–
<b>WA11435.02<sup>3)</sup></b>	<b>34</b>	80	12,1	34	33,9	17,008	–	12,038	–	31,7	–
<b>WA11654<sup>3)</sup></b>	<b>34</b>	98	14	37,1	46,9	17,008	–	12,055	–	34,8	–
<b>WA11794<sup>3)</sup></b>	<b>34</b>	122	24	51,1	46,9	17,008	–	12,055	–	48,8	–

1) Special shaft.

2) Flinger sleeve.

3) R-SAFE seal.

4) Rotary shaft seal.

5) No seal.


6) Special outer ring.

7) Rolling element sets laterally transposed.

# Water pump bearings

Double row

Ball/ball



WA, WB

**Dimension table** (continued) · Dimensions in mm

Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
<b>WB11085.06<sup>2)</sup></b>	<b>36</b>	90,7	14	37,9	38,8	17,008	—	15,008	—	34	—
<b>WB11133.02</b>	<b>36</b>	92,5	17,8	35,9	38,8	17,008	—	15,008	—	34,5	—
<b>WB27065.01<sup>4)</sup></b>	<b>36</b>	96	17	42	37	20	15,918	15,918	17	41,6	—
<b>WB11066.01<sup>1)</sup></b>	<b>36</b>	104,5	49,6	2	52,9	23,502	16,984	—	8,5	—	—
<b>WB11081.01</b>	<b>36</b>	112	20	62,1	29,9	20	—	12,008	—	45,85	—
<b>WB21064.01<sup>1)</sup></b>	<b>36</b>	116,7	27,9	35,9	52,9	23,502	16,984	15,008	8,5	32,2	—
<b>WB11044.03<sup>1)</sup></b>	<b>36</b>	126,4	17,1	49,4	59,9	20,004	—	15,002	—	43,7	—
<b>WB21043.01</b>	<b>36</b>	135,2	25	50,3	59,9	20,004	15,944	15,002	8	41	—
<b>WB21049.01<sup>1)</sup></b>	<b>36</b>	145,7	33,3	64,4	48	20	14,984	15,002	14,7	63,4	—
<b>WB21109.01</b>	<b>36</b>	156,7	22,3	86,4	48	20	14,984	15,002	3,7	74,4	—
<b>WB21050.01<sup>1)</sup></b>	<b>36</b>	159,2	33,3	77,9	48	20	14,984	15,002	14,7	76,2	—
<b>WB07162<sup>1)6)</sup></b>	<b>38,1</b>	63,5	4,74	4,78	53,98	18,961	—	—	—	—	WK2250.T1428
<b>WB27251.01<sup>5)6)</sup></b>	<b>38,1</b>	105,76	39,64	39,22	26,9	19,861	15,861	13,776	39,54	12,7	—
<b>WB27395<sup>6)</sup></b>	<b>38,1</b>	112,67	28,59	42,8	41,28	18,961	15,918	15,918	25,4	40,5	WS2443
<b>WB17622<sup>6)</sup></b>	<b>38,1</b>	113	26,59	45,13	41,28	18,918	—	12,038	—	42,83	—
<b>WB17109<sup>6)</sup></b>	<b>38,1</b>	119,05	26,59	51,18	41,28	18,961	—	15,918	—	48,88	WS2468-2
<b>WB17088<sup>1)6)</sup></b>	<b>38,1</b>	120,5	25,8	40,72	53,98	19,012	—	12,089	—	38,42	WK6474-2D
<b>WB17311<sup>6)</sup></b>	<b>38,1</b>	121,69	30,09	50,32	41,28	18,961	—	12,038	—	48,02	WS2479
<b>WB27163<sup>6)</sup></b>	<b>38,1</b>	125,73	30,86	40,89	53,98	18,961	15,918	15,918	27,43	38,59	WK2495
<b>WB17313<sup>6)</sup></b>	<b>38,1</b>	125,98	30,6	41,4	53,98	18,961	—	15,918	—	39,1	WK2496-2
<b>WB17089<sup>1)6)</sup></b>	<b>38,1</b>	127	31,37	41,65	53,98	19,012	—	15,977	—	39,35	WK6500-2
<b>WB17164<sup>6)</sup></b>	<b>38,1</b>	127	31,36	41,66	53,98	18,961	—	15,918	—	39,36	WK2500-2
<b>WB17165<sup>6)</sup></b>	<b>38,1</b>	127,25	29,13	44,14	53,98	18,961	—	15,918	—	41,84	WK2501
<b>WB27090<sup>1)6)</sup></b>	<b>38,1</b>	127,48	31,03	42,47	53,98	19,012	15,918	15,977	13,72	40,17	WK6501-3B
<b>WB27166<sup>6)</sup></b>	<b>38,1</b>	127,48	31,03	42,47	53,98	18,961	15,918	15,918	13,72	40,17	WK2501-3
<b>WB15100</b>	<b>38,1</b>	131,3	28,37	48,95	53,98	18,961	—	15,918	—	44,68	F-112032
<b>WB15101<sup>2)</sup></b>	<b>38,1</b>	131,6	24,47	53,15	53,98	18,961	—	15,918	—	49,1	F-112033
<b>WB17091<sup>1)6)</sup></b>	<b>38,1</b>	134,87	37,34	43,55	53,98	19,012	—	15,977	—	41,25	WK6531

<sup>1)</sup> Special shaft.

<sup>2)</sup> Flinger sleeve.

<sup>3)</sup> R-SAFE seal.

<sup>4)</sup> Rotary shaft seal.


<sup>5)</sup> No seal.

<sup>6)</sup> Special outer ring.

<sup>7)</sup> Rolling element sets laterally transposed.

# Water pump bearings

Double row  
Ball/ball



WA, WB

**Dimension table (continued) · Dimensions in mm**

Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
WB17092 <sup>1)6)</sup>	38,1	135,64	31,88	49,78	53,98	19,012	—	15,977	—	47,48	WK6534
WB17093 <sup>1)6)</sup>	38,1	141,98	31,75	56,25	53,98	19,012	—	15,977	—	53,95	WK6559-2
WB27094 <sup>1)6)</sup>	38,1	143,48	30,83	58,67	53,98	19,012	15,918	15,977	12,24	56,37	WK6564-6B
WB27167 <sup>6)</sup>	38,1	143,48	30,83	58,67	53,98	18,961	15,918	15,918	12,24	56,37	WK2564-6/WK2564-10
WB17168 <sup>6)</sup>	38,1	144,15	32,47	57,7	53,98	18,961	—	12,038	—	55,4	WK2567D.M3564
WB27263 <sup>6)</sup>	38,1	146,05	36,32	55,75	53,98	18,961	15,918	15,918	33	53,45	WK2575-4
WB27466 <sup>6)</sup>	38,1	148,84	41,04	53,82	53,98	18,961	15,918	15,918	35,2	51,52	WK2586
WB15102	38,1	150,5	34,92	61,6	53,98	18,961	—	15,918	—	57,3	F-112038
WB07099 <sup>1)6)</sup>	38,1	152,4	34,93	63,49	53,98	19,037	—	—	—	—	WK8600.T1617
WB27084 <sup>6)</sup>	38,1	152,4	35,56	62,86	53,98	18,961	15,918	15,918	15,26	60,56	WK2600
WB17085 <sup>6)</sup>	38,1	153,42	45,72	53,72	53,98	18,961	—	15,918	—	51,42	WK2604
WB27086 <sup>6)</sup>	38,1	154,23	29,75	70,5	53,98	18,961	15,939	15,939	8,9	68,2	WK2607A
WB17096 <sup>6)</sup>	38,1	156,59	39,64	62,97	53,98	19,012	—	15,977	—	60,67	WK6616-2
WB17392 <sup>6)</sup>	38,1	156,6	39,62	63	53,98	18,961	—	15,918	—	60,7	WK2616-2
WB27097 <sup>1)6)</sup>	38,1	157,99	46,74	57,27	53,98	19,012	15,918	15,977	14,8	54,97	WK6622B
WB27087 <sup>6)</sup>	38,1	161,93	35,56	72,39	53,98	18,961	15,918	15,918	15,14	70,09	WK2637
WB27098 <sup>1)6)</sup>	38,1	161,93	35,56	72,39	53,98	19,012	15,918	15,977	15,14	70,09	WK6637B

1) Special shaft.

2) Flinger sleeve.

3) R-SAFE seal.

4) Rotary shaft seal.

5) No seal.


6) Special outer ring.

7) Rolling element sets laterally transposed.

# Water pump bearings

Double row

Ball/ball



WA, WB

**Dimension table** (continued) · Dimensions in mm

Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
<b>WB11269.02<sup>1)</sup></b>	<b>40</b>	53,7	10,2	1,6	41,9	24,5	18	—	7,2	—	—
<b>WB11213.01</b>	<b>40</b>	79,7	10	47,7	22	24,502	—	12,038	—	45,7	—
<b>WB01634.01<sup>1)</sup></b>	<b>40</b>	81,5	20,3	1,3	59,9	24,5	—	—	—	—	—
<b>WB11283.01</b>	<b>40</b>	84	18	44	22	24,502	—	12,038	—	43	—
<b>WB11148.03</b>	<b>40</b>	84,5	9,5	35,1	39,9	24,502	—	12,038	—	34	—
<b>WB01077<sup>2)</sup></b>	<b>40</b>	91	6,1	35	49,9	20,004	—	—	—	—	—
<b>WB11130.01<sup>1)</sup></b>	<b>40</b>	96,5	22	49,5	25	24,5	—	15,002	—	47,5	—
<b>WB01181<sup>1)</sup></b>	<b>40</b>	101	22	17,1	61,9	20,004	—	—	—	—	—
<b>WB11264</b>	<b>40</b>	110	24	44	42	20,002	—	12,038	—	40,3	—
<b>WB11180.04<sup>1)</sup></b>	<b>40</b>	112	36,1	36	39,9	24,5	—	12,038	—	34	—
<b>WB11148.02<sup>1)</sup></b>	<b>40</b>	114	19,1	55	39,9	24,502	—	12,038	—	53	—
<b>WB21116.04</b>	<b>40</b>	117,5	24	51,5	42	24,5	20,002	15,002	23	47,8	—
<b>WB21289.01</b>	<b>40</b>	117,5	23,5	51	43	24,5	20,002	15,002	23	47,8	—
<b>WB21219.01<sup>1)</sup></b>	<b>40</b>	129,7	33	62,8	33,9	24,5	—	12,038	23,2	60	—
<b>WB21053</b>	<b>40</b>	135,2	25	48,3	61,9	20,004	15,944	15,002	8	41	—
<b>WB11091.05<sup>1)</sup></b>	<b>40</b>	135,7	18,8	56,9	60	24,5	—	15,002	—	53,2	—
<b>WB21110.01</b>	<b>40</b>	140,9	24	56,9	60	24,5	20,002	15,002	23	53,2	—
<b>WB11000</b>	<b>40</b>	147	35,5	51,5	60	20,002	—	15,002	—	47,8	—
<b>WB21114<sup>1)</sup></b>	<b>40</b>	177,6	23,5	92,2	61,9	20,004	15,944	15,002	6	80,7	—
<b>WB21129</b>	<b>40</b>	177,6	23,5	92,2	61,9	20,004	15,944	15,002	6	80,7	—

<sup>1)</sup> Special shaft.

<sup>2)</sup> Flinger sleeve.

<sup>3)</sup> R-SAFE seal.

<sup>4)</sup> Rotary shaft seal.


<sup>5)</sup> No seal.

<sup>6)</sup> Special outer ring.

<sup>7)</sup> Rolling element sets laterally transposed.

# Water pump bearings

Double row  
Ball/ball



WA, WB

**Dimension table (continued) · Dimensions in mm**

Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
<b>WB11810<sup>1)</sup></b>	<b>47</b>	40,3	2,7	—	37,6	28,4	24,4	—	2,7	—	—
<b>WB11601<sup>1)</sup></b>	<b>47</b>	43,6	23	—	20,6	28,4	24,5	—	—	—	—
<b>WB11602<sup>1)</sup></b>	<b>47</b>	60,6	23	—	37,6	28,4	24,5	—	—	—	—
<b>WB05115<sup>1) 5) 6)</sup></b>	<b>47</b>	76	20	8	48	26	—	—	—	—	F-226707.3
<b>WB21320</b>	<b>47</b>	93	16	42,1	34,9	24	15,918	12,038	15	40	—
<b>WB11128<sup>1)</sup></b>	<b>47</b>	111,2	1	62,2	48	26	—	15	—	41	—
<b>WB21127</b>	<b>47</b>	135,2	25	48,3	61,9	26,004	15,944	15,002	8	41	—
<b>WB11113<sup>1)</sup></b>	<b>47</b>	137,5	1	61,6	74,9	26	—	15,002	—	44	—
<b>WB11146<sup>1)</sup></b>	<b>47</b>	139,2	3,8	64,9	70,5	26	—	15,002	—	43,7	—
<b>WB21115<sup>1)</sup></b>	<b>47</b>	154,2	18,8	64,9	70,5	26	24,5	15,002	18,8	43,7	—
<b>WB21052.01<sup>1)</sup></b>	<b>47</b>	156,7	26	62,8	67,9	20,004	15,944	15,002	6,5	20	F-87971.100
<b>WB11879</b>	<b>47,625</b>	161,28	46,45	45	69,85	25,4	—	12,038	—	43,9	—
<b>WB11881<sup>1)</sup></b>	<b>47,625</b>	170	46,45	53,7	69,85	25,4	—	12,038	—	52,6	—
<b>WB21388.08<sup>1) 4)</sup></b>	<b>52</b>	113,25	22,25	44,1	46,9	25	—	12,038	10	42	—
<b>WB11730</b>	<b>52</b>	156	36,27	51	68,73	25,017	—	15,918	—	48,5	—
<b>WA11665.01<sup>4)</sup></b>	<b>55</b>	130	32	50,65	47,35	30	—	15,01	—	47,8	WS2511.H93/WS2511
<b>WA21782<sup>4)</sup></b>	<b>55</b>	144	20	56	68	30	25	19	19	53,7	—

1) Special shaft.

2) Flinger sleeve.

3) R-SAFE seal.

4) Rotary shaft seal.


5) No seal.

6) Special outer ring.

7) Rolling element sets laterally transposed.

# Water pump bearings

Double row  
Roller/ball



WF, WR, WT

**Dimension table** · Dimensions in mm

Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
<b>WT01779</b>	<b>24</b>	70,9	16	23	31,9	12,038	—	—	—	—	—
<b>WT01504<sup>1)</sup></b>	<b>24</b>	80	16,6	36,5	26,9	12,008	—	—	—	—	—
<b>WT01579</b>	<b>24</b>	86	16	38,1	31,9	12,038	—	—	—	—	—
<b>WR07671<sup>4)</sup></b>	<b>30</b>	51	17	4	30	15,918	—	—	—	—	—
<b>WF02065</b>	<b>30</b>	53,3	13,5	1	38,8	15,918	—	—	—	—	—
<b>WR11837<sup>3)</sup></b>	<b>30</b>	67,3	13,5	30,9	22,9	15,918	—	12	—	28,6	—
<b>WR04037</b>	<b>30</b>	68,39	25	4,59	38,8	15,918	—	—	—	—	RW306206-LB6G43
<b>WR01022.01<sup>2)7)</sup></b>	<b>30</b>	69,3	26	4,5	38,8	15,918	—	—	—	—	—
<b>WT11867<sup>3)</sup></b>	<b>30</b>	72,4	11,5	31	29,9	15,918	—	12,055	—	28,7	—
<b>WR17628<sup>6)</sup></b>	<b>30</b>	73	14	32	27	15,918	—	12,038	—	29,7	—
<b>WR01614.01<sup>6)</sup></b>	<b>30</b>	76	29,9	2,2	43,9	15,918	—	—	—	—	—
<b>WR17058<sup>6)7)</sup></b>	<b>30</b>	76	16,3	32,7	27	15,918	—	12,038	—	30,7	WNS2299-2
<b>WR17059<sup>6)</sup></b>	<b>30</b>	76	13,96	35,04	27	15,918	—	12,038	—	32,74	WNS2299-3
<b>WT11546.03<sup>3)</sup></b>	<b>30</b>	77,95	15	33,05	29,9	15,918	—	12	—	30,45	—
<b>WT11674.08</b>	<b>30</b>	78	15,1	33	29,9	15,918	—	12,038	—	32	—
<b>WR14008</b>	<b>30</b>	78,9	15,2	33,8	29,9	15,918	—	12	—	31,5	—
<b>WR14008.01<sup>1)</sup></b>	<b>30</b>	78,9	15,2	33,8	29,9	15,918	—	12	—	31,5	—
<b>WT11640</b>	<b>30</b>	78,9	15,2	33,8	29,9	15,918	—	12,038	—	31,5	—
<b>WR11702<sup>3)7)</sup></b>	<b>30</b>	79,12	14,1	35,12	29,9	15,918	—	12	—	32,82	—
<b>WR17014<sup>6)</sup></b>	<b>30</b>	79,26	13,6	35,76	29,9	15,918	—	12,038	—	33,46	WNS2312.J3413
<b>WR11369.02<sup>3)</sup></b>	<b>30</b>	79,3	12,1	37,3	29,9	15,918	—	12	—	33,2	—
<b>WT11816.01<sup>3)7)</sup></b>	<b>30</b>	79,5	16,1	33,5	29,9	15,918	—	12,038	—	31,2	—
<b>WR14033.01</b>	<b>30</b>	79,8	15,5	41,4	22,9	15,918	—	12	—	39,1	RW306212-LB6G43
<b>WF01138.02</b>	<b>30</b>	80	14,1	38	27,9	15,918	—	—	—	—	—
<b>WF11567.01<sup>3)7)</sup></b>	<b>30</b>	80	17	31,1	31,9	15,918	—	12,038	—	28,8	—
<b>WR17258<sup>6)7)</sup></b>	<b>30</b>	80,5	19,24	34,26	27	15,918	—	12,038	—	31,96	WNS2316
<b>WR17060<sup>6)</sup></b>	<b>30</b>	81,51	16,18	38,33	27	15,918	—	12,038	—	36,03	WNS2320
<b>WR11072.01</b>	<b>30</b>	81,7	13,7	34,1	33,9	15,918	—	12,038	—	33,4	—

<sup>1)</sup> Special shaft.

<sup>2)</sup> Flinger sleeve.

<sup>3)</sup> R-SAFE seal.

<sup>4)</sup> Rotary shaft seal.


<sup>5)</sup> No seal.

<sup>6)</sup> Special outer ring.

<sup>7)</sup> Rolling element sets laterally transposed.

# Water pump bearings

Double row  
Roller/ball



WF, WR, WT

**Dimension table (continued) · Dimensions in mm**

Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
<b>WT11422<sup>3)</sup></b>	<b>30</b>	82	14	34,1	33,9	15,918	—	12,038	—	32,1	—
<b>WT11422.02</b>	<b>30</b>	82	14	34,1	33,9	15,918	—	12,038	—	32,1	—
<b>WT11751<sup>7)</sup></b>	<b>30</b>	82,15	15	37,25	29,9	15,918	—	12,038	—	34,95	—
<b>WR07302<sup>6)</sup></b>	<b>30</b>	82,55	18,26	37,29	27	15,918	—	—	—	—	WNS2325-1.J3770
<b>WR17651</b>	<b>30</b>	82,75	15,5	37,25	30	15,918	—	12,038	—	34,95	—
<b>WR17315.01<sup>6)</sup></b>	<b>30</b>	84,26	15	42,26	27	15,918	—	12,038	—	39,96	—
<b>WT11649<sup>3)</sup></b>	<b>30</b>	84,3	20,8	33,6	29,9	15,918	—	12,008	—	31,5	—
<b>WR17011<sup>6)</sup></b>	<b>30</b>	84,63	17,27	40,36	27	15,918	—	12,038	—	38,06	WNS2333
<b>WR11515.03<sup>6)</sup></b>	<b>30</b>	85	17	34,2	33,8	15,918	—	12,038	—	33	—
<b>WT11862<sup>3)</sup></b>	<b>30</b>	85	17	38,1	29,9	15,918	—	12	—	35,8	—
<b>WR17061<sup>6)</sup></b>	<b>30</b>	85,1	14,16	43,94	27	15,918	—	12,038	—	41,64	WNS2335
<b>WR17056<sup>6)</sup></b>	<b>30</b>	85,82	14,5	41,32	30	15,918	—	12,038	—	39,02	WNS2337-1
<b>WR01345.02<sup>6)</sup></b>	<b>30</b>	86	21,1	5	59,9	15,918	—	—	—	—	—
<b>WT11974<sup>3)</sup></b>	<b>30</b>	86	17	39,1	29,9	15,918	—	12,008	—	36,9	—
<b>WT11786<sup>3)</sup></b>	<b>30</b>	86,05	14,5	41,65	29,9	15,918	—	12,038	—	39,35	—
<b>WF11137.04</b>	<b>30</b>	86,5	13,5	34,2	38,8	15,918	—	12,038	—	32,45	F-228188
<b>WF11137.06<sup>3)</sup></b>	<b>30</b>	86,5	13,5	34,2	38,8	15,918	—	12,038	—	32,2	—
<b>WR17564<sup>6)</sup></b>	<b>30</b>	86,7	19,31	40,39	27	15,918	—	12,038	—	38,09	—
<b>WF11151</b>	<b>30</b>	86,8	13,4	41,5	31,9	15,918	—	12,055	—	40,3	—
<b>WF11293</b>	<b>30</b>	86,8	13,3	41,6	31,9	15,918	—	12,038	—	39,9	—
<b>WR17008<sup>6)</sup></b>	<b>30</b>	87	17,27	42,73	27	15,918	—	12,038	—	40,43	WNS2342-3
<b>WR11829<sup>3)</sup></b>	<b>30</b>	87,15	18,3	38,95	29,9	15,918	—	12	—	36,65	—
<b>WT11621<sup>3)</sup></b>	<b>30</b>	87,3	20,8	36,6	29,9	15,918	—	12,008	—	34,3	—
<b>WR14012</b>	<b>30</b>	87,5	13,5	38	36	15,918	—	12	—	35,7	RW306211-LBF6G43
<b>WR14012.01<sup>3)</sup></b>	<b>30</b>	87,5	13,5	38	36	15,918	—	12	—	35,7	—
<b>WR17324<sup>6)</sup><sup>7)</sup></b>	<b>30</b>	88,43	16,3	45,13	27	15,918	—	12,038	—	42,83	WNS2348-6
<b>WR17062<sup>1)</sup><sup>6)</sup><sup>7)</sup></b>	<b>30</b>	88,5	19,24	42,26	27	15,918	—	12,038	—	39,96	WNS2348-5
<b>WF05112.02<sup>1)</sup></b>	<b>30</b>	88,75	19,35	33	36,4	16	—	—	—	—	F-93024

<sup>1)</sup> Special shaft.

<sup>2)</sup> Flinger sleeve.

<sup>3)</sup> R-SAFE seal.

<sup>4)</sup> Rotary shaft seal.


<sup>5)</sup> No seal.

<sup>6)</sup> Special outer ring.

<sup>7)</sup> Rolling element sets laterally transposed.

# Water pump bearings

Double row  
Roller/ball



WF, WR, WT

**Dimension table** (continued) · Dimensions in mm

Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
<b>WR17344</b>	<b>30</b>	89,66	16,45	41,73	31,48	15,918	—	12,038	—	39,43	WNS2353
<b>WR17002<sup>3)4)</sup></b>	<b>30</b>	89,75	17,34	38,41	34	15,918	—	12,038	—	36,11	—
<b>WR11036.02</b>	<b>30</b>	90	18,1	33,1	38,8	15,007	—	12,038	—	32	—
<b>WR17015<sup>6)</sup></b>	<b>30</b>	90,83	21,64	42,19	27	15,918	—	12,038	—	40,19	—
<b>WR11450.04<sup>3)4)</sup></b>	<b>30</b>	91	13,85	43,15	34	15,918	—	12	—	40,85	—
<b>WR11450.06<sup>3)</sup></b>	<b>30</b>	91	13,85	43,15	34	15,918	—	12	—	40,85	—
<b>WF11284.03<sup>3)</sup></b>	<b>30</b>	91,5	13,3	34,3	43,9	15,918	—	12,038	—	32,2	—
<b>WF11586<sup>3)6)</sup></b>	<b>30</b>	91,5	11,6	34,2	45,7	15,918	—	12,038	—	32,2	—
<b>WR11569.02</b>	<b>30</b>	92,1	17,69	35,61	38,8	15,918	—	12	—	33,31	—
<b>WR17004<sup>6)</sup></b>	<b>30</b>	92,5	15	38,7	38,8	15,918	—	12	—	36,4	WN2364-7S.H94
<b>WR24032</b>	<b>30</b>	92,5	16,5	37,2	38,8	15,918	12	12	14	34,9	RCHL-RW306201-LB6G43
<b>WR07268<sup>6)</sup></b>	<b>30</b>	93,47	18,26	48,21	27	15,918	—	—	—	—	WNS2367.J3795
<b>WR11368.02<sup>3)</sup></b>	<b>30</b>	93,9	17,4	37,7	38,8	15,918	—	12	—	35	—
<b>WR17119<sup>6)</sup></b>	<b>30</b>	93,95	14,99	40,16	38,8	15,918	—	12,038	—	37,86	WN2369
<b>WF11551<sup>3)</sup></b>	<b>30</b>	94	17,1	38,1	38,8	15,918	—	12,008	—	35,9	—
<b>WR15129</b>	<b>30</b>	94,35	17,5	38,1	38,8	15,918	—	12,008	—	34,95	—
<b>WF01011.02</b>	<b>30</b>	94,5	15,8	39,9	38,8	15,008	—	—	—	—	—
<b>WT11075.09</b>	<b>30</b>	94,5	14,6	41,1	38,8	15,008	—	12	—	40	—
<b>WR11599.01<sup>1)3)</sup></b>	<b>30</b>	94,9	18,3	46,7	29,9	15,918	—	12	—	33,5	—
<b>WR07293<sup>1)6)</sup></b>	<b>30</b>	95,45	14,33	42,32	38,8	15,918	—	—	—	—	WN2375-3
<b>WR17040<sup>6)</sup></b>	<b>30</b>	95,45	14,33	42,32	38,8	15,918	—	12,038	—	40,02	WN2375-4S
<b>WF11131.02</b>	<b>30</b>	96,3	14,6	47,9	33,8	15,918	—	12,038	—	46,4	—
<b>WR11037.02</b>	<b>30</b>	96,4	18,1	39,5	38,8	15,008	—	12,067	—	36,6	—
<b>WF01386.01</b>	<b>30</b>	98	17,1	42,1	38,8	15,918	—	—	—	—	—
<b>WF11017.05<sup>3)</sup></b>	<b>30</b>	98	17,1	42,1	38,8	15,918	—	12,038	—	40,1	—
<b>WF11017.06</b>	<b>30</b>	98	17,1	42,1	38,8	15,918	—	12,038	—	40,1	—
<b>WF11818<sup>3)</sup></b>	<b>30</b>	98	17,1	42,1	38,8	15,918	—	12,055	—	39,8	—
<b>WR05058.01</b>	<b>30</b>	98	17,1	42,1	38,8	15,918	—	—	—	—	F-110557.03

<sup>1)</sup> Special shaft.

<sup>2)</sup> Flinger sleeve.

<sup>3)</sup> R-SAFE seal.

<sup>4)</sup> Rotary shaft seal.


<sup>5)</sup> No seal.

<sup>6)</sup> Special outer ring.

<sup>7)</sup> Rolling element sets laterally transposed.

# Water pump bearings

Double row  
Roller/ball



WF, WR, WT

**Dimension table (continued) · Dimensions in mm**

Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
<b>WR11930</b>	<b>30</b>	98	16,5	51,6	29,9	15,918	–	12	–	49,3	–
<b>WF11728</b>	<b>30</b>	98,21	13,5	45,91	38,8	15,918	–	12,038	–	43,61	–
<b>WT11934.01</b>	<b>30</b>	98,21	13,5	45,91	38,8	15,918	–	12,038	–	43,61	–
<b>WR24015</b>	<b>30</b>	98,5	17,1	51,5	29,9	15,918	12	12	15	49,2	RCHL-RW306221-LCF5G75
<b>WR17041<sup>6)</sup></b>	<b>30</b>	98,79	18,53	41,46	38,8	15,918	–	12,038	–	39,16	WN2388-2S
<b>WT01300.01<sup>1)</sup></b>	<b>30</b>	99,5	15,7	39,9	43,9	15,008	–	–	–	–	–
<b>WR17043</b>	<b>30</b>	99,85	10,94	50,11	38,8	15,918	–	12,038	–	47,81	WN2393S
<b>WR11692<sup>7)</sup></b>	<b>30</b>	100	19,4	41,8	38,8	15,918	–	12	–	39,5	–
<b>WR11304.01<sup>3)</sup></b>	<b>30</b>	100,75	15,5	46,45	38,8	15,918	–	12	–	44,1	–
<b>WR11304.03</b>	<b>30</b>	100,75	15,5	46,45	38,8	15,918	–	12	–	44,1	–
<b>WR07042.01<sup>1)</sup></b>	<b>30</b>	102	17	46,2	38,8	15,918	–	–	–	–	WN2401-5
<b>WR17257</b>	<b>30</b>	102,21	23,55	39,86	38,8	15,918	–	12,038	–	37,56	–
<b>WR14000</b>	<b>30</b>	103	16,5	47,7	38,8	15,918	–	12	–	45,4	RCHL-RW306203-LB6G43
<b>WR14000.01<sup>3)</sup></b>	<b>30</b>	103	16,5	47,7	38,8	15,918	–	12	–	45,4	RCHL-RW306203-LC5F4L5G68
<b>WR17121.01<sup>6)</sup></b>	<b>30</b>	103	16,5	47,7	38,8	15,918	–	12	–	45,4	–
<b>WR07044<sup>1)</sup><sup>6)</sup></b>	<b>30</b>	103,12	27,98	36,34	38,8	15,918	–	–	–	–	WN2406-9
<b>WR17045<sup>1)</sup></b>	<b>30</b>	103,5	19,54	45,16	38,8	15,918	–	12,038	–	42,86	WN2407-5S.T3377
<b>WT11560<sup>1)</sup></b>	<b>30</b>	103,5	19,6	45,1	38,8	15,918	–	12,038	–	43,1	–
<b>WR05132</b>	<b>30</b>	104,1	19,1	50,6	34,4	15,918	–	–	–	–	–
<b>WR07294<sup>1)</sup><sup>6)</sup></b>	<b>30</b>	105,4	20,3	46,3	38,8	15,918	–	–	–	–	WN2415
<b>WF01013.02<sup>1)</sup></b>	<b>30</b>	105,75	14,35	39,5	51,9	15,008	–	–	–	–	–
<b>WR05110<sup>2)</sup></b>	<b>30</b>	105,9	21,4	45,7	38,8	15,918	–	–	–	–	F-45943
<b>WF01016.07</b>	<b>30</b>	105,95	19,65	47,5	38,8	16	–	–	–	–	–
<b>WR11034.03</b>	<b>30</b>	106	27,7	39,5	38,8	15,008	–	12,067	–	36,6	–
<b>WR11040.01<sup>2)</sup></b>	<b>30</b>	106	23,1	44,1	38,8	15,918	–	12,038	–	39,6	–
<b>WR17047<sup>6)</sup></b>	<b>30</b>	106,5	22,06	45,64	38,8	15,918	–	12,038	–	43,34	WN2419S

<sup>1)</sup> Special shaft.

<sup>2)</sup> Flinger sleeve.

<sup>3)</sup> R-SAFE seal.

<sup>4)</sup> Rotary shaft seal.


<sup>5)</sup> No seal.

<sup>6)</sup> Special outer ring.

<sup>7)</sup> Rolling element sets laterally transposed.

# Water pump bearings

Double row  
Roller/ball



WF, WR, WT

**Dimension table** (continued) · Dimensions in mm

Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
<b>WR17585.01<sup>6)</sup></b>	<b>30</b>	106,75	31,9	47,85	27	15,918	—	12,038	—	45,55	—
<b>WF15047<sup>6)</sup></b>	<b>30</b>	108,3	18,5	51	38,8	15,918	—	12,038	—	48	F-110734
<b>WF15047.07<sup>6)</sup></b>	<b>30</b>	108,3	18,5	51	38,8	15,918	—	12,038	—	48	—
<b>WT21639.02</b>	<b>30</b>	108,5	22,1	47,6	38,8	15,918	12,038	12,038	21	45,3	—
<b>WR14018</b>	<b>30</b>	108,8	20,5	49,5	38,8	15,918	—	12	—	47,2	RCHL-RW306215FS21-LCF5G75
<b>WR15093<sup>1)</sup></b>	<b>30</b>	109,05	33,05	41,5	34,5	15,918	14,987	—	30,85	—	F-112013
<b>WF01009.04</b>	<b>30</b>	109,25	17,85	39,5	51,9	15,008	—	—	—	—	—
<b>WF05136.03<sup>1)</sup></b>	<b>30</b>	109,25	17,85	39,5	51,9	15,008	—	—	—	—	—
<b>WF11337.01</b>	<b>30</b>	109,25	17,85	39,5	51,9	15,008	—	12,038	—	38	—
<b>WR14019<sup>7)</sup></b>	<b>30</b>	109,9	29,3	41,8	38,8	15,918	—	12	—	39,5	RCHL-RW306216-LCF5G75
<b>WF11107.02</b>	<b>30</b>	110	21,7	44,4	43,9	15,918	—	12,038	—	42,8	—
<b>WT11694</b>	<b>30</b>	110	21,7	49,5	38,8	15,918	—	12,038	—	47,2	—
<b>WR11159.02</b>	<b>30</b>	110,3	18,9	39,5	51,9	15,008	—	12,067	—	37,5	—
<b>WR07009<sup>1)6)</sup></b>	<b>30</b>	110,39	21,45	50,14	38,8	15,918	—	—	—	—	WN2434
<b>WR17049<sup>6)</sup></b>	<b>30</b>	110,39	21,45	50,14	38,8	15,918	—	12,038	—	47,84	WN2434-4S
<b>WT11609</b>	<b>30</b>	113,9	22,5	52,6	38,8	15,918	—	12,038	—	50,1	—
<b>WR07352<sup>6)</sup></b>	<b>30</b>	114	19,1	56,1	38,8	15,918	—	—	—	—	WN2448-1.H104
<b>WT11588.03</b>	<b>30</b>	114,4	20,4	55,2	38,8	15,008	—	13,038	—	10	—
<b>WR11856<sup>3)</sup></b>	<b>30</b>	115	20,7	55,5	38,8	15,918	—	12	—	53,2	—
<b>WF05106.01<sup>1)</sup></b>	<b>30</b>	115,5	36,8	39,9	38,8	15,008	—	—	—	—	F-113080
<b>WF01014.02<sup>2)</sup></b>	<b>30</b>	115,75	17,85	46	51,9	16	—	—	—	—	—
<b>WR14009</b>	<b>30</b>	116,95	17	61,15	38,8	15,918	—	12,038	—	58,85	RCHL-RW306223-LC5G68
<b>WR17454<sup>6)</sup></b>	<b>30</b>	117,98	24,58	54,6	38,8	15,918	—	12,038	—	52,3	—
<b>WF11763.01</b>	<b>30</b>	118,5	27,1	39,5	51,9	15,008	—	12,067	—	36,6	—
<b>WF11039.02</b>	<b>30</b>	118,9	23,5	39,5	55,9	15,008	—	12,067	—	36,6	—
<b>WR17295<sup>6)</sup></b>	<b>30</b>	120	20,7	60,5	38,8	15,918	—	12,038	—	58,2	WN2472S
<b>WR17050<sup>6)</sup></b>	<b>30</b>	121,8	31,51	51,49	38,8	15,918	—	12,038	—	49,19	WN2479S.RIT
<b>WT01866</b>	<b>30</b>	121,8	27	56	38,8	16	—	—	—	—	—

<sup>1)</sup> Special shaft.

<sup>2)</sup> Flinger sleeve.

<sup>3)</sup> R-SAFE seal.

<sup>4)</sup> Rotary shaft seal.


<sup>5)</sup> No seal.

<sup>6)</sup> Special outer ring.

<sup>7)</sup> Rolling element sets laterally transposed.

# Water pump bearings

Double row  
Roller/ball



WF, WR, WT

**Dimension table (continued) · Dimensions in mm**

Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
<b>WR05091<sup>2)</sup></b>	<b>30</b>	121,9	37,4	45,7	38,8	15,912	—	—	—	—	—
<b>WR05108<sup>1)2)</sup></b>	<b>30</b>	121,9	37,4	45,7	38,8	15,918	—	—	—	—	—
<b>WR11796</b>	<b>30</b>	121,9	17,5	65,6	38,8	15,918	—	12,04	—	48,6	—
<b>WR11845</b>	<b>30</b>	124,66	22,06	72,6	30	15,918	—	12,038	—	49,05	—
<b>WR17557<sup>6)</sup></b>	<b>30</b>	125	20,5	65,7	38,8	15,918	—	12,038	—	39,11	—
<b>WR01008.02<sup>1)</sup></b>	<b>30</b>	125,25	17,75	55,5	51,9	15,008	—	—	—	—	—
<b>WR05105</b>	<b>30</b>	127,43	22	66,63	38,8	15,918	—	—	—	—	F-110023C
<b>WR15157</b>	<b>30</b>	127,5	22,1	66,6	38,8	15,918	—	12,038	—	51,43	—
<b>WR11360.01</b>	<b>30</b>	127,8	23,4	65,6	38,8	15,918	—	12,04	—	48,6	—
<b>WR17286<sup>1)6)</sup></b>	<b>30</b>	136,39	20,54	77,05	38,8	15,918	—	12,038	—	50,5	WN2536S
<b>WR07051<sup>1)6)</sup></b>	<b>30</b>	139	23,11	77,09	38,8	15,918	—	—	—	—	WN2547
<b>WR17667<sup>6)</sup></b>	<b>30</b>	142	24,25	78,95	38,8	15,918	—	12,038	—	47,9	—
<b>WF11032.03<sup>1)2)</sup></b>	<b>30</b>	142,65	56,25	47,6	38,8	16	15,008	—	52,15	—	—
<b>WR01019.01<sup>6)</sup></b>	<b>30</b>	144	46,1	38	59,9	15,918	—	—	—	—	—
<b>WR07052<sup>1)6)</sup></b>	<b>30</b>	147,11	26	82,31	38,8	15,918	—	—	—	—	WN2579
<b>WR11871<sup>6)</sup></b>	<b>30</b>	166,03	23,15	115,88	27	15,918	—	12,038	—	88	—
<b>WT22096.03</b>	<b>34</b>	90,8	22	34,9	33,9	17,008	15,918	12,055	20,5	32,6	—
<b>WT12068</b>	<b>34</b>	96,4	19,5	41	35,9	17,008	—	12,038	—	38,7	—
<b>WF21222.03</b>	<b>34</b>	98	17,1	42,1	38,8	17,008	15,918	12,038	16	40,6	—
<b>WT11593</b>	<b>34</b>	104,08	19	46,28	38,8	17,008	—	15,918	—	43,8	—
<b>WT11628</b>	<b>34</b>	104,9	17,5	48,6	38,8	17,008	—	12,038	—	46	—
<b>WT11685.01<sup>3)</sup></b>	<b>34</b>	105,5	21,1	48,5	35,9	17,008	—	12,038	—	46,2	—
<b>WF21211.02</b>	<b>34</b>	111	24,1	40	46,9	17,008	15,008	12,055	23	39	—
<b>WT11590.01<sup>3)</sup></b>	<b>34</b>	111	21	38,1	51,9	17,008	—	12	—	35,5	—
<b>WT11726</b>	<b>34</b>	114,58	19	56,78	38,8	17,008	—	15,918	—	54,48	—
<b>WT11079.02</b>	<b>34</b>	120,5	28,8	44,8	46,9	17,008	—	12,038	—	39	—

<sup>1)</sup> Special shaft.

<sup>2)</sup> Flinger sleeve.

<sup>3)</sup> R-SAFE seal.

<sup>4)</sup> Rotary shaft seal.

<sup>5)</sup> No seal.


<sup>6)</sup> Special outer ring.

<sup>7)</sup> Rolling element sets laterally transposed.

# Water pump bearings

Double row

Roller/ball



WF, WR, WT

**Dimension table** (continued) · Dimensions in mm

Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
<b>WR24086.01<sup>3)7)</sup></b>	<b>35</b>	84,7	15,2	37,5	32	18	17,5	12	14,5	34,8	-
<b>WR14007</b>	<b>35</b>	85,5	15,5	40,1	29,9	18	-	12	-	37,8	RCHL-RW357013-LC5G68
<b>WR14007.01<sup>3)</sup></b>	<b>35</b>	85,5	15,5	40,1	29,9	18	-	12	-	37,8	RCHL-RW357013-LC5F4L5GG8
<b>WR11773</b>	<b>35</b>	91	16,4	35,8	38,8	18	-	12,038	-	33,5	-
<b>WR24035</b>	<b>35</b>	92,5	16,5	37,2	38,8	18	15,918	12	15	34,9	RW357002-LB6G43
<b>WR24034</b>	<b>35</b>	95	17,5	38,7	38,8	18	12	12	15	36,4	RCHL-RW357004-LB6G43
<b>WR24006</b>	<b>35</b>	96	26	40,1	29,9	18	15,918	12	7	37,8	RCHL-RW357006-LC5G75
<b>WR24025</b>	<b>35</b>	100,4	16,5	45,1	38,8	18	15,918	12	14,5	42,8	RCHL-RW357001-LD5LC5G75
<b>WR24038</b>	<b>35</b>	103,2	26,4	38	38,8	18	15,918	12	24,5	35,7	RCHL-RW357003-LC5G75
<b>WR14026.01<sup>3)</sup></b>	<b>35</b>	135,7	18,8	60,9	56	18	-	12,038	-	58,6	-
<b>WF11067</b>	<b>36</b>	101,5	17,1	40,5	43,9	16,95	-	12,038	-	38,5	-
<b>WF21141.01<sup>2)</sup></b>	<b>36</b>	116,45	19,7	57,75	39	20	16	16	18,75	54	-
<b>WF21900<sup>3)</sup></b>	<b>36</b>	119,1	21,5	45,7	51,9	17,008	15,008	12,055	20,5	43,4	-
<b>WF21088.01</b>	<b>36</b>	122,5	29	41,6	51,9	17,008	15,008	12,055	28	40,85	-
<b>WF21722</b>	<b>36</b>	123,7	26	45,8	51,9	17,008	15,008	12,055	25	43,8	-
<b>WR21112.02<sup>1)</sup></b>	<b>36</b>	125,5	25,35	48,25	51,9	20	15,002	15,002	22,5	44,5	-
<b>WF17053.01</b>	<b>36</b>	126	21	53,1	51,9	20,008	-	15,01	-	51,2	-
<b>WF21089</b>	<b>36</b>	130,7	33	45,8	51,9	17,008	15,008	12,055	32	43,8	-
<b>WF21544</b>	<b>36</b>	148	23	73,1	51,9	17,008	15,008	12,038	22	71	-
<b>WR01785.01<sup>1)6)</sup></b>	<b>38,1</b>	25	-	-	25	18,961	-	-	-	-	-
<b>WR11078.02</b>	<b>38,1</b>	73,1	26,1	-	46,9	18,961	15,918	-	25	-	-
<b>WR15088.01</b>	<b>38,1</b>	74,5	25,7	1,9	46,9	18,961	15,918	-	24	-	F-110607-20
<b>WR01812<sup>6)</sup></b>	<b>38,1</b>	79,1	30	1,1	48	18,961	-	-	-	-	-
<b>WR05103</b>	<b>38,1</b>	79,9	24	1,92	53,98	18,961	-	-	-	-	-
<b>WR15114</b>	<b>38,1</b>	79,9	24	1,92	53,98	18,961	15,918	-	20,3	-	F-110483
<b>WR15114.02<sup>1)</sup></b>	<b>38,1</b>	79,9	24	1,8	54,1	18,961	15,918	-	20,3	-	F-110483.3

<sup>1)</sup> Special shaft.

<sup>2)</sup> Flinger sleeve.

<sup>3)</sup> R-SAFE seal.

<sup>4)</sup> Rotary shaft seal.


<sup>5)</sup> No seal.

<sup>6)</sup> Special outer ring.

<sup>7)</sup> Rolling element sets laterally transposed.

# Water pump bearings

Double row  
Roller/ball



WF, WR, WT

**Dimension table (continued) · Dimensions in mm**

Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
<b>WR17670<sup>7)</sup></b>	<b>38,1</b>	88,96	23,1	34,96	30,9	18,961	—	12,038	—	32,66	—
<b>WR07017<sup>6)</sup></b>	<b>38,1</b>	90,88	33,32	3,58	53,98	18,961	—	—	—	—	WKN2357.L198
<b>WR17399<sup>6)</sup></b>	<b>38,1</b>	114,93	21,99	38,96	53,98	18,961	—	15,918	—	36,66	WKN2452-2
<b>WR17018<sup>6)</sup></b>	<b>38,1</b>	115,33	23,47	37,88	53,98	18,961	—	12,038	—	35,58	WKN2454D
<b>WR17669<sup>6)</sup></b>	<b>38,1</b>	117,98	20	44	53,98	18,961	—	15,918	—	41,7	—
<b>WR27010<sup>6)</sup></b>	<b>38,1</b>	118,15	19	51,15	48	18,961	15,918	12,038	17,54	48,85	WNS2465-1
<b>WR07100<sup>6)</sup></b>	<b>38,1</b>	119,36	61,8	3,58	53,98	18,961	—	—	—	—	WKN2469
<b>WR17019<sup>6)</sup></b>	<b>38,1</b>	120,5	25,8	40,72	53,98	18,961	—	15,918	—	38,42	WKN2474-2
<b>WR17641</b>	<b>38,1</b>	122,69	37,85	45,94	38,9	18,961	—	12,038	—	43,64	—
<b>WR27384<sup>6)</sup></b>	<b>38,1</b>	123,1	31,02	38,1	53,98	18,961	15,918	15,918	13,97	35,8	WKN2484-1
<b>WR15121</b>	<b>38,1</b>	123,5	23,37	47,15	53,98	18,961	—	15,906	—	41,2	F-45981
<b>WR15139<sup>1)</sup></b>	<b>38,1</b>	124,9	22	48,92	53,98	18,961	—	15,918	—	45,3	—
<b>WR17267<sup>6)</sup></b>	<b>38,1</b>	125,4	28,95	42,47	53,98	18,961	—	15,918	—	40,17	WKN2493
<b>WR17020.01</b>	<b>38,1</b>	125,98	28	44	53,98	18,961	—	12,038	—	41,7	WKN2495D
<b>WR17285<sup>6)</sup></b>	<b>38,1</b>	126	30,52	41,5	53,98	18,961	—	12,038	—	39,2	—
<b>WR24023</b>	<b>38,1</b>	127,36	18	68,26	41,1	18,961	15,918	12,038	15,5	65,96	RCHL-RW387404A-LC5G68
<b>WR17021.01<sup>6)</sup></b>	<b>38,1</b>	128	18	56,02	53,98	18,961	—	15,918	—	53,72	WKN2503
<b>WR17022<sup>6)</sup></b>	<b>38,1</b>	128,88	24,1	50,8	53,98	18,961	—	12,038	—	48,5	WKN2507-2D.TJ3311
<b>WR27567<sup>6)</sup></b>	<b>38,1</b>	129,93	33	42,95	53,98	18,961	15,009	12,038	31,09	40,65	—
<b>WR24023</b>	<b>38,1</b>	127,36	18	68,26	41,1	18,961	15,918	12,038	15,5	65,96	RCHL-RW387404A-LC5G68
<b>WR17652<sup>6)</sup></b>	<b>38,1</b>	130	25,92	50,1	53,98	18,961	—	12,038	—	47,8	—
<b>WR15120</b>	<b>38,1</b>	131,6	23,87	53,75	53,98	18,961	—	15,906	—	49,3	F-45646
<b>WR17298<sup>6)</sup></b>	<b>38,1</b>	133,31	32,54	46,79	53,98	18,961	—	12,038	—	44,49	WKN2524D
<b>WR27023<sup>6)</sup></b>	<b>38,1</b>	134,62	31,74	48,9	53,98	18,961	15,918	15,918	7,1	46,6	WKN2530
<b>WR17013.01<sup>6)</sup></b>	<b>38,1</b>	134,87	37,34	43,55	53,98	18,961	—	12,038	—	41,25	WKN2531-9D
<b>WR17024<sup>6)</sup></b>	<b>38,1</b>	134,87	37,34	43,55	53,98	18,961	—	15,918	—	41,25	WKN2531
<b>WR17025<sup>6)</sup></b>	<b>38,1</b>	134,87	30,09	50,8	53,98	18,961	—	15,918	—	48,5	WKN2531-3
<b>WR17227<sup>6)</sup></b>	<b>38,1</b>	134,88	30,1	50,8	53,98	18,961	—	12,038	—	48,5	WKN2531-8D

<sup>1)</sup> Special shaft.

<sup>2)</sup> Flinger sleeve.

<sup>3)</sup> R-SAFE seal.

<sup>4)</sup> Rotary shaft seal.

<sup>5)</sup> No seal.


<sup>6)</sup> Special outer ring.

<sup>7)</sup> Rolling element sets laterally transposed.

# Water pump bearings

Double row

Roller/ball



WF, WR, WT

**Dimension table** (continued) · Dimensions in mm

Designation	Dimensions									Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	
<b>WR17027<sup>6)</sup></b>	<b>38,1</b>	135,64	31,88	49,78	53,98	18,961	—	15,918	—	47,48 WKN2534
<b>WR17037<sup>1,6)</sup></b>	<b>38,1</b>	135,64	31,88	49,78	53,98	19,012	—	15,977	—	47,48 WKN6534
<b>WR17297<sup>6)</sup></b>	<b>38,1</b>	138,3	35,84	48,48	53,98	18,961	—	15,918	—	46,18 WKN2544-2
<b>WR17028<sup>6)</sup></b>	<b>38,1</b>	137,92	33,14	50,8	53,98	18,961	—	12,038	—	48,5 WKN2543-3D.TJ3315
<b>WR17029<sup>6)</sup></b>	<b>38,1</b>	138,27	24,11	60,18	53,98	18,961	—	12,038	—	57,88 WKN2544D
<b>WR27347<sup>6)</sup></b>	<b>38,1</b>	136,4	36,22	46,2	53,98	18,961	15,918	15,918	12,32	43,9 WKN2537.F1055
<b>WR25109</b>	<b>38,1</b>	142,3	39,4	48,92	53,98	18,961	15,918	15,918	35,8	45,3 F-45648
<b>WR27030<sup>6)</sup></b>	<b>38,1</b>	143,48	30,83	58,67	53,98	18,961	15,918	15,918	12,24	56,37 WKN2564-6/WKN 2564-5
<b>WR17117<sup>6)</sup></b>	<b>38,1</b>	144,15	32,47	57,7	53,98	18,961	—	12,038	—	55,4 WKN2567D
<b>WR17031<sup>6)</sup></b>	<b>38,1</b>	144,7	32,05	58,67	53,98	18,961	—	15,918	—	56,37 WKN2569
<b>WR17394<sup>1,6)</sup></b>	<b>38,1</b>	144,7	32,05	58,67	53,98	19,012	—	15,977	—	56,37 —
<b>WR14024</b>	<b>38,1</b>	148,85	28,24	66,63	53,98	18,961	—	12,038	—	64,33 IHA-RW387405AFS2-LC5G75
<b>WR27348<sup>6)</sup></b>	<b>38,1</b>	150,5	35,05	61,47	53,98	18,961	15,918	15,918	12,88	59,17 WKN2592-2
<b>WR27101<sup>1,6)</sup></b>	<b>38,1</b>	151,87	22,5	75,39	53,98	18,961	18,009	8,395	19,5	36,91 WKN2597.T3637
<b>WR17118<sup>6)</sup></b>	<b>38,1</b>	152,15	40,47	57,7	53,98	18,961	—	12,038	—	55,4 WKN2599D
<b>WR17032<sup>6)</sup></b>	<b>38,1</b>	153,42	45,75	53,69	53,98	18,961	—	15,918	—	51,39 WKN2604
<b>WR17033<sup>6)</sup></b>	<b>38,1</b>	156,59	39,62	62,99	53,98	18,961	—	15,918	—	60,69 WKN2616
<b>WR27034<sup>6)</sup></b>	<b>38,1</b>	157,99	46,74	57,27	53,98	18,961	15,918	15,918	14,78	54,97 WKN2622
<b>WR27301<sup>6)</sup></b>	<b>38,1</b>	157,99	46,74	57,27	53,98	18,961	15,918	12,038	14,78	54,97 WKN2622-1D
<b>WR27467<sup>6)</sup></b>	<b>38,1</b>	158,68	35,05	69,65	53,98	18,961	15,918	15,918	12,88	67,35 WKN2627-1/WKN2627
<b>WR17574<sup>6)</sup></b>	<b>38,1</b>	160,5	44,42	62,1	53,98	18,961	—	15,918	—	59,8 WKN2631
<b>WR27341<sup>6)</sup></b>	<b>38,1</b>	161,04	46,74	60,32	53,98	18,961	15,918	15,918	33,3	58,02 WKN2634-1
<b>WR11843</b>	<b>38,1</b>	169,84	23,15	92,71	53,98	18,961	—	12,038	—	90,41 —
<b>WR17326<sup>6)</sup></b>	<b>38,1</b>	169,84	23,15	92,71	53,98	18,961	—	15,918	—	90,41 —
<b>WR17036<sup>6)</sup></b>	<b>38,1</b>	174,75	52,53	68,24	53,98	18,961	—	12,038	—	65,94 WKN2688-7D
<b>WR27035<sup>6)</sup></b>	<b>38,1</b>	174,75	52,53	68,24	53,98	18,961	15,918	15,918	14,1	65,94 WKN2688
<b>WR27343<sup>6)</sup></b>	<b>38,1</b>	174,75	35	85,77	53,98	18,961	15,918	12,038	14,1	83,47 WKN2688-3D

<sup>1)</sup> Special shaft.

<sup>2)</sup> Flinger sleeve.

<sup>3)</sup> R-SAFE seal.

<sup>4)</sup> Rotary shaft seal.


<sup>5)</sup> No seal.

<sup>6)</sup> Special outer ring.

<sup>7)</sup> Rolling element sets laterally transposed.

# Water pump bearings

Double row  
Roller/ball



WF, WR, WT

**Dimension table (continued) · Dimensions in mm**

Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
<b>WR01565.03<sup>7)</sup></b>	<b>40</b>	62,65	1,85	22	38,8	20,004	—	—	—	—	—
<b>WT01715.02<sup>7)</sup></b>	<b>40</b>	67,65	27	1,85	38,8	20,004	—	—	—	—	—
<b>WF01555.01</b>	<b>40</b>	85,25	1,85	33,5	49,9	20,004	—	—	—	—	—
<b>WR01418.01</b>	<b>40</b>	85,25	1,85	33,5	49,9	20,004	—	—	—	—	—
<b>WT11353<sup>2)</sup></b>	<b>40</b>	103,3	20,6	43,9	38,8	20,004	—	12,038	—	38,9	—
<b>WF11549.03<sup>2)</sup></b>	<b>40</b>	129,8	27,1	52,8	49,9	20,004	—	12,038	—	47,4	—
<b>WF11672.01<sup>4)</sup></b>	<b>40</b>	132	17,1	61,5	53,4	20,004	—	16	—	56,5	—
<b>WF11058.02<sup>2)</sup><sup>4)</sup></b>	<b>40</b>	132	18,1	61,5	52,4	20,004	—	16	—	56,5	—
<b>WF11061.02<sup>2)</sup></b>	<b>40</b>	143	31,5	61,5	50	20,004	—	16	—	55	—
<b>WF21171.03<sup>1)</sup><sup>2)</sup></b>	<b>40</b>	151	51,6	49,5	49,9	20	14,5	16	49	44	—
<b>WF11192.01<sup>2)</sup></b>	<b>40</b>	168	45,1	73	49,9	20,004	—	12,038	—	64	—
<b>WR04031<sup>1)</sup></b>	<b>42</b>	80	32	2,1	45,9	22	—	—	—	—	IH-RW428620-LD5G75
<b>WR24002</b>	<b>42</b>	110,5	23,6	41	45,9	22	19	12	22,6	38,7	RW4286-01-LC43
<b>WR24020</b>	<b>42</b>	115,5	26,5	43,1	45,9	22	18	13	24	40,8	RCHL-RW428604-LCF5G75
<b>WR24021</b>	<b>42</b>	127,5	26,6	55	45,9	22	18	12	24,15	52,7	RCHL-RW428621A-LCF5G75
<b>WR14043</b>	<b>42</b>	130,4	29,4	55,1	45,9	22	—	16	—	52,8	—
<b>WR14003.01<sup>1)</sup><sup>3)</sup></b>	<b>42</b>	135,7	18,8	61	55,9	22	—	12,038	—	58,7	RCHL-RW428617-LD5F4L5G68
<b>WR14016</b>	<b>42</b>	142	41	55,1	45,9	22	—	16	—	52,8	RCHL-RW428602-LC5G68
<b>WR14069</b>	<b>42</b>	142,75	28,95	67,9	45,9	22	—	12	—	65,8	—
<b>WT11527</b>	<b>47</b>	124	27,1	47	49,9	24	—	16	—	40	—
<b>WT21156.01</b>	<b>47</b>	124	27,1	47	49,9	24	20	12,038	25,5	46	—
<b>WT11352.04<sup>2)</sup></b>	<b>47</b>	134	27,1	57	49,9	24	—	16	—	50	—
<b>WR27256<sup>6)</sup></b>	<b>47,625</b>	176,1	20	102,12	53,98	25,4	18,961	15,918	16,5	63,5	WNS2693-1
<b>WR11858</b>	<b>47,625</b>	179,71	33,14	92,59	53,98	25,4	—	12,038	—	48,45	—

<sup>1)</sup> Special shaft.

<sup>2)</sup> Flinger sleeve.

<sup>3)</sup> R-SAFE seal.

<sup>4)</sup> Rotary shaft seal.

<sup>5)</sup> No seal.


<sup>6)</sup> Special outer ring.

<sup>7)</sup> Rolling element sets laterally transposed.

# Water pump bearings

Double row

Roller/ball



WF, WR, WT

**Dimension table** (continued) · Dimensions in mm

Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
<b>WR01123.01<sup>1)</sup></b>	<b>55</b>	72	10	2	60	25,021	—	—	—	—	—
<b>WR01125.02</b>	<b>55</b>	86	25	1	60	25,061	—	—	—	—	—
<b>WR07658<sup>1),6)</sup></b>	<b>55</b>	95,6	3,7	31,9	60	25,061	—	—	—	—	—
<b>WR11122.01</b>	<b>55</b>	110	25	25	60	25,061	—	16,056	—	24	—
<b>WR17103<sup>2),6)</sup></b>	<b>55</b>	127	25	42	60	25,061	—	16,056	—	38,75	WNS2500
<b>WR17104<sup>2),6)</sup></b>	<b>55</b>	127	25	42	60	25,061	—	15,056	—	37,5	WNS2500-1.F2773
<b>WR17104.01<sup>1)</sup></b>	<b>55</b>	127	25	42	60	25,061	—	15,056	—	37,5	—
<b>WR27105<sup>6)</sup></b>	<b>55</b>	145,54	31,88	53,66	60	25,061	18,961	15,918	28,7	51,36	WNS2572.T3264
<b>WF11228</b>	<b>55</b>	150	30	63,6	56,4	25,061	—	16	—	61,5	WNS2590
<b>WT11687</b>	<b>55</b>	150	30	63,6	56,4	25,061	—	16	—	61,5	—
<b>WR27106<sup>6)</sup></b>	<b>55</b>	153,29	32	61,29	60	25,061	18,961	15,918	13,59	58,99	WNS2603
<b>WR27107<sup>6)</sup></b>	<b>55</b>	156,6	35,43	61,17	60	25,061	18,961	15,918	13,59	58,87	WNS2616-6
<b>WR27256<sup>6)</sup></b>	<b>55</b>	176,1	20	102,12	53,98	25,4	18,961	15,918	16,5	63,5	WNS2693-1
<b>WR11103.04</b>	<b>55</b>	187	25	62	100	25,061	—	15,056	—	42	—

<sup>1)</sup> Special shaft.

<sup>2)</sup> Flinger sleeve.

<sup>3)</sup> R-SAFE seal.

<sup>4)</sup> Rotary shaft seal.


<sup>5)</sup> No seal.

<sup>6)</sup> Special outer ring.

<sup>7)</sup> Rolling element sets laterally transposed.

# Water pump bearings

Triple row  
Roller/ball/roller



WM

**Dimension table** - Dimensions in mm


Designation	Dimensions										Previous designation
	D	L	L <sub>1</sub>	L <sub>2</sub>	C	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	
<b>WM01798.01</b>	<b>30</b>	105,95	19,55	46,5	39,9	16	-	-	-	-	-
<b>WM01901.01</b>	<b>38,1</b>	82,78	26,5	2,3	53,98	18,961	-	-	-	-	-
<b>WM01878.01</b>	<b>38,1</b>	86,8	30,52	2,3	53,98	18,961	-	-	-	-	-
<b>WM12348<sup>1)</sup></b>	<b>38,1</b>	90,68	34,4	2,3	53,98	18,961	15,918	-	26,4	-	-

1) Special shaft.

# Water pump bearings

Double decker

Ball/ball and roller/ball



WD

**Dimension table** · Dimensions in mm

Designation	Dimensions													Previous designation	
	D	D <sub>i</sub>	L	L <sub>1</sub>	L <sub>2</sub>	C <sub>i</sub>	d <sub>k</sub>	D <sub>11</sub>	D <sub>22</sub>	L <sub>11</sub>	L <sub>22</sub>	C <sub>0</sub>	L <sub>111</sub>	L <sub>222</sub>	
<b>WD01980.07<sup>3)4)7)</sup></b>	<b>40</b>	24,5	121,5	14,5	49,5	57,5	12,038	-	-	-	-	32,9	22,6	2	-

1) Special shaft.

2) Flinger sleeve.

3) R-SAFE seal.

4) Rotary shaft seal.

5) No seal.

6) Special outer ring.

7) Rolling element sets laterally transposed.

# Addresses

<b>USA (Aftermarket)</b>	LuK Automotive Systems 5370 Wegman Drive Valley City, OH 4428-9700 Tel. +1 330 273 4383 Fax +1 330 273 3522 <a href="mailto:luk-in-a-fag-as.us@schaeffler.com">luk-in-a-fag-as.us@schaeffler.com</a>	<b>India</b> INA Bearing India Pvt. Ltd. Plot No. A-3, Talegoan Industrial & Floriculture Park, Village Amb., Navlakh Umbre, Taluka Maval Pune 410 507 Tel. +91 20 30614100 Fax +91 20 30614308 <a href="mailto:info.in@schaeffler.com">info.in@schaeffler.com</a>
<b>USA (OEM)</b>	Schaeffler Group Automotive 1750 East Big Beaver Road Troy, MI 48083 Tel. +1 248 528 9080 Fax +1 248 528 4961 <a href="mailto:richard.neilson@schaeffler.com">richard.neilson@schaeffler.com</a>	<b>China</b> Schaeffler Holding (China) Co., Ltd. No. 1 Antuo Road (west side of Anhong Road) AnTing JiaDing District 201804 Shanghai Tel. +86 21 3957 6666 Fax +86 21 3957 6600 <a href="mailto:info_china@schaeffler.com">info_china@schaeffler.com</a>
<b>Brazil</b>	Schaeffler Brasil Ltda. Bairro Éden 18087-101 Sorocaba, SP Tel. +55 15 33 35 19 00 Fax +55 15 33 35 38 20 <a href="mailto:sac.br@schaeffler.com">sac.br@schaeffler.com</a>	<b>Korea</b> Schaeffler Korea Corporation 14F, Kyobo life insurance Bldg. #1, Jongno-gu Seoul, 110-714 Tel. +82 2-311-3000 Fax +82 2-311-3060 <a href="mailto:sangnam.lee@schaeffler.com">sangnam.lee@schaeffler.com</a>
<b>Germany</b>	WPB GmbH & Co. KG Industriestraße 1–3 91074 Herzogenaurach Tel. +49 9132 82 3767 Fax +49 9132 82 4900 <a href="mailto:gerald.loeslein@schaeffler.com">gerald.loeslein@schaeffler.com</a>	



**Schaeffler Technologies  
GmbH & Co. KG**  
Industriestraße 1–3  
91074 Herzogenaurach  
Germany  
Internet [www.ina.com](http://www.ina.com)  
E-mail [info.de@schaefller.com](mailto:info.de@schaefller.com)  
  
In Germany:  
Phone 0180 5003872  
Fax 0180 5003873  
  
From other countries:  
Phone +49 9132 82-0  
Fax +49 9132 82-4950

Every care has been taken to ensure the correctness of the information contained in this publication but no liability can be accepted for any errors or omissions. We reserve the right to make technical changes.

© Schaeffler Technologies GmbH & Co. KG  
Issued: 2014, June

This publication or parts thereof may not be reproduced without our permission.  
TPI 131 GB-D